
# R series (10A

-10 -223



①Model Name ②Rated Current

3 Line to ground capacitor code: See table 1.1.

table1.1 Line to ground capacitor code

	Code	Line to ground capacitor (nominal value)
	000	Not Provided
	223	22000pF

4 Options

D :DIN rail installation type
T :Terminal block type

DT:Terminal block and DIN rail type

\* The dimensions change when the option is set. Refer to External view.

## Features of SNR series (10A)

# Ripple noise attenuation type for switch mode power supplies(DC)

· 50 VDC


· Best filter for switch mode power supplies of analog circuits

## **Specifications**

•	•				
No.	Items	SNR-10-223			
NO.	items	Interface:Connector			
1	Rated Voltage DC[V]	50			
2	Rated Current DC[A] *1	10 (Peak 20)			
3	Test Voltage (Terminal-Mounting Plate)	500 VAC (Cutoff Current = 100mA), 1 minute at room temperature and humidity			
4	Isolation Resistance (Terminal-Mounting Plate)	500 VDC 50M $\Omega$ min at room temperature and humidity			
5	D.C Resistance[m $\Omega$ ]	20 max			
6	Operating temperature	-40 to +71 ℃ (Refer to Derating Curve)			
7	Operating humidity	20 to 95%RH (Non condensing)			
8	Storage temperature/humidity	-40 to +75℃/20 to 95%RH (Non condensing)			
9	Vibration	10 to 55Hz, 19.6m/s² (2G), 3min. Period, 1hour each X, Y and Z axis			
10	Impact	196.1m/s² (20G), 11ms Once each X, Y and Z axis			
11	Safety agency approvals	UL60950-1, C-UL (CSA60950-1), EN60950-1			
12 Case size (without projection) /Weight		52 X 35 X 117 mm [2.05 X 1.38 X 4.61 inches] (W X H X D) /140g max (Option : -D, -T, -DT refer to external view)			

<sup>\*1</sup> Peak current for 10 sec. And Duty 35% max, refer to Instruction Manual 5. In detail.


## **Circuit Diagram**



CY: Line to ground capacitor Co: Electrolytic capacitor  $\stackrel{\perp}{=}$ : Mounting Plate

■Expected life: 10 years

# **Derating Curve**






 $2-\phi 4.5$ 


[0.18] Mounting Hole +Vout

## **External view**

#### **Standard Type**

### Terminal block Type





※ Tolerance: ±1 [±0.04]

※ Dimensions in mm, [ ]=inches

\* Weight: 150g max

\* Case : PBT

- PCB Material /thickness : CEM3 /1.6mm [0.06 inches] % Mounting plate : Iron (surface finishing : nickel plating) t=1.0 [0.04] % Case : PBT
- ※ Dimensions in mm, [ ]=inches
- ※ Keeping drawing current per pin below 5A (7A at peak current)
- for CN1 to CN2

I/O Co	nnector	Mating connector	Terminal
CN1,CN2	B6P-VH	VHR-6N	Reel:SVH-21T-P1.1
			Bulk:BVH-21T-P1.1

1.2.3

456

Pin No. Function

Name Plate

108.5

[4.27] 112

Pin No. Function

1,2,3 -Vout

+Vout

-Vout

+Vout

(Mfr:J.S.T)

Option harness: Refer to Instruction Manual 4

**DIN rail installation Type** 

CN1
Pin No. Function

-Vin

+Vin

1.2.3

456

M4

(9)

N1 Pin No. Function

1,2,3 -Vin


≟ FG

### Terminal block type+DIN rail installation Type

※ PCB Material /thickness : CEM3 /1.6mm [0.06 inches]

Mounting plate: Iron (surface finishing: nickel plating) t=1.0 [0.04]

※ Terminal block screw tightening torque M3:0.8N ⋅ m (8.5kgf ⋅ cm) max Keeping drawing current per pin below 8A (10A at peak current) for TB1 to TB2



※ Tolerance : ±1 [±0.04]

Mounting Plate

- \*\* Weight: 150g max \*\* PCB Material /thickness: CEM3 / 1.6mm [0.06 inches]
- Mounting plate: Iron (surface finishing: nickel plating) t=1.0 [0.04]
- \* Case : PBT
- ※ Dimensions in mm, [ ]=inches
  - Keeping drawing current per pin below 5A (7A at peak current) for CN1 to CN2

I/O Co	nnector	Mating connector	Terminal
CN1,CN2	B6P-VH	VHR-6N	Reel:SVH-21T-P1.1
			Bulk:BVH-21T-P1.1
			(Mfr:J.S.T)

Option harness: Refer to Instruction Manual 4

DIN rail

- Weight: 160g max
  PCB Material /thickness: CEM3 /1.6mm [0.06 inches]
- Mounting plate: Iron (surface finishing: nickel plating) t=1.0 [0.04]
- ※ Dimensions in mm, [ ]=inches
- Terminal block screw tightening torque M3:0.8N · m (8.5kgf · cm) max
- Keeping drawing current per pin below 8A (10A at peak current) for TB1 to TB2

## ■Note when installing the EMI/EMC Filter on a DIN rail.

When the EMI/EMC Filter is grounded through the DIN rail, the proper noise attenuation may not be achieved.

Be sure to connect the FG terminal of the EMI/ EMC Filter body to the earth.

