
Size: 1.812" L X 2.500" W X 2.080"H

ALL PRODUCTS ARE ROHS COMPLIANT





Solenoid shown energized in drawing with plunger fully seated

| Part No. | Duty Cycle | Voltage | Resistance (Ω) ± 5% | Max On Time | Watts Seated (W) | Current Seated (A) |
|----------|--------------|-----------------|------------------------|----------------|------------------------|--------------------------|
| 2005-M-1 | Continuous | 120 VAC / 60Hz | 20.5 | 8 | 17.9 | 0.43 |
| 2255-M-1 | Intermittent | 120 VAC / 60 Hz | 18.3 | 3 Mins | 23.5 | 0.64 |
| 2006-M-1 | Continuous | 240 VAC / 60 Hz | 82.0 | 8 | 17.5 | 0.22 |
| 2256-M-1 | Intermittent | 240 VAC / 60 Hz | 73.5 | 3 Mins | 23.8 | 0.32 |

Continuous Duty = 100% "On" Time Intermittent Duty = 20% "On" Time

When ordering please refer to Part No. as listed above

| | Holding Force (oz.) | | | | | | | | |
|-------------------|---------------------|-------|-------|-------|-------|-------|-------|-------|-----|
| Stroke (in.) | 0.060 | 0.125 | 0.250 | 0.375 | 0.500 | 0.625 | 0.750 | 1.000 | |
| Continuous Duty | 160 | 128 | 101 | 97 | 100 | 110 | 96 | 64 | 112 |
| Intermittent Duty | 192 | 160 | 128 | 120 | 120 | 110 | 101 | 64 | N/A |

Additional Specifications:

Dielectric Strength: 1500 VRMS

Heat Sink: None

Coil Insulation: Class "A"; 105°C Max Temperature

Coil Termination: Solder Lugs Total Unit Weight: 18 oz. / 510 g

