1. Base Data

| Part No. | 300-30957 |
|-------------------------------------|--|
| Туре | HIS-PACK-9.5/4.7 |
| Color | Green-Yellow |
| Features | • E-beam Crosslinked Polyolefin, thin-wall and flexible • Shrink ratio 2:1 • Available in colors: black, red, blue, transparent and yellow/green. • 10 sizes from 1,2 mm to 25,4 mm • Handy dispenserbox including table with full range of applications |
| Application | • General purpose electrical insulation • Protection against corrosion and mechanical abrasion |
| shortdescription50character | Thin wall heat shrink tubing |
| Shrink Ratio | 2:1 |
| Size | 9.5/4.8 |
| Variant | Thin-Wall |
| 2. Product Dimensions | |
| Length (L) | 196.8 " / 5 m |
| Wall Thickness (WT) | .023 |
| Wall Thickness | 0.60 mm |
| Longitudinal change after shrinkage | +/- 5% |
| Recov. Ø d max. | 4.7 mm |
| Recovered Ø | .17 " |
| Supplied Ø | .37 " / 9.5 mm |

4. Material and Specifications

| Material | Polyolefin, cross-linked (POX) |
|-------------------------|---------------------------------------|
| Material Shortcut | POX |
| Certification | UL224 125 °C 600V VW-1 |
| Dielectric Strength | 20 kV/mm according to IEC 243 |
| Elongation at break | 400% (ASTM D 2671) |
| Flammability | UL224 VW-1 (except clear) |
| Insulation Class | E (VDE 0530) |
| Min. Shrink Temperature | +100 °C |
| Operating Temperature | -67 °F to +257 °F (-55 °C to +125 °C) |
| ROHS Conformity | √ RoHS |