EZ-LIGHT® Touch Gen 2 K50 FDA-Grade Illuminated Buttons



Datasheet

Lighted touch button with bipolar outputs



- FDA-grade materials; rated to IEC IP67, IP68, and IP69K
- Laser marked information withstands aggressive cleaning procedures
- Excellent immunity to false triggering by water spray, detergents, oils, and other foreign materials
- Rugged, cost-effective, and easy-to-install touch button with multicolor light
- Momentary versions remain activated as long as touch is present
- Latching versions start up not activated and toggle between activated and not activated on successive touches
- Ergonomically designed to eliminate hand, wrist, and arm stresses associated with repeated switch operation; require no physical force to operate
- Can be actuated with bare hands or in gloves
- 12 to 30 V dc operation

Models

Model ¹	Function	Output	Light (not activated)	Light (activated)	Connection
K50ALBT2FXGHQP	Lotobing	Bipolar, N.O.	_	Green	150 mm (6 in) pigtail PVC cable with a 5-pin M12/ Euro-style male, stainless steel, quick disconnect (QD)
K50RLBT2FXGHQP	Latching	Bipolar, N.C.			
K50ABT2FXGHQP	Managartani	Bipolar, N.O.			
K50RBT2FXGHQP	Momentary	Bipolar, N.C.			
K50ALBT2FGGHQP	Latelete e	Bipolar, N.O.	Green	Green	
K50RLBT2FGGHQP	Latching	Bipolar, N.C.			
K50ABT2FGGHQP	Managartani	Bipolar, N.O.			
K50RBT2FGGHQP	Momentary	Bipolar, N.C.			
K50ALBT2FRGHQP	Lotobio	Bipolar, N.O.	Red	Green	
K50RLBT2FRGHQP	Latching	Bipolar, N.C.			
K50ABT2FRGHQP	Managartani	Bipolar, N.O.			
K50RBT2FRGHQP	Momentary	Bipolar, N.C.			



WARNING: Not To Be Used for Personnel Protection

Never use this device as a sensing device for personnel protection. Doing so could lead to serious injury or death. This device does not include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A sensor failure or malfunction can cause either an energized or de-energized sensor output condition.

¹ To order the 2 m (6.5 ft) cable models, omit suffix QP from model number (example, K50ALBT2FXGH). A model with a QD requires a mating cable (see *Cordsets* on page 3).



Original Document 189836 Rev. C

Specifications

Supply Voltage

12 to 30 V dc

Supply Current

< 75 mA max current at 12 V dc (exclusive of load) < 50 mA max current at 30 V dc (exclusive of load)

Supply Protection Circuitry

Protected against reverse polarity and transient voltages

Output Rating

Maximum Load: 150 mA

On-state saturation voltage: < 2 V at 10 mA dc; < 2.5 V at 150

nA dc

Off-state leakage current: <10 µA at 30 V dc

Operating Conditions

Temperature: -40 °C to +50 °C (-40 °F to +122 °F) Humidity: 90% at 50 °C maximum relative humidity (non-condensing)

Storage

-40 °C to +70 °C (-40 °F to +158 °F)

Environmental Rating

IEC IP67, IP69K per DIN 40050-9.

Vibration and Mechanical Shock

Vibration 10 Hz to 55 Hz 1.0 mm p-p amplitude per IEC 60068-2-6 Shock 30G 11 ms duration, half sine wave per IEC 60068-2-27

Certifications





Output Response Time

Momentary models: 50 milliseconds On and Off Latching models: 150 milliseconds On and Off

Power-Up Delay

300 milliseconds

Latching models start up in a 'not activated' state

Connections

150 mm (6 in) pigtail PVC cable with a 5-pin M12/Euro-style male, stainless steel, quick disconnect (QD) or 2 m (6.5 ft) unterminated PVC-jacketed cable

Construction

Base, dome, and nut: FDA-grade polycarbonate

Mounting

 $M30 \times 1.5$ Threaded base Max torque 4.5 N·m (40 in·lbf)

Required Overcurrent Protection



WARNING: Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table.


Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.

Supply wiring leads < 24 AWG shall not be spliced. For additional product support, go to http://

www.bannerengineering.com.

Supply Wiring (AWG)	Required Overcurrent Protection (Amps)
20	5.0
22	3.0
24	2.0
26	1.0
28	0.8
30	0.5

Dimensions



All measurements are listed in millimeters (inches), unless noted otherwise.

Wiring Diagram



Accessories

Cordsets

5-Pin Threaded M12/Euro-Style Cordsets—Single Ended				
Model	Length	Style	Dimensions	Pinout (Female)
MQDC1-501.5	0.50 m (1.5 ft)	Straight		
MQDC1-506	1.83 m (6 ft)			
MQDC1-515	4.57 m (15 ft)			
MQDC1-530	9.14 m (30 ft)		M12 x 1 - ø 14.5 -	1 - 2
MQDC1-506RA	1.83 m (6 ft)	Right-Angle	32 Typ. [1.26"] 30 Typ. [1.18"] 6 14.5 [0.57"]	1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
MQDC1-515RA	4.57 m (15 ft)			
MQDC1-530RA	9.14 m (30 ft)			

5-Pin Threaded M12/Euro-Style Cordsets—Washdown Stainless Steel				
Model	Length	Style	Dimensions	Pinout (Female)
MQDC-WDSS-0506	1.83 m (6 ft)	Straight		2
MQDC-WDSS-0515	4.57 m (15 ft)		Ø15.5 mm	1 - (60)
MQDC-WDSS-0530	9.14 m (30 ft)			1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray


5-Pin Threaded M12/Euro-Style Cordsets—Washdown, with Shield				
Model	Length	Style	Dimensions	Pinout (Female)
MQDCWD-506	1.83 m (6 ft)			2
MQDCWD-530	9.14 m (30 ft)	Straight	42 Typ. [1.65"] 0 15.0 [0.57"] M12 x 1	1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray

Brackets

SMB30A


- Right-angle bracket with curved slot for versatile orientation
- Clearance for M6 (1/4 in) hardware
- Mounting hole for 30 mm sensor
- 12-ga. stainless steel

Hole center spacing: A to B=40 Hole size: A=Ø 6.3, B= 27.1 x 6.3, C=Ø 30.5



SMB30FA

- Swivel bracket with tilt and pan movement for precise adjustment
- Mounting hole for 30 mm sensor
- 12-ga. 304 stainless steel
- Easy sensor mounting to extrude rail T-slot
- Metric and inch size bolt




Bolt thread: SMB30FA, A= 3/8 - 16 x 2 in; SMB30FAM10, A= M10 -1.5 x 50

Hole size: B= Ø 30.1

SMB30FVK


- V-clamp, flat bracket and fasteners for mounting to pipe or extensions
- Clamp accommodates 28 mm dia. tubing or 1 in. square extrusions
- 30 mm hole for mounting sensors

Hole size: A= ø 31



SMB30MM

- 12-ga. stainless steel bracket with curved mounting slots for versatile orientation
- Clearance for M6 (1/4 in) hardware
- Mounting hole for 30 mm sensor




Hole center spacing: A = 51, A to B = 25.4Hole size: $A = 42.6 \times 7$, $B = \emptyset 6.4$, $C = \emptyset 30.1$

SMB30RAVK

- V-clamp, right-angle bracket and fasteners for mounting sensors to pipe or extrusion
- Clamp accommodates 28 mm dia. tubing or 1 in. square extrusions
- 30 mm hole for mounting


Hole size: $A = \emptyset 30.5$



SMB30SC

- Swivel bracket with 30 mm mounting hole for sensor
- Black reinforced thermoplastic polyester
- Stainless steel mounting and swivel locking hardware included


Hole center spacing: A=ø 50.8 Hole size: A=Ø 7.0, B=Ø 30.0



SMBAMS30P

- · Flat SMBAMS series bracket
- 30 mm hole for mounting sensors
- Articulation slots for 90° + rotation
- 12-ga. 300 series stainless steel

Hole center spacing: A=26.0, A to B=13.0 Hole size: A=26.8 x 7.0, B=Ø 6.5, C=Ø 31.0



SMBAMS30RA

- Right-angle SMBAMS series bracket
- 30 mm hole for mounting sensors
- Articulation slots for 90° + rotation
- 12-ga. (2.6 mm) cold-rolled steel

Hole center spacing: A=26.0, A to B=13.0 Hole size: A=26.8 x 7.0, B=Ø 6.5, C=Ø 31.0



TC-K50-CL

Touch cover



Diameter: A = Height: B =

Banner Engineering Corp. Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp.