

Path: [Home](#) > [Rack Index](#) > Panel Rails

### Tapped Rails:

The strongest, fastest to use, most economical and **OUR MOST POPULAR** panel rail. Designed to work with all of our accessories without needing adaptors. Downside is you **MUST** use 10-32 hardware.


### Square Hole Rails:

Mainly used when hanging large servers (using mounting hooks or "snap" in rails - that require square holes). Anything else you want to rack mount you simply order your favorite thread clip nuts (ie...10-32, 12-24 or M6).

Square hole rails also allow you **THE MOST FLEXIBILITY**....you can use hooks, "snap in" rails, 10-32, 12-24 or M6 thread cage nuts. Downside is you need to purchase cage nuts for each hole used. They also take longer to mount - usually requires our insertion tool - **RCNIT** (see below). **ALSO**, you should know **AHEAD** of time where you will mount equipment & need cage nuts installed. It is not much fun juggling heavy rack mount equipment while trying to clip cage nuts into the square holes you need!

# Square Hole - Cage Nut - Insertion Tool

Part Number **RCNIT**



- Allows for easy installation of cage nuts in square rail holes - a valuable tool.
- Spring steel tool
- Highly recommended, as square hole - cage nut hardware is NOT easy to install.



[Assembly Instructions](#)

# Panel Rails (C2 Series)

## TAPPED RAILS

- **SOLD IN PAIRS**
- Drilled and tapped (10-32)
- Heavy duty construction - formed from 10 gauge steel
- Full EIA hole centers (5/8 - 5/8 - 1/2 inch spacing)
- Bolts vertically in cabinet to amhal struts
- Includes strut mounting hardware, panel mounting hardware available on page 119
- Zinc plated finish
- Front of rail allows for 19" panel rack mounting
- Rear of rail flange for rear equipment support or accessory mounting



Part Number (Sold in Pairs)	Panel Height	
	Inches	Units
CCR35TZPL	35.00	20
CCR42TZPL	42.00	24
CCR49TZPL	49.00	28
CCR56TZPL	56.00	32
CCR63TZPL	63.00	36
CCR70TZPL	70.00	40
CCR78TZPL	78.75	45
CCR85TZPL	85.75	49

## SQUARE HOLE RAILS

- **SOLD IN PAIRS**
- Square hole punched - allowing choice of hardware for 10-32 or 12-24 or M6 thread cage nuts)
- Includes a starter quantity (25) of 10-32 cage nuts
- Heavy duty construction - formed from 12 gauge steel
- Full EIA hole centers (5/8 - 5/8 - 1/2 inch spacing)
- Bolts vertically in cabinet to amhal struts
- Includes strut mounting hardware, panel mounting hardware available on page 119
- Zinc plated finish
- Front of rail allows for 19" panel rack mounting
- Rear "L" of rail for rear equipment support or accessory mounting




19" Rack Mount



Cage Nut  
Installation Tool

- Allows for easy installation of cage nuts in square rail hole
- Spring steel tool
- Part Number **RCNIT**



Additional Cage Nuts

Part Number	Qty. Per Package	Thread
1421CNA25	25	10-32
1421CNA100	100	10-32
1421CNC25	25	12-24
1421CNC100	100	12-24
1421CNB25	25	M6
1421CNB100	100	M6

Part Number (Sold in Pairs)	Panel Height	
	Inches	Units
CPR35SZPL	35.00	20
CPR42SZPL	42.00	24
CPR49SZPL	49.00	28
CPR56SZPL	56.00	32
CPR63SZPL	63.00	36
CPR70SZPL	70.00	40
CPR78SZPL	78.75	45
CPR85SZPL	85.75	49

Welded