



# Heating Products



### NC - Normally Closed (Red)

Used in conjunction with heaters.  
Contact opens when rising temperatures reach the set point temperature shutting heater off.

### NO - Normally Open (Blue)

Used in conjunction with fans.  
Contact closes when rising temperatures reach the set point temperature turning fan on.

## Thermostat

- Designed to provide air temperature control and monitoring in cabinets.
- Thermostat NC (Normally Closed) for the control of heaters and heater fans.
- Thermostat NO (Normally Open) for the control of cooling units, or for switching signal transmitters in case of overheating.
- Available in Fahrenheit or Celsius.

Sensor Element:	Thermostatic bi-metal
Switching difference (hysteresis):	±4°F (±3°K)
Adjustment Range:	30-140°F
Noise Suppression:	"N" (according to VDE 0875)
Connection:	2 pole terminal for AWG 14 (2.5mm <sup>2</sup> )
Mounting:	Easily installed by clip mounting on 35 mm or 38 mm DIN rails (included)
Housing:	Flame retardant plastic UL94VO
Color:	Gray (SB)
Protection:	IP30
Approval:	UL Recognized Component , cUL Recognized Component, CE

Part No.	Scale	Contact Type	Dimensions Height x Width x Depth	Switching Capacity	Ship Wt. lbs
SKT011409NC	°F	Normally Closed	2.4 x 1.3 x 1.4	15 A (1) AC 120 V, 10 A (1) AC 250 V	1
SKT011409NC-C	°C	Normally Closed	2.4 x 1.3 x 1.4	15 A (1) AC 120 V, 10 A (1) AC 250 V	1
SKT011419NO	°F	Normally Open	2.4 x 1.3 x 1.4	15 A (1) AC 120 V, 10 A (1) AC 250 V	1
SKT011419NO-C	°C	Normally Open	2.4 x 1.3 x 1.4	15 A (1) AC 120 V, 10 A (1) AC 250 V	1

Climate Control Products  
Control Devices



## Breather Kit (Pressure Compensation Plug)



- Packaged individually.
- Provides for controlled pressure compensation due to temperature variations (i.e. night/day operation).
- Recommend two plugs per cabinet in opposite locations.
- Minimum cutout diameter 1.46"

Part No.	Dimensions (Diameter x Depth)	Ship Wt. lbs
SDA412	2.6" x 1.2"	1

Mounting:	PG 29 (1.14") thread with union nut, minimum cutout diameter
Material:	Polycarbonate UL94VO
Protection:	IP45
Color:	RAL 7032 beige