

## Switch - FL SWITCH SFNB 8TX - 2891002

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ethernet switch, 8 TP RJ45 ports, automatic detection of data transmission speed of 10/100 Mbps (RJ45), autocrossing function

### Product Features

- ✓ Multi-mode and single-mode fiberglass connections are available for larger distances
- ✓ Auto negotiation and autocrossing detection simplifies installation and setup
- ✓ Local diagnostic indicators with LEDs
- ✓ Security options with cable locking
- ✓ RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps



### Ethernet

### Key commercial data

Packing unit	1 1
Weight per Piece (excluding packing)	400.0 GRM
Custom tariff number	85176200
Country of origin	Taiwan

### Technical data

#### Dimensions

Width	50 mm
Height	110 mm
Depth	70 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (no condensation)
Permissible humidity (storage/transport)	5 % ... 95 % (no condensation)

# Switch - FL SWITCH SFNB 8TX - 2891002

## Technical data

### Ambient conditions

Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above mean sea level)
Noise immunity	EN 61000-6-2:2005

### Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s

### Function

Basic functions	Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode
Status and diagnostic indicators	LEDs: U <sub>s</sub> , link and activity per port

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length ((twisted pair)	100 m

### Supply voltage

Supply voltage	24 V DC
Residual ripple	3.6 V <sub>pp</sub> (within the permitted voltage range)
Supply voltage range	9 V DC ... 32 V DC
Typical current consumption	140 mA (@24 V DC)
Max. current consumption	380 mA (@9 V DC)

### General

Mounting type	DIN rail
Type AX	Block design
Weight	320 g
Housing material	Aluminum
Noise emission	EN 61000-6-4

## Classifications

### eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	19030117

# Switch - FL SWITCH SFNB 8TX - 2891002

## Classifications

### eCl@ss

eCl@ss 5.1	19030117
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

### UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / cULus Listed

---

#### Ex Approvals

UL Listed / cUL Listed / cULus Listed

---

#### Approvals submitted

---

### Approval details

UL Listed 
-----------------------------------------------------------------------------------------------

## Switch - FL SWITCH SFNB 8TX - 2891002

### Approvals

