

Plastic label - UC-EMLP (11X9) - 0819291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Plastic label, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Adhesive, Lettering field: 11 x 9 mm



Why buy this product

- The UC-EMLP ... UniCard labeling range includes self-adhesive device markers with good adhesive properties
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Self-adhesive with good adhesive properties
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 152433
Weight per Piece (excluding packing)	8.64 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	11 mm
Width (a)	9 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Plastic label - UC-EMLP (11X9) - 0819291

Technical data

General

Number of individual labels	10
Number of individual labels per row	2
RoHS compliant	Yes
Adhesive	Acrylic
Printability	InkJet, CMS
Device	5147777 BLUEMARK X1
	5147999 BLUEMARK CLED
	5147888 BLUEMARK LED
	5144615 CMS-P1-PLOTTER
	1051993 B-STIFT
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Burning behaviour	self-extinguishing
Adhesive strength	250 µm

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

Plastic label - UC-EMLP (11X9) - 0819291

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER, for accommodating UC-EMP..., UC-EMLP...