### TW Series — 22mm NEMA Style Pushbuttons

Oiltight Switches & Pilot Devices







# TW NEMA Style Switches with snap-on contacts

### **Key features include:**

- Corrosion resistant octagonal chrome plated locking bezel
- Snap-on 10A contact blocks
- Transformer or full voltage
- Incandescent or LED illumination
- Slow make, double break, self cleaning contacts
- Modular construction for maximum flexibility
- NEMA 4X and IP65 watertight/oiltight panel
- Available assembled or as sub-components
- Large M3.5 screw terminals with captive sems plate

IDEC has your 22mm switching needs covered.

Button styles include flush, extended, mushroom, or square and all bodies are crafted from fracture-resistant nylon.

All illuminated units feature two lense styles, one that maximizes light dispersion, the other accommodates direct lense engraving.

Self cleaning contact mechanisms allow for a wide current rating, 5mA to 10A, which reduces the need for various contact materials.

When looking for a 22mm switch that is durable, easy to use, and versatile, then IDEC's TW series is your solution.













# IDEC Oiltight Switches & Pilot Devices

DC-13 Control of electromagnets

	Conforming to Standards			EN60947-1, EN60947-5-1, VDE0660-200, UL508, CSA C22-2 No.14									
	Approvals												
	File No. E68961 File No. LR21451 Certificate No. 2030010305027380			CSA: pushbuttons and selector switches: A600 pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V) UL: pushbuttons and selector switches: A600 pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V)									
	TÜV Rheinland Registration No: J9551802 (E-Stops) Registration No: J9551803 (All other switches) Registration No: J9551804 (Pilot Lights)			TÜV: pushbuttons and selector switches: A600=P600 (NO, NC)/Q600 (NO-EM, NC-LB) pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V)									
	Operating Temperature			Operation: -25 to +50°C (without freezing) Storage: -40 to +80°C (without freezing)									
	Vibration Resistance			5 to 55Hz, 100m/sec <sup>2</sup> (10g) conforming to IEC6068-2-6									
	Shock Resistance			1000m/sec <sup>2</sup> (100g)	) conforn	ning to	IEC6068	3-2-7					
	Electric Shock Protection			Class 0 conformin	g to IEC	60536							
	Degree of Protection (conforming to IEC60529) (conforming to NEMA ICS6-110)			IP65 from front of the panel; (IP54 for key switches) IP20 (Type HW-F contact block) NEMA 1, 2, 3, 3R, 3S, 4, 4X, 5, 12, 13 (NEMA 1, 2, 3R, 5, 12, 13 for key switches)									
tions	Mechanical Life			Momentary pushbuttons: 5,000,000 (900 operations per hour) All other switches: 500,000									
ifica	Pollution Degree (conforming to IEC60947-1)			3 for switches not using a transformer 2 for switches using a transformer									
Specifications	Rated Operational Characteristics			AC-15: A600 or Ue = 250V, Ie = 3A (NO, NC, NO-EM, NC-LB) DC-13: P600 or Ue = 125V, Ie = 1.1A (NO, NC) DC-13: Ω600 or Ue = 125V, Ie = 0.9A (NO-EM, NC-LB)									
	Rated Insulation Voltage			600V									
	Rated Switching Over-Voltage			Less than 4kV, conforming to IEC60947-1									
	Rated Impulse Withstanding Voltage			4kV for contact circuit 2.5kV for lamp circuit									
	Rated Thermal Current				10 Amp								
	Minimum Switching Capacity			5 mA at 3V AC/DC									
	Contact Operation			Slow break NC or slow make NO, self-cleaning									
	Recommended Terminal Torque			0.8 N m (7.1 in lb.)									
	External Short-Circuit Protection			10A 250V fuse conforming to IEC60269-1									
	Applicable Wire Size			Minimum 1 x 22 AWG, max. 2 x 14 AWG or 1 x 12 AWG									
	Contact Resistance			Initial contact resistance of $50m\Omega$ or less									
	Contact Gap			4mm (NO and NC) 2mm (NO-EM and NC-LB)									
	Electrical Reliability			MTBF < 1 fault for 10 million operation cycles (3V DC, 5mA)									
	Lamp Ratings			Incandescent: 1 W LEDs: 6V: 17mA max, 12/24V: 11mA max, 120/240V: 10mA max									
	Horsepower Rating			1/4 HP @ 120V (single-phase, non-reversing motor); 1 HP @ 240V (3 phase, non-reversing motor)									
	Maximum Inrush Current			40 A (40 ms)									
	Contact Material			Silver									
ings	Pushbuttons Illuminated Pushbuttons Selector Switches Illuminated Selector Switches  Rated Continuous Curre		Type HW-C/HW-F										
Rat													
act													
Contact Ratings	Pushbutton Selectors Contact Ratings by Utili: IEC 60947-5-1			zation Category AC-15 (A600) DC-13 (P600)									
				Contact Ratings	by Utilization Cat	egory							
	Operational Voltage					24V	48V	50V	110V	220V	440V		
S		AC AC-12 Control of resistive loads 8			solid state loads	10A	_	10A	10A	6A	2A		
risti	Operational Current	50/60 Hz	AC-15 C	Control of electromagnetic	loads (> 72VA)	10A	_	7A	5A	3A	1A		
acte			DC-12 C	Control of resistive loads 8	solid state loads	8A	5A	_	2.2A	1.1A			
haracteristics		DC	DC-13 C	Control of electromagnets		5A	2A		1.1A	0.6A	_		


2A

1.1A 0.6A

# IDEC Oiltight Switches & Pilot Devices

### Pilot Lights (Assembled)







1. Use only when interpreting part numbers. Do not use for developing part numbers.

2. All transformers step down to 6V.

## Oiltight Switches & Pilot Devices



### Pilot Lights (Assembled) con't

### **Part Numbers: Pilot Lights**



Style		<b>Operating Voltage</b>	Part Number		
Round Flat	Transformer	120VAC 240VAC 480VAC	APW1126@-@ APW1246@-@ APW1486@-@		
	Full Voltage	_	APW199 <i>@</i> -@-3		
Dome	Transformer	120VAC 240VAC 480VAC	APW2126@-@ APW2246@-@ APW2486@-@		
	Full Voltage	_	APW299 @-@-@		
Square Flat	Transformer	120VAC 240VAC 480VAC	APQW1B126 <i>⊕</i> -② APQW1B246 <i>⊕</i> -② APQW1B486 <i>⊕</i> -②		
	Full Voltage	_	APQW1B99@-@-3		



- 1. In place of ②, specify the Lens Color Code from table below.
- 2. In place of ③, specify the Full Voltage Code from table below.
- 3. In place of 4, specify the Lamp Type Code from table below.
- 4. For accessories, see page A3-156.
- 5. For dimensions, see page A3-158.
- 6. For sub-assembly part numbers, see next page.

### **2 Lens Color Code**

© Ecilo Color Code				
Code				
A				
G				
R				
S				
W				
Υ				

### **3 Full Voltage Code**

Voltage	Code		
6V AC/DC	6V		
12V AC/DC	12V		
24V AC/DC	24V		
120V AC	120V (LED only)		
240V AC	240V (LED only)		

### **4** Lamp Type Code

Lamp	Code				
Incandescent	Blank				
LED	D				


### 




### Dimensions con't

### **Pilot Lights** Round Flush APW1 Full Voltage







### Round Flush Marking Type APW1B Full Voltage




### Dome APW2 Full Voltage




### Square Flush Marking Type APQW1B Full Voltage




### **Illuminated Selector Switches**




### Round Flush APW1 Transformer



### Round Flush Marking Type APW1B Transformer



### Dome APW2 Transformer



### Square Flush Marking Type APQW1B Transformer

