



**IDEC CORPORATION** 

# High Visibility LED Indicating Towers with Striped Design

# Stylish design

Unique lens shape offers high visibility

## Four different mounting styles

Marking possible on non-illuminating areas

# Flexible arrangement of LED units

#### Colour Arrangement according to IEC Standards

Indicating towers on machines should have the applicable colours in the following order from the top down; RED, YELLOW, BLUE, GREEN, WHITE. (IEC60204-1 Fifth edition Chapter 10.3.2 Colours)

Colours for indicator lights and their meanings with respect to the condition of the machine.


Colour	Meaning	Explanation	Action by operator
RED	Emergency	Harzadous condition	Immediate action to deal with hazardous condition
YELLOW	Abnormal	Abnormal condition Impending critical condition	Monitoring and/or intervention (for example by re-establishing the intended function)
BLUE	Mandatory	Indication of a condition that requires action by the operator	Mandatory action
GREEN	Normal	Normal condition	Optional
WHITE	Neutral	Other conditions; may be used whenever doubt exists about the application of RED, YELLOW, GREEN, BLUE	Monitoring

(IEC 60204-1)

# Stylish design

The ø40×60 oval shape of the SignaLight presents a stylish image. LD6A LED SignaLight is highly visible due to the striped design, making a clear distinction between illuminating and nonilluminating areas.

Unlike conventional products, the nonilluminating area is covered, making a distinction between non-illuminating and illuminating areas. This enables the illuminating area to provide brighter illumination.





**IDEC LD6A** 





(light distribution measured by a beam profiler)

# Unique lens shape offers high visibility

Three different illumination methods and a unique lens shape enable high visibility from different directions.

Characteristics of the lens and light





By combining the diffusing lens, which diffuses the light broadly, with the condensing lens, a super bright area is created enabling high visibility. Also, the illumination through the light guide enhances the visibility when the SignaLight is viewed from below.

# Four different mounting styles

Four different mounting styles are available which enable mounting on aluminum frames, wall mounting, direct mounting, and pole mounting.



(The SignaLight in the above photo is attached to a 40-mm-sq. aluminum frame)

Marking is possible in the non-illuminating areas.



The color arrangement can be changed easily by stacking LED units. The LED units use plug-in terminals which have proven to provide high reliability for IDEC relays. Optional LED units are available for expansion. (The length of the center screw needs to be changed.)



Up to 5 LED units with 5 different illumination colors – red, yellow, blue, green, pure white – can be stacked. Dark gray and light gray housings are available. IP65 protection degree – dustproof and waterproof.











Dark gray

Light gray

#### Oval shape with striped design. Presents a stylish image on all equipment.

- · SignaLight with striped design.
- Non-illuminating area between the lenses makes the illuminating color stand out. Built-in super bright LEDs.
- The lens part uses 3 different illumination methods. IDEC's unique lens shape enables high-visibility from different directions.
- Four different mounting styles available. Easy mounting on aluminum frames, wall mounting, direct mounting, and pole mounting.
- Degree of protection: IP65



#### **Functional Specifications**

Safety Standards	IEC60947-5-1, EN60947-5-1, UL508, CSA C22.2 No.14		
Operating Temperature	-25 to +55°C (no freezing) See Highest Temperature Limitations of page 8.		
Operating Humidity	45 to 85%RH (no condensation)		
Storage Temperature	-40 to +75°C (no freezing)		
Overvoltage Category	III (IEC60664-1)		
Impulse Withstand Voltage	800V (IEC60947-1)		
Insulation Resistance	100 MΩ minimum (500V DC megger)		
Dielectric Strength	Between live and dead parts: 1000V, 1 minute		
Pollution Degree	3		
Corrosion Immunity	Atmosphere free from corrosive gases		
Vibration Resistance	Operating extremes: 10 to 55 Hz, amplitude 0.5 mm		
Shock Resistance	Operating extremes: 147 m/s <sup>2</sup> , 6 shocks each in 6 axes		
Degree of Protection	IP65 (IEC60529)		
Housing Color	Dark gray, light gray		
Material	Housing:ABS resinLens:AS resinPole:Steel (nickel-chrome plated)Pole stand:Diecast aluminum		
Cable	UL1007 AWG22		

#### **Supplied Parts**

Mounting Style	Supplied Parts
Frame mount	M4 screw (4 pcs)*, M4 spring washer (4 pcs)*, M4 plain washer (4 pcs)*, M5 screw (2 pcs), M5 spring washer (2 pcs), M5 plain washer (2 pcs), bracket (1 pc)
Wall mount	M4 screw (I=20) (4 pcs), M4 screw (I=8) (4 pcs)*, M4 spring washer (8 pcs)*, M4 plain washer (8 pcs)*, M4 nut (4 pcs), bracket (1 pc), gasket (1 pc)
Direct mount	M5 screw (4 pcs)*, M5 spring washer (4 pcs)*, M5 plain washer (4 pcs)*, M5 nut (4 pcs)*, O-ring (4 pcs), gasket (1 pc)
Pole mount	M5 screw (4 pcs), M5 spring washer (4 pcs), M5 plain washer (4 pcs), M5 nut (4 pcs), O-ring (4 pcs), gasket (1 pc)

\* For dark gray housing, black parts are supplied. For light gray housing, silver parts are supplied.



#### **Specifications**

Rated Insulation Voltage	60V		
Operating Voltage	24V AC/DC :	±10%	
Rated Voltage	24V AC/DC		
LED Color Code	R (red), Y (yellow), S (blue), G (green), W (pure white)		
Rated Current	R, Y	S, G	W
(per tier)	25 mA	30 mA	20 mA
Power Consumption	R, Y	S, G	W
(per tier)	0.6W	0.75W	0.5W
LED Life (Note)	Approx. 30,000 hours (until the brightness reduces to 50% the initial value when lit at complete direct current of the rated voltage under 25°C environment.)		

Note: Life of the LED differs according to operating conditions and environment.

#### **External Contact Ratings**

¥				
Contact Capacity	Current Capacity	100 mA minimum		
(per tier)	Dielectric Strength	35V AC minimum		
<b>T</b> O	Current Capacity	100 mA minimum		
Transistor Capacity (per tier)	Dielectric Strength	35V minimum		
	Leakage Current	0.1 mA maximum		

#### **LED/Lens Color Code**

LED Color	Standard Type	Clear Lens Type
R: Red	Red lens	Transparent lens
Y: Yellow	Yellow lens	Transparent lens
S: Blue	Blue lens	Transparent lens
G: Green	Green lens	Transparent lens
W: Pure white	Transparent lens	

For pure white (W) LED, the lens color for standard and clear lens type is transparent.

#### Type No. Development

LD6A - 5 G Q B - RYSGW C					
Number of tiers 1: 1 tier 2: 2 tiers 3: 3 tiers 4: 4 tiers 5: 5 tiers		<ul> <li>Lens color</li> <li>blank: same as LED color (standard type)</li> <li>C: transparent (clear lens type)</li> <li>LED color code</li> </ul>			
Mounting style G: frame mount W: wall mount D: direct mount P: pole mount	Housing color B: dark gray W: light gray Voltage Q: 24V AC/DC	(specify code from highest tier) R: red Y: yellow S: blue G: green W:pure white			



#### Types

Package Quantity: 1

Mounting Style Tiers Type No. (Ordering Type No.) LED Color Code Weigh					<u> </u>
Mounting Style	Tiers	Dark Gray Housing			Weight (approx.)
	1	LD6A-1GQB-	LD6A-1GQW-	R, Y, S, G, W	180g
	2	LD6A-2GQB-	LD6A-2GQW-	RY, RG	220g
Frame Mount	3	LD6A-3GQB-	LD6A-3GQW-	RYS, RYG	260g
	4	LD6A-4GQB-	LD6A-4GQW-	RYSG	300g
	5	LD6A-5GQB-	LD6A-5GQW-	RYSGW	340g
	1	LD6A-1WQB-	LD6A-1WQW-	R, Y, S, G, W	180g
	2	LD6A-2WQB-	LD6A-2WQW-	RY, RG	220g
Wall Mount	3	LD6A-3WQB-	LD6A-3WQW-	RYS, RYG	260g
	4	LD6A-4WQB-	LD6A-4WQW-	RYSG	300g
	5	LD6A-5WQB-	LD6A-5WQW-	RYSGW	340g
	1	LD6A-1DQB-	LD6A-1DQW-	R, Y, S, G, W	150g
	2	LD6A-2DQB-	LD6A-2DQW-	RY, RG	190g
Direct Mount	3	LD6A-3DQB-	LD6A-3DQW-	RYS, RYG	230g
	4	LD6A-4DQB-	LD6A-4DQW-	RYSG	270g
	5	LD6A-5DQB-	LD6A-5DQW-	RYSGW	310g
	1	LD6A-1PQB-	LD6A-1PQW-	R, Y, S, G, W	635g
	2	LD6A-2PQB-	LD6A-2PQW-	RY, RG	675g
Pole Mount	3	LD6A-3PQB-	LD6A-3PQW-	RYS, RYG	715g
	4	LD6A-4PQB-	LD6A-4PQW-	RYSG	755g
	5	LD6A-5PQB-	LD6A-5PQW-	RYSGW	795g

• Select the illumination color from the top tier specifying the LED color code from the left. □: R (red), Y (yellow), S (blue), G (green), W (pure white)

#### **Ordering Non-Standard Products**

•Order according to the table above. Specify the illumination color from the top tier.

Example: When the LED color is <u>RYGSW</u> => LD6A-5GQW-RYGSW

•Clear lens type also available. Specify "C" after the LED color code. Example: LD6A-5GQW-RYSGW => LD6A-5GQW-RYSGWC

#### Accessories

Accessories Package Quantity				
	Name/Appearance	Type No. (Ordering Type No.)	LED Color Code	
LED Unit		LD9Z-6ALB-	R, Y, S, G, W	
	For dark gray housing	LD9Z-6ALB-□C	R, Y, S, G	
	For light grow housing	LD9Z-6ALW-	R, Y, S, G, W	
	For light gray housing	LD9Z-6ALW-□C	R, Y, S, G	

• Specify an LED color code in place of  $\Box$ . R (red), Y (yellow), S (blue), G (green), W (pure white)

• When using pure white (W) with a clear lens, order LD9Z-6ALB-W (dark gray housing) or LD9Z-6ALW (light gray housing).


Package Quantity: 1

Name/Appe	arance	Type No. (Ordering Type No.)	Remarks
Center Screw Set 1 tier		LD9Z-6AC1	A plain washer and a spring washer are supplied.
6	2 tiers	LD9Z-6AC2	
	3 tiers	LD9Z-6AC3	
00	4 tiers	LD9Z-6AC4	
	5 tiers	LD9Z-6AC5	


Pole Mount

### **Dimensions**

Frame Mount




Cable size: UL1007 AWG22




Wall Mount Type

Ч




Direct Mount



Dimension Table (Dimensions in mn				
Tiers	Frame Mount (L1)	Wall Mount (L2)	Direct mount (L3)	Pole Mount (L4)
1	156	156	98	408
2	186	186	128	438
3	216	216	158	468
4	246	246	188	498
5	276	276	218	528


#### **Panel Cut-Out**




\*Complies with IEC60947-5-1.

## Wiring Examples


#### Mechanical Contacts



#### NPN Transistors



#### PNP Transistors





#### **Safety Precautions**


- Turn off the power to the LD6A series before mounting, dismounting, wiring, and assembling the LED unit. Make sure of correct wiring, otherwise electrical shocks or fire may result.
- Mount LD6A on a solid surface not subjected to vibrations.
- Do not mount the LD6A upside-down or horizontally.

#### Instructions

#### Mounting

#### Frame Mounting

- Insert two nuts in the frame, and attach the bracket using two M5 screws. Recommended tightening torque: 2.6 to 2.7 N·m
- 2. Mount the LD6A to the bracket using four M4 screws.
  - Recommended tightening torque: 1.6 to 1.7 N·m




- Note: See table below for typical examples of frames and nuts. Consult the manufacturer of the frame for the installation method of the frame nut.
- Examples of recommended frames and frame nuts

Frame Size	Frame	Frame Nut	Manufac- turer
□30 mm (Note)	SFF-302	SFB-001 SFB-4B5 SFB-101	SUS
□40 mm	SFF-402	SFB-008 SFB-4A5 SFB-108	Corporation

Note: The mounting bracket for the housing is 40 mm.

When using a frame mount type, be sure to use flexible conduit, otherwise the waterproof characteristic is impaired. Refer to the "Example of Flexible Conduit" shown on the right.



- Do not leave the LD6A without a cap or unassembled.
- Install the supplied gasket, otherwise waterproof characteristics is impaired.
- Do not apply any chemicals which may corrode the plastic material.
   If the LDCA is subjected to strong without
- If the LD6A is subjected to strong vibrations, the hexagon socket screw may become loose. Take measures to prevent loosening. (See the figure on the right.)

M20

AL16/M20/A/BL

PAFS16BL

Adaptaflex

Example of Flexible Conduit

Conduit Port Size

Gland

Conduit

Manufacturer



• Do not loosen the screw for which the tightening torque is not specified.

#### Wiring

- Connect the wiring as shown below. Incorrect wiring may damage the internal circuit.
- ·Be sure to insulate unused wires.
- Connect an appropriate fuse to the power line as shown in the figure on page 7.
- Use a fuse with 1A rated current
- · Use a UL listed external fuse holder.
- Use a class 2 power supply only.
- When using the same color for two or more tiers, only one wire is used to light all tiers of the same color. Determine the contact capacity in consideration of the LED rated current.

#### Wire Color

LED Color	Wire Color
LED Unit-Red	Red
LED Unit-Yellow	Orange
LED Unit-Blue	Blue
LED Unit-Green	Green
LED Unit-Pure White	White
Power Line	Yellow

#### Highest Temperature Limitations

The highest temperature is limited to 50°C when all tiers are lit continuously in the following combinations:

- 1. Two or more tiers including blue and green (example: Red-Green-Blue, Green-Green-Red)
- 2. Four or five tiers (example: Red-Yellow-Green-Pure White, Red-Yellow-Blue-Green-Pure White)

Specifications and other descriptions in this catalog are subject to change without notice.



#### IDEC CORPORATION

 IDEC CORPORATION (USA)

 Tel: +1-408-747-0550 / (800) 262-IDEC (4332)

 Fax: +1-408-744-9055 / (800) 635-6246

 E-mail: opencontact@idec.com

 IDEC CANADA LIMITED

 Tel: +1-905-890-8561, Toll Free: (888) 317-4332

 Fax: +1-905-890-8562

 E-mail: sales@ca.idec.com

 IDEC AUSTRALIA PTY. LTD.

 Tel: +1-397-63-3255

 E-mail: sales@au.idec.com


IDEC ELECTRONICS LIMITED Tel: +44-1256-321000, Fax: +44-1256-327755 E-mail: sales@uk.idec.com IDEC ELEKTROTECHNIK GmbH Tel: +49-40-25 30 54 - 0, Fax: +49-40-25 30 54 - 24 E-mail: service@idec.de IDEC (SHANGHAI) CORPORATION Tel: +86-21-5353-1000, Fax: +86-21-5353-1263 E-mail: idec@cn.idec.com IDEC (BEIJING) CORPORATION Tel: +86-10-6581-5119 IDEC (SHENZHEN) CORPORATION

+86-755-8356-2977, Fax: +86-755-8356-29

IDEC IZUMI (H.K.) CO., LTD. Tel: +852-2803-8989, Fax: +852-2565-0171 E-mail: info@hk.idec.com IDEC TAIWAN CORPORATION Tel: +886-2-2698-3929, Fax: +886-2-2698-3931 E-mail: service@twidec.com IDEC IZUMI ASIA PTE. LTD. Tel: +86-6746-1155, Fax: +65-6844-5995 E-mail: info@sg.idec.com


 Wall Mounting
 Make four tapped holes in the mounting panel and mount the bracket and gasket using four screws (M4 x 20).

- Recommended tightening torque: 1.6 to 1.7 N·m 2. Mount the LD6A to the bracket using four screws (M4 x 8).
- Recommended tightening torque: 1.6 to 1.7 N·m




#### Direct Mounting

• Recommended tightening torque: 2.6 to 2.7 N·m



#### **Pole Mounting**

The pole mount type can be installed in four ways. The recommended mounting method (pattern 4) is described below. Recommended tightening torque: 2.6 to 2.7 N·m (M5 screw)



7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan Tel: +81-6-6398-2571, Fax: +81-6-6392-9731 E-mail: marketing@idec.co.jp