# IDEC

Think Automation and beyond...



IDEC Surface Mount LED Spider Lights





Good Visibility
From the front and the side.



IP67 Protection
Can be used in
environments
exposed to
water.




Cable Wiring
Direct wiring
ensures
waterproof
characteristics.



**Direct Surface Mounting** 

Requires only a small space behind the mounting surface. Can be installed without concern for other components behind mounting area.





# Red/Green

Two-color alternate illumination available.



### Seven Colors

Amber, blue, green, cool white, red, warm white, & yellow.



#### Legends

Marking film can be inserted into the flat type lens.



#### Slim Profile

Can be installed in small areas easily.

# LH Series Surface Mount Indicators

# Innovative indicators in a slim & stylish design. Reduces installation space.

- Direct mounting on surfaces such as panels, aluminum frames, and walls using screws.
- Surface mount style does not affect the placement of other components. Requires only a small space behind the mounting surface for screws and nuts.
- · Slim design well suited for installation in small spaces.
- Direct cable wiring style ensures waterproof characteristics.
   1m, 3m, and 5m cables available.
- IP67 (IEC60529) rated.
- Excellent visibility from the front and from the side.
- Legends and symbols can be printed on marking film to customize flat type.
- · Red/Green two-color alternate illumination available.



Standards	Marks	File No. or Organization
EN 60598-2-1	TUV	TÜV SÜD
EN 60598-2-1 EN 60947-5-1	(€	EC Low Voltage Directive
E68961	c (UL) us	UL, cUL

LH series surface mount indicators are approved by TÜV as class III lighting fixtures.

#### **Specifications**

Rated Insulation Voltage (Ui)	32V
Rated Voltage	24V AC/DC
Operating Voltage Range	24V AC/DC ±10%
Rated Current	17 mA
Maximum Current Draw	0.6W (25 mA)
Illumination Color	A (amber), G (green), PW (cool white), R (red), S (blue), W (warm white), Y (yellow) R (red) /G (green) alternate
LED Lamp Life	Approx. 50,000 hours (When used on complete DC at 25°C, brightness reduces to 50% of the initial intensity.)



www.IDEC.com/usa/SpiderLights



#### **Specifications**


opeomediene.			
Applicable Standards	IEC 60947-1, IEC 60947-5-1, EN 60598-2-1, EN 60947-5-1 UL508, CSA C22.2 No.14		
Operating Temperature	-20 to +55°C (no freezing)		
Operating Humidity	45 to 85% RH (no condensation)		
Storage Temperature	-30 to +80°C (no freezing)		
Impulse Withstand Voltage (illuminating part)	800V		
Insulation Resistance	Between live and dead parts: 100 $M\Omega$ minimum		
Dielectric Strength	Between live and dead parts: 2000V, 50/60Hz , 1 minute		
Pollution Degree	3		
Vibration Resistance	60m/s <sup>2</sup> , 5 to 55 Hz, amplitude 0.5 mm		
Shock Resistance	1000m/s <sup>2</sup>		
Cable Tensile Strength	90N minimum		
Degree of Protection	IP67 (IEC 60529)		
Housing Color	Black		
Cable	UL20276, 24 AWG 2-core (one-color) 3-core (2-color alternate)		
Cable Outside Diameter	ø4.1mm		
Allowable Cable Bending Radius	24.6mm minimum		
Weight	50g (1m cable)		

## **Dome Type**


#### **Part Numbers**

Shape	Cable	Part No.	② Illumination Color	
Dome ø37 One Color	1m	LH1D-D2HQ4C10-©	Specify a color code in place of <sup>②</sup> in the Part No. A: amber	
	3m	LH1D-D2HQ4C30-©	G: green PW: cool white R: red S: blue W: warm white Y: yellow	
	5m	LH1D-D2HQ4C50-©		
Dome ø37 Red/Green 2-color alternate	1m	LH1D-D2HQ4C10-RG		
	3m	LH1D-D2HQ4C30-RG	R (red) / G (green) 2-color alternate illumination	
	5m	LH1D-D2HQ4C50-RG		


#### **Dimensions**



#### · One-color Illumination




#### · Two-color Alternate Illumination



#### **Lens Colors**


Illumination Type	Illumination Color	Lens Color	
	Amber	Amber	
One Color	Blue	Blue	
	Green	Green	
	Cool White	Clear (Note)	
	Red	Red	
	Warm White	Clear (Note)	
	Yellow	Yellow	
Two-color Alternate	e Red/Green Clear (f		




Note: Because lenses have a white diffusion cover inside, cool white, warm white, and red/green types look white when the light is off.


## **Flat Type**

Shape	Cable	Part Number	② Illumination Color
Flat One Color Full	1m	LH1D-H2HQ4C10-@	Specify a color code in place of <sup>②</sup> in the Part No.  A: amber
	3m	LH1D-H2HQ4C30-©	G: green PW: cool white R: red
	5m	LH1D-H2HQ4C50-@	S: blue W: warm white Y: yellow
Flat Red/Green 2-color Alternate	1m	LH1D-H2HQ4C10-RG	
	3m	LH1D-H2HQ4C30-RG	R (red) / G (green) 2-color alternate illumination
	5m	LH1D-H2HQ4C50-RG	






#### Two-color Alternate Illumination



#### **Lens Colors**

Lens Colors			
ion Tyna	nation lor	Lens Color	
А	ber	Amber	
	ıe eı	Blue	
G	en	Green	
Color Cod	Nhite	Clear	
	ed	Red	
War	White	Clear	
Y	ow	Yellow	
Alternate Red	Red/Green Clear		
-			



800-262-IDEC

www.IDEC.com/usa/SpiderLights


#### **Replacement Parts**

Shape	Material	Part Number	② Lens Color
Lens (flat type)	Polyarylate	LH9Z-1DLH2-©	For flat type.  Specify a color code in place of ② in the Part No.  A: amber G: green C: clear R: red S: blue Y: yellow  Note: Use C (clear) lens for R/G (red/green alternate), W (warm white), or PW (cool white) illumination.


#### Instructions

#### **Panel Mounting**

Using two M3 screws, install the LH indicator to a mounting surface. Tighten the screws to a torque of 0.6 N·m maximum. Mounting screws are not provided and must be supplied by the user.



Note: The dome lens is not removable. Do not attempt to remove the lens, otherwise damage will occur.




Note 1: Do not install the LH indicator by attaching the lens only, such as by taping down on the lens as the internal components may come loose.


Note 2: Make sure that the back of the indicator is securely attached to the mounting surface so that the lens cannot be easily removed.

#### **Inserting Marking Film into Flat Type Lens**


1. Insert a flat screwdriver into the groove between the base and lens.




2. Twist the screwdriver and disengage the lens from the base.




3. Remove the lens from the base.



 Insert the edge of a marking film into the gap between the base and the diffusion plate, and place the marking film on top of the diffusion plate.



5. Replace the lens. Ensure that the lens is installed snugly.



Note 1: Do not touch the gasket, as this may affect its waterproof characteristics.


Note 2: Do not touch the diffusion plate.

#### Markings

Legends and symbols can be printed on marking film that can be used with the flat lens. One 0.1mm-thick film can be inserted.

Marking films are not inlcuded and must be supplied by the user.

Recommended marking film: Polyester



#### **Applications**

**Conventional Indicators** 






**IDEC LED Spider** 









**Picking Application** 



**Door Monitoring** 



**Robotic Arm** 







www.IDEC.com/usa/SpiderLights

#### www.idec.com

USA IDEC Corporation Tel: (408) 747-0550 opencontact@IDEC.com

Canada IDEC Canada Ltd. Tel: (905) 890-8561 sales@ca.IDEC.com

Australia IDEC Australia Pty. Ltd. Tel: +61-3-9763-3244 sales@au.IDEC.com Japan IDEC Corporation Tel: +81-6-6398-2571

products@IDEC.co.jp

United Kingdom IDEC Electronics Ltd. Tel: +44-1256-321000 IDEC@uk.IDEC.com Germany
IDEC Elektrotechnik GmbH
Tel: +49-40-253054-0
service@IDEC.de

Hong Kong IDEC (H.K.) Co., Ltd. Tel: +852-2803-8989 info@hk.IDEC.com China/Beijing IDEC (Beijing) Corporation Tel: +86-10-6581-6131

idec@cn.IDEC.com

idec@cn.IDEC.com

China/Shanghai IDEC (Shanghai) Corporation Tel: +86-21-5353-1000 **China/Shenzhen IDEC (Shenzhen) Corporation**Tel: +86-755-8356-2977

Singapore IDEC Asia Pte. Ltd. Tel: +65-6746-1155 info@sg.IDEC.com

Taiwan
IDEC Taiwan Corporation
Tel: +886-2-2698-3929
service@tw.IDEC.com

©2009 IDEC Corporation. All Rights Reserved. Catalog No. LH9Y-B100-0 5/09 15K