

Marker for terminal blocks - UC-TM 5 - 0818108

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: Bluemark, Plotter, BLUEMARK CLED, Mounting type: Snap into tall marker groove, For terminal block width: 5.2 mm, Lettering field: 10.5 x 4.6 mm



Why buy this product

- The UC-TM ... UniCard labeling range includes markers for products with tall marker grooves
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The sheets provide space for including function texts
- The markers support multi-line labeling
- The format automatically ensures printing with a high degree of positioning accuracy

Key commercial data

| | |
|------------------------|---|
| Packing unit | 0 |
| Minimum order quantity | 10 |
| Catalog page | Page 51 (CL2-2011) |
| GTIN |  4 046356 133982 |
| Custom tariff number | 39269097 |
| Country of origin | POLAND |

Technical data

General

| | |
|---|--------------------------------|
| Note | Can be labeled with CMS |
| Width (a) | 5 mm |
| Color | white |
| Inflammability class according to UL 94 | V2 |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Components | free from silicone and halogen |
| Material | PA |
| Number of individual labels | 96 |
| Number of individual labels per row | 12 |

Marker for terminal blocks - UC-TM 5 - 0818108

Classifications

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |