

## Antenna cable - RAD-CAB-LMR400-20 - 5606125

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, 20 ft. in length, type N (male) to type N (male), 50  $\Omega$  impedance



### Product description

Antenna cable, 20 ft. in length, type N (male) to type N (male), 50  $\Omega$  impedance

### Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	719.2 GRM
Custom tariff number	85442000
Country of origin	China

### Technical data

#### Dimensions

Fixed cable length	6 m
--------------------	-----

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

#### General

Connection 1	Connector connection
Connection method	Type N (male)
Note	Both sides
Cable type	LMR-400
Frequency range	400 MHz ... 5.8 GHz

#### Attenuation

868 / 900 MHz	0.98 dB
2.4 GHz	1.54 dB
5 GHz	2.24 dB

## Antenna cable - RAD-CAB-LMR400-20 - 5606125

### Classifications

#### eCl@ss

eCl@ss 4.0	27060805
eCl@ss 4.1	27060805
eCl@ss 5.0	27061805
eCl@ss 5.1	27061805
eCl@ss 6.0	27061805
eCl@ss 7.0	27061805
eCl@ss 8.0	27061805

#### ETIM

ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC001682

#### UNSPSC

UNSPSC 6.01	26121608
UNSPSC 7.0901	26121608
UNSPSC 11	26121608
UNSPSC 12.01	26121608
UNSPSC 13.2	26121608