

D2SW



Sealed Subminiature Basic Switch

- High quality, watertight switch meets IP67 (IEC 529) requirements (lead wire types) and IP50 (terminal types)
- Monoblock construction assures high sealing capability and is ideal for applications where water spray or dust is prevalent
- Perfect for automotive, vending, factory machines, etc. which require environmentally resistive capabilities
- Wide operating temperature range of -40°C to 85° C
- ROHS Compliant

Part	Rated Resistive Load - Switch	Actuator types	Contact form	Operating Force	Seal type	Termination Style	Service Life - Electrical (Min. @ Rated Loads)
D2SW-01DS	0.1A @ 125VAC/0.1A @ 30VDC	Pin plunger	SPDT	180g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-01HS	0.1A @ 125VAC/0.1A @ 30VDC	Pin plunger	SPDT	180g	IP67	Solder	200,000 ops
D2SW-01MS	0.1A @ 125VAC/0.1A @ 30VDC	Pin plunger	SPDT	180g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-01TS	0.1A @ 125VAC/0.1A @ 30VDC	Pin plunger	SPDT	180g	IP67	110 Quick Connect	200,000 ops
D2SW-01L1DS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge lever	SPDT	60g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-01L1HS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge lever	SPDT	60g	IP67	Solder	200,000 ops
D2SW-01L1MS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-01L1TS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops
D2SW-01L2DS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-01L2HS	0.1A @ 125VAC/0.1A	Hinge roller	SPDT	60g	IP67	Solder	200,000 ops

	@ 30VDC	lever					
D2SW-01L2MS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-01L2TS	0.1A @ 125VAC/0.1A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops
D2SW-01L3DS	0.1A @ 125VAC/0.1A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-01L3HS	0.1A @ 125VAC/0.1A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Solder	200,000 ops
D2SW-01L3MS	0.1A @ 125VAC/0.1A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-01L3TS	0.1A @ 125VAC/0.1A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops

Part	Rated Resistive Load - Switch	Actuator types	Contact form	Operating Force	Seal type	Termination Style	Service Life - Electrical (Min. @ Rated Loads)
D2SW-3DS	3A @ 125VAC/3A @ 30VDC	Pin plunger	SPDT	180g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-3HS	3A @ 125VAC/3A @ 30VDC	Pin plunger	SPDT	180g	IP67	Solder	200,000 ops
D2SW-3MS	3A @ 125VAC/3A @ 30VDC	Pin plunger	SPDT	180g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-3TS	3A @ 125VAC/3A @ 30VDC	Pin plunger	SPDT	180g	IP67	110 Quick Connect	200,000 ops
D2SW-3L1DS	3A @ 125VAC/3A @ 30VDC	Hinge lever	SPDT	60g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-3L1HS	3A @ 125VAC/3A @ 30VDC	Hinge lever	SPDT	60g	IP67	Solder	200,000 ops
D2SW-3L1MS	3A @ 125VAC/3A @ 30VDC	Hinge lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-3L1TS	3A @ 125VAC/3A @ 30VDC	Hinge lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops
D2SW-3L2DS	3A @ 125VAC/3A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	Through-Hole PCB - Straight	200,000 ops
D2SW-3L2HS	3A @ 125VAC/3A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	Solder	200,000 ops

D2SW-3L2MS	3A @ 125VAC/3A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-3L2TS	3A @ 125VAC/3A @ 30VDC	Hinge roller lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops
D2SW-3L3DS	3A @ 125VAC/3A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Through- Hole PCB - Straight	200,000 ops
D2SW-3L3HS	3A @ 125VAC/3A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Solder	200,000 ops
D2SW-3L3MS	3A @ 125VAC/3A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	Lead Wires - Bottom exit	200,000 ops
D2SW-3L3TS	3A @ 125VAC/3A @ 30VDC	Simulated roller lever	SPDT	60g	IP67	110 Quick Connect	200,000 ops





Snap Action Switch D2SW

Watertight Miniature Snap Action Switch

- High-quality watertight miniature snap action switch — meets IP67 (IEC 529) requirements (for lead wire types) and IP50 (for terminal types)
- Monoblock construction assures high sealing capability and is ideal for dusty places or where water is sprayed
- Wide operating temperature range of -40°C to 85°C
- Perfect for the automobile, agriculture machinery, automatic vending machine, refrigerator, ice-manufacturing, bath equipment, hot-water supply, air conditioner, and factory machine industries, which require highly environment-resistant capabilities
- RoHS Compliant



Ordering Information

Actuator	Terminal	Model	
		Model 3 A	Model 0.1 A
Pin plunger 	Solder terminals	D2SW-3HS	D2SW-01HS
	Tab terminals (#110)	D2SW-3TS	D2SW-01TS
	PCB terminals	D2SW-3DS	D2SW-01DS
	With lead wires	D2SW-3MS	D2SW-01MS
Hinge lever 	Solder terminals	D2SW-3L1HS	D2SW-01L1HS
	Tab terminals (#110)	D2SW-3L1TS	D2SW-01L1TS
	PCB terminals	D2SW-3L1DS	D2SW-01L1DS
	With lead wires	D2SW-3L1MS	D2SW-01L1MS
Simulated roller lever 	Solder terminals	D2SW-3L3HS	D2SW-01L3HS
	Tab terminals (#110)	D2SW-3L3TS	D2SW-01L3TS
	PCB terminals	D2SW-3L3DS	D2SW-01L3DS
	With lead wires	D2SW-3L3MS	D2SW-01L3MS
Hinge roller lever 	Solder terminals	D2SW-3L2HS	D2SW-01L2HS
	Tab terminals (#110)	D2SW-3L2TS	D2SW-01L2TS
	PCB terminals	D2SW-3L2DS	D2SW-01L2DS
	With lead wires	D2SW-3L2MS	D2SW-01L2MS

Note: 1. The standard lengths of the lead wires (AWG22) of models incorporating them are 30 cm (12 in).

Specifications

■ Characteristics

		D2SW-3	D2SW-01
Operating speed (see note 2)		0.1 mm to 1 m/second (at pin plunger)	
Operating frequency	Mechanical	300 operations/min.	
	Electrical	60 operations/min.	
Insulation resistance		100 MΩ min. (at 500 VDC)	
Contact resistance		50 mΩ max. (initial value)	
Dielectric strength		1,000 VAC, 50/60 Hz for 1 min. between contacts of the same polarity	600 VAC, 50/60 Hz for 1 min. between contacts of the same polarity
		1,500 VAC, 50/60 Hz for 1 min. between current-carrying metal parts and ground, and between each terminal and noncurrent-carrying metal part	
Inrush current	NO	10 A	—
	NC	20 A	—
Vibration resistance	Malfunction	10 to 55 Hz, 1.5 mm double amplitude	
Shock resistance	Malfunction	300 m/s ² (approx. 30 g)	
Life expectancy	Mechanical	5,000,000 operations min.	
	Electrical	200,000 operations min. (3 A at 125 VAC) 100,000 operations min. (2 A at 250 VAC)	200,000 operations min.
Ambient temperature	Operating	-40° to 85°C (with no icing)	
Ambient humidity	Operating	95% max.	
Enclosure rating		Reference to IP67 IEC 529 (lead wire type) and IP50 (terminal type)	
Weight	Terminal model	2 g	
	Lead wire model	10 g	

Note: 1. Data shown are of initial value.

2. The operating speed value shown is for pin plunger models. For hinge lever models, contact OMRON.

■ Operating Characteristics

Characteristics	Part number				
	Terminal model				Lead wire model
	D2SW-3□S D2SW-01□S	D2SW-3L1□S D2SW-01L1□S	D2SW-3L3□S D2SW-01L3□S	D2SW-3L2□S D2SW-01L2□S	D2SW-3MS D2SW-01MS
OF max.	180 g	60 g	60 g	60 g	180 g
RF min.	30 g	6 g	6 g	6 g	30 g
PT max.	0.6 mm	—	—	—	0.6 mm
OT min.	0.5 mm	1.0 mm	1.0 mm	1.0 mm	0.5 mm
MD max.	0.1 mm	0.8 mm	0.8 mm	0.8 mm	0.1 mm
FP max.	—	13.6 mm	15.5 mm	19.3 mm	—
OP	8.4±0.3 mm	8.8±0.8 mm	10.7±0.8 mm	14.5±0.8 mm	8.4±0.3 mm

■ Ratings

D2SW-3

Rated Voltage	Non-inductive load (A)				Inductive load			
	Resistive load		Lamp load		Inductive load		Motor load	
	NC	NO	NC	NO	NC	NO	NC	NO
125 VAC	3 A		1 A	0.5 A	1 A	0.5 A	1 A	0.5 A
250 VAC	2 A		0.5 A	0.3 A	0.5 A	0.3 A	0.5 A	0.3 A
30 VDC	3 A		1 A		1 A		1 A	




D2SW-01

Rated Voltage	Non-inductive load				Inductive load			
	Resistive load		Lamp load		Inductive load		Motor load	
	NC	NO	NC	NO	NC	NO	NC	NO
125 VAC	0.1 A		—		—		—	
30 VDC	0.1 A		—		—		—	

- Note:**
1. The above current ratings are the values of the steady-state current.
 2. Inductive load has a power factor of 0.7 min. (AC) and a time constant of 7 ms max. (DC).
 3. Lamp load has an inrush current of 10 times the steady-state current.
 4. Motor load has an inrush current of 6 times the steady-state current.

■ Contact Form

* Indicates lead wire color



■ Approvals



UL (File No. E41515), CSA (File No. LR21642-388), EN 61058-1

Dimensions

Unit: mm (inch)



Pin Plunger

D2SW-3□S
D2SW-01□S





Hinge Lever

D2SW-3L1□S
D2SW-01L1□S





Simulated Roller Lever

D2SW-3L3□S
D2SW-01L3□S



Hinge Roller Lever

D2SW-3L2□S
D2SW-01L2□S





Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

2. The above illustrations and dimensions are for models with solder terminals. Refer to "Terminals" for models with tab (#110) and PCB terminals. The dimensions not described are the same as those of models with pin plungers.

Pin Plunger


Lead Wires




- Note:** 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.
 2. The above illustrations and dimensions are for models with pin plungers. The dimensions and operating characteristics of the actuators of models incorporating them are the same as those of the actuators of models with both actuators and terminals.

Terminals


Solder Terminals




Tab Terminals (#110)



PCB Terminals



PCB Mounting




- Note:** Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Precautions

■ Mounting

Use two M2.3 mounting screws with spring washers to mount the switch. Tighten the screws to a torque of 0.23 to 0.26 N • m (2.3 to 2.7 kgf • cm)

Mounting holes



When soldering a lead wire to a terminal of the D2SW, use a soldering iron with a maximum capacity of 60 W and do not take more than 5 seconds to solder the lead wire, otherwise the characteristics of the D2SW may be altered.

Make sure that there is no icing when using the D2SW at low ambient temperatures.

■ Operations

Make sure that the switching object is perfectly separated from the actuator when the switch is not operated and the actuator is pressed appropriately by the switching object when the switch is operated.

The switch should be set so that its stroke will be within the rated OT when the switch is operated.


Install the switching object so that its moving direction is the same as that of the actuator.

Handle D2SW models with pin plungers with care so that the sealing rubber parts around the pin plungers will not be damaged.

■ Enclosure Ratings

The D2SW was tested under water and passed the following watertightness test, which however, does not mean that the D2SW can be used in the water. JIS C0929 (rules for testing the watertightness of electrical devices and materials), class 7 (watertightness test). Refer to the following illustration for the test method.

IEC Publication 529, class IP67. Refer to the following illustration for the test method.



Note: The object to be tested is left in the water for 30 minutes on condition that the distance between the surface of the water and the top of the object be 15 cm minimum, and the distance between the surface of the water and the bottom of the object be 1 m minimum.