MOS FET Relays G3VM-21GR1

MOS FET Relay with Low Output Capacitance and ON Resistance ($C \times R = 5pF \cdot \Omega$) in a 20-V Load Voltage, SOP Package.

- ON resistance of 1 Ω (typical) suppresses output signal attenuation.
- Leakage current of 1.0 nA max. (0.2 nA typ.) when relay is open.
- · RoHS Compliant.

■ Application Examples

- Semiconductor inspection tools
- Measurement devices
- Broadband systems
- Data loggers



Note: The actual product is marked differently from the image shown

■ List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
SPST-NO	Surface-mounting	20 VAC	G3VM-21GR1	100	
terminals			G3VM-21GR1(TR)		2,500


■ Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-21GR1




Note: The actual product is marked differently $_{0.4\pm0.}$ from the image shown here.



Weight: 0.1 g


■ Terminal Arrangement/Internal Connections (Top View)

G3VM-21GR1



■ Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-21GR1



■ Absolute Maximum Ratings (Ta = 25°C)

Item		Symbol	Rating	Unit	Measurement conditions
Input	LED forward current	I _F	50	mA	
Repetitive peak LED forward current		I _{FP}	1	Α	100 μs pulses, 100 pps
	LED forward current reduction rate	Δ I _F /°C	-0.5	mA/°C	$T_a \ge 25^{\circ}C$
	LED reverse voltage	V_R	5	٧	
	Connection temperature	T _j	125	°C	
Output	Load voltage (AC peak/DC)	V_{OFF}	20	٧	
	Continuous load current	I _o	300	mA	
	ON current reduction rate	Δ I _{ON} /°C	-3.0	mA/°C	$T_a \ge 25^{\circ}C$
	Connection temperature	T _j	125	°C	
Dielectric strength between input and output (See note 1.)		V _{I-O}	1,500	V_{rms}	AC for 1 min
Operating temperature		T _a	-20 to +85	°C	With no icing or condensation
Storage temperature		T_{stg}	-55 to +125	°C	With no icing or condensation
Soldering temperature (10 s)			260	°C	10 s


Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

Item		Symbol	Mini- mum	Typical	Maxi- mum	Unit	Measurement conditions
Input	LED forward voltage	V _F	1.0	1.15	1.3	V	I _F = 10 mA
	Reverse current	I _R			10	μΑ	V _R = 5 V
	Capacity between terminals	C _T		15		pF	V = 0, f = 1 MHz
	Trigger LED forward current	I _{FT}			4	mA	I _O = 100 mA
Output	Maximum resistance with output ON	R _{ON}		1	1.5	Ω	I _F = 5 mA, I _O = 300 mA, t < 1 s
	Current leakage when the relay is open	I _{LEAK}		0.2	1.0	nA	V _{OFF} = 20 V T _a = 50°C
	Capacity between terminals	C _{OFF}		5.0	12.0	pF	V = 0, f = 100 MHz, t < 1 s
Capacity between I/O terminals		C _{I-O}		0.8		pF	f = 1 MHz, V _s = 0 V
Insulation resistance		R _{I-O}	1,000			ΜΩ	$V_{I-O} = 500 \text{ VDC}, R_{oH} \le 60\%$
Turn-ON time		t _{ON}		0.09	0.5	ms	$I_F = 10 \text{ mA}, R_L = 200 \Omega,$
Turn-OFF time		t _{OFF}		0.2	0.5	ms	$V_{DD} = 20 \text{ V (See note 2.)}$

2. Turn-ON and Turn-OFF Times

Note:




■ Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}			20	V
Operating LED forward current	I _F	7		30	mA
Continuous load current (AC peak/DC)	Io			300	mA
Operating temperature	T _a	25		60	°C

■ Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage



On-state resistance vs. Ambient temperature




Trigger LED forward current vs. Ambient temperature




Turn ON, Turn OFF time vs. LED forward current


On-state voltage VON (V)




Turn ON, Turn OFF time vs. Ambient temperature



Current leakage vs. Load voltage



Output terminal capacitance COFF/COFF(ov) vs. Load voltage





All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

Specifications subject to change without notice

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON **OMRON ELECTRONIC**

COMPONENTS LLC 55 E. Commerce Drive, Suite B Schaumburg, IL 60173

847-882-2288

Cat. No. X302-E-1

12/10

OMRON ON-LINE

Global - http://www.omron.com USA - http://www.components.omron.com

Printed in USA

MOS FET Relays **G3VM-21GR1**