Relays & Sockets



### **RU Series Universal Relays**

### Full featured universal miniature relays Designed with environment taken into consideration

- Two terminal styles: plug-in and PCB mount
- Non-polarized LED indicator available on plug-in relays
- No internal wires, lead-free construction
- Cadmium-free contacts
- Mechanical flag indicator available on plug-in relays
- Manual latching lever with color coding for AC or DC coil
- Snap-on yellow marking plate; optional marking plates are available in four other colors
- Maximum contact ratings: 10A (RU2), 6A (RU4), 3A (RU42)
- · UL Recognized, CSA Certified, EN Compliant











### With Latching or Momentary Lever

#### 


The contact position can be confirmed through. the five small windows.

#### 

Standard yellow marking plate is easily replaced. with optional marking plates in four colors for easy identification of relays.

### LED Indicator\*-----

Non-polarized green LED indicator is standard provision for plug-in terminal, latching lever



#### **Latching and Momentary Lever**

Using the lever, operation can be checked without energizing the coil. The lever is color coded for AC and DC coils.

	Latching	Momentary
AC coil:	Orange	Red
DC coil:	Green	Blue

#### **In Normal Operation**




Note: Turn off the power to the relay coil when using the latching lever. After checking the operation, return the latching lever in the normal position.

### Standard (without lever)


#### 

For identification of AC or DC coils.

AC coil: Yellow DC coil: Blue









Coil Voltage	Tape Color
24V AC	White
100 to 110V AC	Clear
110 to 120V AC	Blue
200 to 220V AC	Black
220 to 240V AC	Red
24V DC	Green
6V DC	
12V DC	Voltage marking on
48V DC	yellow tape
110V DC	

754 www.idec.com

### **Part Number Selection**

Contact	Model	Standard	With Latching Lever	With Momentary Lever	Coil Voltage Code (Standard Stock in bold)
DPDT (10A)	Standard	RU2S-C-	RU2S-	RU2S-M-	A24, <b>A110</b> , <b>A220</b> D6, D12, <b>D24</b> , D48, D110
	With RC (AC coil only)	RU2S-CR-	RU2S-R-	RU2S-MR-	A110, A220
	With diode (DC coil only)	RU2S-CD-	RU2S-D-	RU2S-MD-	D6, D12, <b>D24</b> , D48, D110
100 the 1000	PCB	RU2V-NF-	_	_	A24, A110, A220 D6, D12, <b>D24</b> , D48, D110
4PDT (6A)	Standard	RU4S-C-	RU4S-	RU4S-M-	A24, <b>A110</b> , <b>A220</b> D6, D12, <b>D24</b> , D48, D110
	With RC (AC coil only)	RU4S-CR-	RU4S-R-	RU4S-MR-	A110, A220
	With diode (DC coil only)	RU4S-CD-	RU4S-D-	RU4S-MD-	D6, D12, D24, D48, D110
Utackeld O Like Co	PCB	RU4V-NF-	_	_	A24, <b>A110</b> , A220 D6, D12, <b>D24</b> , D48, D110
4PDT Bifurcated (3A)	Standard	RU42S-C-	RU42S-	RU42S-M-	A24, A110, A220 D6, D12, <b>D24</b> , D48, D110
	With RC (AC coil only)	RU42S-CR-	RU42S-R-	RU42S-MR-	A110, A220
	With diode (DC coil only)	RU42S-CD-	RU42S-D-	RU42S-MD-	D6, D12, D24, D48, D110
Uththio Uhitition	PCB	RU42V-NF-	_	_	A24, A110, A220 D6, D12, <b>D24</b> , D48, D110



- 1. Plug-in terminal models have an LED indicator and a mechanical indicator as standard.
- 2. PCB models do not have an LED indicator or a mechanical indicator.

### **Ordering Information**

When ordering, specify the Part No. and coil voltage code:

(example) RU2S-C A110

Part No. Coil Voltage Code

### **Coil Voltage Table**

Coil Voltage Code	A24	A110	A220	D6	D12	D24	D48	D110
Coil Rating	24V AC	110-120V AC	220-240V AC	6V DC	12V DC	24V DC	48V DC	110V DC

#### **Sockets**

Relays	Spring Clamp DIN Rail Mount	Standard DIN Rail Mount	Finger-safe DIN Rail Mount	Panel Mount	PCB Mount
RU2S (DPDT)	SU2S-11L	SM2S-05 SM2S-05C SY4S-51		SY4S-51	SM2S-61 SM2S-62
RU4S (4PDT) RU42S (4PDT)	SU4S-11L	SY4S-05	SY4S-05C		SY4S-61 SY4S-62
	NS((		T.	10/0/0/0/0/0/0/0/0/0/0/0/0/0/0/0/0/0/0/	

### **Hold Down Springs & Clips**

Appearance Description		Relay For DIN Mount Socket		For Through Panel & PCB Mount Socket	Min Order Ωty
$\langle \rangle$	Pullover Wire Spring	RU2S/RU4S/ RU42S	SY4S-02F1	SY4S-51F1	10
180	Leaf Spring (side latch)	RU2S/RU4S/ RU42S	SFA-202	SFA-302	20
-	Leaf Spring (top latch)	RU2S/RU4S/ RU42S	SFA-101	SFA-301	20

#### **Accessories**

Name	Part Number	Color Code *	Min. Order Qty.
Marking Plate	RU9Z-P*	A (orange), G (green), S (blue), W (white), Y (yellow)	10



Specify a color code when ordering. The marking plate can be removed from the relay by inserting a flat screwdriver under the marking plate.

### **Specifications**

Contact Material     Silver alloy     Silver (gold classes)       Contact Resistance 1     50 mΩ maxim       Minimum     24V DC, 5 mA (reference value)     1V DC, 1 mA       Operate Time 3     20 ms maxim	1V DC, 0.1 mA					
Minimum Applicable Load <sup>2</sup> Operate Time <sup>3</sup> 24V DC, 5 mA (reference value)  1V DC, 1 mA 20 ms maxin	1V DC, 0.1 mA					
Applicable Load <sup>2</sup> (reference value) 1V DC, 1 mA  Operate Time <sup>3</sup> 20 ms maxim						
·	num					
Release Time <sup>3</sup> 20 ms maxim	num					
<b>Power Consumption</b> AC: 1.1 to 1.4VA (50 Hz), 0.9 to 1.2V	A (60 Hz) DC: 0.9 to 1.0W					
Insulation Resistance 100MΩ minimum (500	V DC megger)					
Between contact and coil: 2	500V AC, 1 minute					
Dielectric Strength Between contacts of d	fferent poles:					
2500V AC, 1 minute 20	2500V AC, 1 minute 2000V AC, 1 minute					
Between contacts of the same po	Between contacts of the same pole: 1000V AC, 1 minute					
Operating Frequency  Electrical: 1800 operation Mechanical: 18,000 opera	,					
Vibration Resistance  Damage limits: 10 to 55 Hz, Operating extremes: 10 to 55	•					
Shock Resistance Damage limits: 1000 Operating extremes: 1	, , ,					
Mechanical Life AC: 50,000,000 operations DC: 100,000,000 operations	50,000,000 operations					
Electrical Life <sup>4</sup> See table on pa	ge 758					
	PCB model: -55 to +70°C (no freezing) Blade model: -55 to +60°C (no freezing)					
Operating Humidity 5 to 85% RH (no cor	densation)					
Weight Approx. 35	g					



- Measured using 5V DC, 1A voltage drop method
   Measured at operating frequency of 120 operations/min (failure rate level P, reference value)
   Measured at the rated voltage (at 20°C), excluding contact bouncing; Release time of AC relays with RC: 25 ms maximum Release time of DC relays with diode: 40 ms maximum
- 4. Contact Load and Electrical Life (at ambient temperature 20°C)
  5. Measured at the rated voltage.



Description	Appearance	Use with	Part No.	Remarks
Aluminum DIN Rail (1 meter length)		All DIN rail sockets	BNDN1000	IDEC offers a low-profile DIN rail (BNDN1000). The BNDN1000 is designed to accommodate DIN mount sockets. Made of durable extruded aluminum, the BNDN1000 measures 0.413 (10.5mm) in height and 1.37 (35mm) in width (DIN standard). Standard length is 39" (1,000mm).
DIN Rail End Stop	A CONTRACTOR OF THE PARTY OF TH	DIN rail	BNL5	9.1 mm wide.
Replacement Hold-Down Spring Anchor		Horseshoe clip for DIN rail sockets	Y778-011	For use on DIN rail mount socket when using pullover wire hold down spring. 2 pieces included with each socket.

### **Coil Ratings**

Rated Voltage (V)		Coil	±13/0 (at 20 G)		Coil Resistance (Ω)	Operating Characteristics (values at 20°C)			
		Voltage Code	50 Hz	60 Hz	±10% (at 20°C)	Maximum Continuous Applied Voltage	Pickup Voltage	Dropout Voltage	
AC (50/60 Hz)	24	A24	49.3	42.5	164			30% minimum	
	110-120	A110	8.4-10.0	7.1-8.2	4,550	110%	80% maximum		
(00) 00 112)	220-240	A220	4.2-5.0	3.6-4.2	18,230				
	6	D6	155		40		80% maximum	10% minimum	
	12	D12	80		160	110%			
DC	24	D24	44.7		605				
	48	D48	18		2,560				
	110	D110	8.8	9	12,100				



<sup>1.</sup> The rated current includes the current of the LED indicator.

### **Surge Suppressor Ratings**

Mo	odel	Ratings
AC Coil	With RC	RC series circuit R: 20 k $\Omega$ , C: 0.033 $\mu$ F
DC Coil	With Diode	Diode reverse voltage: 1000V Diode forward current: 1A

### **Contact Ratings**

Maximum Contact Capacity									
Contact	Continuous	Allowable Co	ontact Power	Voltage	Rated Load				
	Current	Resistive Load	Inductive Load	(V)	Res. Load	Ind. Load			
DPDT	10A	2500VA AC	1250VA AC	250 AC	10A	5A			
	IUA	300W DC	150W DC	30 DC	10A	5A			
4PDT	6A	1500VA AC	600VA AC	250 AC	3A	0.8A			
4701		180W DC	90W DC	30 DC	3A	1.5A			
4PDT	3A	750VA AC	200VA AC	250 AC	3A	0.8A			
bifurcated	ъΑ	90W DC	45W DC	30 DC	3A	1.5A			



On 4PDT relays, the maximum allowable total current of neighboring two poles is 6A. At the rated load, make sure that the total current of neighboring two poles does not exceed 6A (3A + 3A = 6A).
 Inductive load for the rated load — cos Ø = 0.3, L/R = 7 ms

USA: 800-262-IDEC

### **UL and c-UL Ratings**

Voltage	Resistive			General Use			Horse Power Rating		
	RU2	RU4	RU42	RU2	RU4	RU42	RU2	RU4	RU42
250V AC	10A	_	3A	_	6A	_	_	1/10HP	_
30V DC	10A	6A	3A	_	_	_	_	_	_

### **CSA Ratings**

	•			
Valtana	Resistive			
Voltage	RU42			
250V AC	3A			
30V DC	3A			

### **TÜV Ratings**


	Voltage	R	esistiv	е	Inductive		
		RU2	RU4	RU42	RU2	RU4	RU42
	250V AC	10A	6A	3A	5A	0.8A	0.8A
	30V DC	10A	6A	3A	5A	1.5A	1.5A

### **Socket Specifications**


	Sockets	Terminal	Electrical Rating	Wire Size	Torque
DIN Rail Mount Sockets	SU2S-11L	Spring clamp terminals	250V/10A	24-16 AWG	_
	SU4S-11L	Spring clamp terminals	250V/6A (using RU4), 10A (using RU2)	24-16 AWG	_
	SM2S-05	M3 screw with captive wire clamp	300V, 10A	Maximum up to 2—#14AWG	5.5 - 9in∙lbs
	SM2S-05C	M3 screw with captive wire clamp, fingersafe	300V, 10A	Maximum up to 2—#14AWG	5.5 - 9in • lbs
	SY4S-05	M3 screw with captive wire clamp	300V, 7A (using RU4), 10A (using RU2)	Maximum up to 2—#14AWG	5.5 - 9in∙lbs
	SY4S-05C	M3 screw with captive wire clamp, fingersafe	300V, 7A (using RU4), 10A (using RU2)	Maximum up to 2—#14AWG	5.5 - 9in∙lbs
Through Panel Mount Socket	SY4S-51	Solder	300V, 7A	_	_
PCB Mount Socket	SY4S-61	PCB mount	300V, 7A	_	_
	SY4S-62	PCB mount	250V, 7A	_	_

### **Electrical Life Curves**


### **RU2 (Resistive Load)**




### **RU4 (Resistive Load)**




### **RU42 (Resistive Load)**




### **RU2 (Inductive Load)**



### **RU4 (Inductive Load)**




**RU42 (Inductive Load)** 




#### **Maximum Switching Current**


#### RU2



### RU4




#### **RU42 (Bifurcated)**




#### **Ambient Temperature vs. Temperature Rise Curves**


#### RU2 (AC Coil, 50 Hz)




#### RU2 (AC Coil, 60 Hz)




### RU2 (DC Coil)




### RU4/RU42 (AC Coil, 50 Hz)



### RU4/RU42 (AC Coil, 60 Hz)



#### RU4/RU42 (DC Coil)



A

The above temperature rise curves show the characteristics when 100% the rated coil voltage is applied.


The heat resistance of the coil is 120°C. The slant dashed line indicates the allowable temperature rise for the coil at different ambient temperatures Load current 6A x 2 poles is for the RU4 models only.

### **Internal Connection (View from Bottom)**

### **RU2S-\* Standard**

(1)12

(5)14 (9)11



(4)42

(8)44

(12)4

(14)A2

**RU2S-\*R with RC** 




#### **RU2S-\*D With Diode**

(1<u>)1</u>2

(5)14

13)A





(12)41

(14)A2

Over 24V DC coil

#### **RU2V-NF-\***



(1)12 (2)22 (3)32 (4)42 (5)14 (6)24 (7)34 (8)44 (9)11 (10)21 (11)31 (12)41

-0-

### RU4S-\*/RU42S-\* Standard

Over 24V AC/DC coil




24V AC/DC coil or less



### RU4S-\*R/RU42S-\*R With RC



RU4S-\*D/RU42S-\*D With Diode RU4V-NF-\*/RU42V-NF-\*




24V DC coil or less



Over 24V DC coil


#### **Dimensions (mm)**

#### RU2S



Marking plate removal slot is provided only on one side. Insert a flat screwdriver into the slot to remove the marking


#### **RU2V**



All dimensions in mm.


### Dimensions con't (mm)


#### RU4S



Marking plate removal slot is provided only on one side. Insert a flat screwdriver into the slot to remove the marking plate.

### RU4V, RU42V






All dimensions in mm.

### **Spring Clamp DIN Rail Mount Sockets**


#### **SU2S-11L**




## SU4S-11L

5

(Top View)









### **Standard DIN Rail Mount Sockets**

#### SM2S-05



### SY4S-05




## Finger-safe DIN Rail Mount Sockets

#### SM2S-05C

### 


#### SY4S-05C

Dimensions con't (mm)





#### **PCB Mount Sockets**

#### SM2S-61




#### SM2S-62






 17.2 min. when using a hold-down spring.
 13.2 min. when using a hold-down spring for the relay with check button.

SY4S-61 SY4S-62






#### \* 17.2 min. when using a hold-down spring. \*\* 13.2 min. when using a hold-down spring for the relay with check button

#### **Through Panel Mount Socket**

### SY4S-51







### **Driving Circuit for Relays**

- 1. To ensure correct relay operation, apply rated voltage to the relay coil.
- 2. Input voltage for the DC coil:

A complete DC voltage is best for the coil power to make sure of stable relay operation. When using a power supply containing a ripple voltage, suppress the ripple factor within 5%. When power is supplied through a rectification circuit, the relay operating characteristics, such as pickup voltage and dropout voltage, depend on the ripple factor. Connect a smoothing capacitor for better operating characteristics as shown below.







Emax = Maximum of pulsating current Emin = Minimum of pulsating current Emean = DC mean value

3. Leakage current while relay is off:


When driving an element at the same time as the relay operation, special consideration is needed for the circuit design. As shown in the incorrect circuit below, leakage current (lo) flows through the relay coil while the relay is off. Leakage current causes coil release failure or adversely affects the vibration resistance and shock resistance. Design a circuit as shown in the correct example.





4. Surge suppression for transistor driving circuits:

When the relay coil is turned off, a high-voltage pulse is generated, causing a transistor to deteriorate and sometimes to break. Be sure to connect a diode to suppress the back electromotive force. Then, the coil release time becomes slightly longer. To shorten the coil release time, connect a Zener diode between the collector and emitter of the transistor. Select a Zener diode with a Zener voltage slightly higher than the power voltage.




#### **Protection for Relay Contacts**


**Operating Instructions** 

- The contact ratings show maximum values. Make sure that these values are not exceeded. When an inrush current flows through the load, the contact may become welded. If this is the case, connect a contact protection circuit, such as a current limiting resistor.
- 2. Contact protection circuit:

When switching an inductive load, arcing causes carbides to form on the contacts, resulting in increased contact resistance. In consideration of contact reliability, contact life, and noise suppression, use of a surge absorbing circuit is recommended. Note that the release time of the load becomes slightly longer. Check the operation using the actual load. Incorrect use of a contact protection circuit will adversely affect switching characteristics. Four typical examples of contact protection circuits are shown in the following table:



3. Do not use a contact protection circuit as shown below:



Generally, switching a DC inductive load is more difficult than switching a DC resistive load. Using an appropriate arc suppressor, however, will improve the switching characteristics of a DC inductive load.

#### **Soldering**

- 1. When soldering the relay terminals, use a soldering iron of 30 to 60W, and quickly complete soldering (within approximately 3 seconds).
- 2. Use a non-corrosive rosin flux.

#### **Operating Instructions con't**

#### **Other Precautions**

1. General notice:

To maintain the initial characteristics, do not drop or shock the relay.

The relay cover cannot be removed from the base during normal operation. To maintain the initial characteristics, do not remove the relay cover.

Use the relay in environments free from condensation, dust, sulfur dioxide (SO<sub>2</sub>), and hydrogen sulfide (H<sub>2</sub>S).

Make sure that the coil voltage does not exceed applicable coil voltage range.

- 2. UL and CSA ratings may differ from product rated values determined by IDEC.
- 3. Do not use relays in the vicinity of strong magnetic field, as this may affect relay operation.

### **Safety Precautions**

- Turn off the power to the relay before starting installation, removal, wiring, maintenance, and inspection of the relays. Failure to turn power off may cause electrical shock or fire hazard.
- Observe specifications and rated values, otherwise electrical shock or fire hazard may be caused.
- Use wires of the proper size to meet voltage and current requirements. Tighten the terminal screws on the relay socket to the proper tightening torque.
- Surge absorbing elements on AC relays with RC or DC relays with diode are
  provided to absorb the back electromotive force generated by the coil. When
  the relay is subject to an excessive external surge voltage, the surge absorbing element may be damaged. Add another surge absorbing provision to the
  relay to prevent damage.

### **Precautions for the RU Relays**

- Before operating the latching lever of the RU relay, turn off the power to the RU relay. After checking the circuit, return the latching lever to the original position.
- Do not use the latching lever as a switch. The durability of the latching lever is a minimum of 100 operations.
- When using DC loads on 4PDT relays, apply a positive voltage to terminals of neighboring poles and a negative voltage to the other terminals of neighboring poles to prevent the possibility of short circuits.
- DC relays with a diode have a polarity in the coil terminals. Apply the DC voltage to the correct terminals.

USA: 800-262-IDEC

Canada: 888-317-IDEC