IDEC Miniature Switches & Pilot Devices

CSA Certified

File No. LR21451

ø16mm - A6 Series

A6 Series — Miniature Switches and Pilot Devices: 16mm

CE

Key features of the A6 series switches and pilot lights include:

- 16mm (5/8") mounting hole
- LED illumination
- Compact design saves space
- Momentary, Maintained, Selectors, and E-Stops
- · Gold-clad Silver contacts for reliable low level switching
- Snap action contacts
- IP40 (dustproof) or IP65 (oiltight) versions

UL Recognized

File No.E55996



	Degree of Protection		IP40: Dustproof					
S			IP65 Waterproof/Oiltight/Corrosion Resistant					
	Contact Configuration		SPDT, DPDT					
	Maximum Voltage		250V AC/DC					
	Thermal Current		3A					
	Minimum Applicable Load		5V AC/DC, 1mA (subject to operating conditions)					
	Contact Material		Gold-clad silver					
	Terminal Style		.110" Solder/ Quick Connect					
	Operating Temperature		LED Type: -25° to +55°C (no freezing)					
tior	Operating Humidity		45 to 85% RH					
Specifications	Contact Resistance		50m Ω maximum (initial value)					
	Insulation Resistance		100M Ω minimum (500V DC megger)					
	Vibration Resistance		10 to 55Hz, amplitude 1.5mm p-p					
	Shock Resistance		Damage limits: 500m/sec ² (approx. 50G) Operating extremes: 200m/sec ² (approx. 20G)					
	Electrical Life		100,000 operations minimum (at full rated load)					
	Mechanical Life		Maintained: 100,000 operations minimum Momentary: 1,000,000 operations minimum Selector/Keylock: 250,000 operations minimum					
	Dielectric Strength		Switch Unit: 2,000VAC, 1 min. between live/dead part and terminals of different poles; 1,000V AC, 1 minute between terminals of the same pole; 1,500V AC, 1 minute between contact and lamp terminals. Illumination Unit: 2,000VAC, 1 min. between live part/ground					
	Soldering Temperature		20W/5 seconds or 260°C/3 seconds					
Contact Ratings	Operating Voltage		24V		120V		240V	
	AC (50/60Hz)	Resistive			1.0A		0.5A	
		Inductive	—		0.7A		0.5A	
	DC	Resistive	1.0A		0.2A			
	DC	Inductive	0.7A		0.1A			
LED Lamp Ratings	Rated Voltage/Current		5V DC ±5%	6V AC/DC (±10%)		12V AC/DC (±10%)	24V AC/DC (±10%)	
			8mA	DC: A, R, W, Y: 6mA G, S: 5mA AC: A, R, W, Y: 8mA G, S: 7mA		DC: 8mA AC: 9mA	DC: 8mA AC: 9mA	

1. AC Inductive Load, PF = 0.6 - 0.7; DC Inductive Load, L/R = 7ms.

2. Minimum applicable load (reference value) is 5V AC/DC/1mA (applicable range is subject to the operating conditions and load).

3. LED lamp contains a built-incurrent-limiting resistor and a protection diode.

4. LED's don't "burn out." Luminance is reduced to 50% of initial intensity after being lit for 50,000 hours continuously.

A2-17

AL6 Illuminated Pushbuttons (Assembled)


Part Numbers: LED Illuminated Pushbuttons

		bers: LED Illuminated Pushbuttor		Part Numbers				
	Description	Style	Voltage	Contact	Momentary Maintained (Latching)			
A2					Dustproof (IP40)	Oiltight (IP65)	Dustproof (IP40)	Oiltight (IP65)
Switches & Pilot Devices	Standard Lens	Round 18mm diameter	24V AC/DC ±10%	SPDT DPDT	AL6M-M14-@ AL6M-M24-@	AL6M-M14P-@ AL6M-M24P-@	AL6M-A14-@ AL6M-A24-@	AL6M-A14P-@ AL6M-A24P-@
		Square 18mm	24V AC/DC ±10%	SPDT DPDT	AL6Q-M14-@ AL6Q-M24-@	AL6Q-M14P-@ AL6Q-M24P-@	AL6Q-A14-@ AL6Q-A24-@	AL6Q-A14P-@ AL6Q-A24P-@
		Rectangular 18mm x 24mm	24V AC/DC ±10%	SPDT DPDT	AL6H-M14-@ AL6H-M24-@	AL6H-M14P-@ AL6H-M24P-@	AL6H-A14-@ AL6H-A24-@	AL6H-A14P-@ AL6H-A24P-@
	Oversize Lens	Round 24mm diameter	24V AC/DC ±10%	SPDT DPDT	_	AL6M-M14P-M@ AL6M-M24P-M@	_	AL6M-A14P-M@ AL6M-A24P-M@
		Square 24 mm	24V AC/DC ±10%	SPDT DPDT	_	AL6Q-M14P-Q② AL6Q-M24P-Q②	_	AL6Q-A14P-Q@ AL6Q-A24P-Q@
		Rectangular 18mm x 24mm	24V AC/DC ±10%	SPDT DPDT	_	AL6Q-M14P-H② AL6Q-M24P-H②	_	AL6Q-A14P-H@ AL6Q-A24P-H@
	1. In place of ⁽²⁾ , specify Lens/LED Color Code from table below. 2. Lamps also available in 5V DC, 6V AC/DC or 12 V AC/DC, change ⁽⁴⁾ using voltage/lamp codes (ie AL6M-M13- ⁽²⁾) uses 12V				② Lens/LED Color Code Color Code Amber A		Voltage Code Voltage 5V DC	Code
	AC/DC LED). 3. LED lamp is included in unit and contains a current-limiting				Green G		6V AC/DC	2
	resista	or and a protection diode. (External resistor	Red R		12V AC/DC	3		
		der as sub-assembled, see page A2-21. ccessories, see page A2-25.	Blue S		24V AC/DC	4		
		5. Tor accessories, see page A2-25.						

6. For dimensions, see page A2-27.


White W Yellow Y

Schematics — A Series: 5/8" (16mm)




Dimensions — A Series: 5/8" (16mm)

Pushbuttons, Ø 5/8" (16mm)




Large Size Lens



all dimensions are in mm

Selector Switches, Ø 5/8" (16mm)



all dimensions are in mm

