


CSS150 Series

3 x 5" 150W AC-DC Medical Power Supplies

RoHS



- ◆ Wide Range AC Input
- ◆ Low profile, Industry Standard Footprint
- ◆ Global Safety Agency Compliance

Key Market Segments & Applications

Medical
Gaming
Test and Measurement

Features and Benefits


Feature	Benefit
◆ Industry standard footprint	◆ Availability to second source
◆ Wide Range AC Input	◆ Global Operation
◆ Dual input fuses	◆ Easier system compliance

Specifications

		CSS150
ITEMS		
Input Voltage range	V	90 - 264VAC (47 - 400Hz)(1) or 120 - 180VDC
Inrush Current	A	<60A maximum at 264VAC input, 25°C ambient cold start
Input Current (115/230VAC)	A	1.7 / 0.85
Leakage Current	µA	<250µA 264VAC 63Hz
Hold Up Time (Typ)	ms	16ms at 115VAC input
Temperature Coefficient	-	±0.05%/°C
Voltage Accuracy	%	±1%
Adjustment Range	%	±3%
Minimum Load	A	None
Total Regulation	%	±3%
Ripple & Noise	%	2% peak to peak
Overcurrent Protection	-	110 - 150%
Overvoltage Protection	V	110 - 150% of nominal (Cycle input power to reset)
Remote On/Off	-	Unit on: Floating or low <1.2V, Unit off: Apply 5V with respect to 0V
Efficiency	%	89% typical
Off load power draw	W	<0.5W
Operating Temperature	-	0 to +70°C derate linearly to 50% load from 50 to 70°C
Storage Temperature	°C	-20 to +85°C
Humidity (non condensing)	-	20 - 95% RH
Cooling	-	Convection or forced air (2.5m/s)
Withstand Voltage	-	Input to Ground 1.5kVAC, Input to Output 4kVAC, Output to Ground 500VDC for 1 min.
Isolation Resistance	-	>100M at 25C & 70%RH, Output to Ground 500VDC
Vibration (non operating)	-	19.6m/s ² (10~55Hz:2G Constant, X,Y,Z 60min each.)
Shock	-	< 196.1 m/s ² (20G)
Safety Agency Approvals	-	UL60601-1, EN60601-1, IEC60601-1, CE Mark
Conducted & Radiated EMI	-	EN55011-B, FCC Class B
Immunity	-	EN60601-1-2
MTBF	-	100,000 (MIL-217F-HDBK)
Weight (Typ)	g	340g
Size (WxLxH)	mm	3 x 5 x 1.3" (including underside components)
Warranty	yrs	Two Years

(1) Derate linearly to 90W convection rating from 90 to 100VAC input.

Outline Drawings



Dimension :
L127(5") x W76.2(3") x H30.0(1.18")mm

Pin Assignments :

CN1	PIN1	L
	PIN2	N
CN2	PIN1	PS-ON +
	PIN2	PS-ON -
CN3	PIN1	GND
	PIN2	GND
	PIN3	GND
	PIN4	+V
	PIN5	+V
	PIN6	+V

Model Selector

Model	Output Voltage (V)	Voltage Adjust (V)	Maximum Current Convection (A)	Maximum Power Convection (W)	Maximum Current Forced Air	Maximum Power Forced Air
CSS150-12	12V	11.64 - 12.36V	8.3A	100W	12.5A	150W
CSS150-15	15V	14.55 - 15.45V	6.7A	100W	10A	150W
CSS150-24	24V	23.28 - 24.72V	4.2A	100W	6.3A	150W
CSS150-36	36V	34.92 - 37.08V	2.8A	100W	4.2A	150W
CSS150-48	48V	46.60 - 49.44V	2.1A	100W	3.1A	150W

Other Medical Products

KM	15 - 40W pcb mount medical
CSS65	40 - 65W 2x4" medical
NV175	175 - 200W 1-4 outputs
NV300	300W 1-4 outputs

- ◆ Input Connector mates with Molex Housing 09-50-3031 or equivalent
- ◆ Output Connector mates with Molex Housing 09-50-3061 or equivalent
- ◆ Sense Connector (CN3) mates with J.S.T. XHP-2

For Additional Information, please visit
us.tdk-lambda.com/lp/products/css-series.htm