


RJ Series



Slim Power Relays (Bifurcated Contacts)




RJ Series Slim Power Relay Plug-in Terminal (bifurcated contacts)

High contact reliability with bifurcated contacts (minimum applicable load: 1V DC, 100µA)

- The smallest width for 2-pole/bifurcated contacts relay (based on IDEC research as of April 2011)
- Non-polarized green LED indicator available (except for simple type)
- IDEC's unique light-guide structure enables an RJ relay to be identified by the illuminating LED.
- Diode, reverse polarity diode, and RC circuits are available.
- Peak inverse voltage is 1000V.
- UL recognized, CSA certified, VDE approved, EN compliant.

Applicable Standards

Approable Granadius								
Standards	Mark	File No. or Organization						
UL508	71	UL Recognized File No. E55996						
CSA C22.2 No.14		CSA File No. LR35144						
EN61810-1	VDE REGNr. B312	VDE No. 40015055						
EN01810-1	CE	EU Low Voltage Directive						



Relays

Bifurcated Contacts

	2-pole ((bifurcated contacts DPDT)		
Туре	Part No. (Ordering Part No.)	Coil Voltage Code		
Standard (with LED indicator)	RJ22S-CL-*	A12, A24, A110, A115, A120, A220, A230, A240, D5, D6, D12,		
Simple (without LED indicator)	RJ22S-C-*	D24, D48, D100		
With diode (with LED indicator)	RJ22S-CLD-*			
With diode (without LED indicator)	RJ22S-CD-*	D5, D6, D12, D24, D48, D100		
With diode Reverse polarity (with LED indicator)	RJ22S-CLD1-*			
With diode Reverse polarity (without LED indicator)	RJ22S-CD1-*			
With RC circuit (with LED indicator)	RJ22S-CLR-*	A12, A24, A110, A115, A120, A220,		
With RC circuit (without LED indicator)	RJ22S-CR-*	A230, A240		

Coil Voltage Code

Code	Voltage		
A12	12V AC		
A24	24V AC		
A110	110V AC		
A115	115V AC		
A120	120V AC		
A220	220V AC		
A230	230V AC		
A240	240V AC		
D5	5V DC		
D6	6V DC		
D12	12V DC		
D24	24V DC		
D48	48V DC		
D100	100-110V DC		

Contact Ratings

Allowable C	ontact Power		Rated L	.oad	Allowable	Allowable	Minimum Applicable Load (Note)	
Resistive Load	Inductive Load	Voltage	Resistive Load	Inductive Load cosø=0.4 L/R=7ms	Switching Current	Switching Voltage		
250VA AC	100VA AC	250V AC	1A	0.4A	1A	250V AC	1V DC 100uA	
30W DC	15W DC	30V DC	1A	0.5A	IA	125V DC	(reference value)	

Note: Measured at operating frequency of 120 operations per minute (failure rate level P, reference value)

Ratings

	UL Ratings			CSA Ratings						VDE Ratings		
Voltage	Resistive		Gener	General Use Res		Resistive Inductive		ctive	General Use		Resistive	
	NO	NC	NO	NC	NO	NC	NO	NC	NO	NC	NO	NC
250V AC	_	_	1A	1A	_	_	_	_	1A	1A	1A	1A
30V DC	1A	1A	_	_	1A	1A	1A	1A	_	_	1A	1A

Coil Ratings

	Without LED India				Indicator	With LED Indicator			Operating Characteristics (against rated values at 20°C)					
	Voltage (V) Coil Voltage Code		Voltage (mA) ±15%		Coil Resistance (Ω)	Rated Current (mA) ±15%, (at 20°C)		Coil Resistance (Ω)	Pickup Voltage	Dropout Voltage	Maximum Continuous Applied	Power Consumption		
	Code		50Hz	60Hz	±10% (at 20°C)	50Hz	60Hz	±10% (at 20°C)	(initial value)	(initial value)	Voltage (Note)			
	12V	A12	87.3	75.0	62.5	91.1	78.8	62.5						
	24V	A24	43.9	37.5	243	47.5	41.1	243						
	110V	A110	9.6	8.2	5,270	9.5	8.1	5,270				Approx.		
AC	115V	A115	9.1	7.8	6,030	9.0	7.7	6,030	80%	30%	140%	1.1VA (50Hz) 0.9 to 1.2VA (60Hz)		
50/60 Hz	120V	A120	8.8	7.5	6,400	8.7	7.4	6,400	maximum	minimum				
	220V	A220	4.8	4.1	21,530	4.8	4.1	21,530						
	230V	A230	4.6	3.9	24,100	4.6	3.9	24,100					ļ	
	240V	A240	4.3	3.7	25,570	4.3	3.7	25,570						
	5V	D5	10	06	47.2	11	10	47.2						
	6V	D6	88	3.3	67.9	92	2.2	67.9						
DC	12V	D12	44	1.2	271	48	3.0	271	70%	10%	170%	Approx.		
DC	24V	D24	22	2.1	1,080	25	5.7	1,080	maximum	minimum		0.53 to 0.64W		
	48V	D48	11	1.0	4,340	10).7	4,340						
	100-110V	D100	5.3	-5.8	18,870	5.2	-5.7	18,870			160%			

Note: Maximum continuous applied voltage is the maximum voltage that can be applied to relay coils.

Specifications


Relay		RJ22S			
Number of Po	oles	2-pole			
Contact Con	figuration	DPDT (bifurcated contacts)			
Contact Mate	erial	AgNi (gold clad)			
Degree of Pr	otection	IP40			
Contact Resi (initial value)	stance	50 mΩ maximum (measured using 5V DC, 1A voltage drop method)			
Operating Tir	me (at 20°C)	15 ms maximum (at the rated coil voltage, excluding contact bounce time) With diode or RC: 20 ms maximum			
Release Time	e (at 20°C)	10 ms maximum (at the rated coil voltage, excluding contact bounce time) With diode or RC: 20 ms maximum			
Impulse With	stand Voltage	10,000V AC (between contact and coil)			
Insulation Re	esistance	100 M Ω minimum (500V DC megger)			
	Between contact and coil	5,000V AC, 1 minute			
Dielectric Strength	Between contacts of the same pole	1,000V AC, 1 minute			
Caongar	Between contacts of the different poles	3,000V AC, 1 minute			
Vibration	Operating Extremes	10 to 55 Hz, amplitude 0.75 mm			
Resistance	Damage Limits	10 to 55 Hz, amplitude 0.75 mm			
Shock	Operating Extremes	NO contact: 200 m/s ² , NC contact: 100 m/s ²			
Resistance	Damage Limits	1,000 m/s ²			
Electrical Life)	AC load: 100,000 operations minimum (operating frequency 1,800 per hour) DC load: 200,000 operations minimum (operating frequency 1,800 per hour)			
Mechanical L	Life	AC load: 10 million operations minimum (operating frequency 18,000 operations per hour) DC load: 20 million operations minimum (operating frequency 18,000 operations per hour)			
Operating Te (100% rated		-40 to +70°C (no freezing)			
Operating Hu	umidity	5 to 85%RH (no condensation)			
Storage Tem	perature	-40 to +85°C (no freezing)			
Storage Hum	nidity	5 to 85%RH (no condensation)			
Weight (appr	ox.)	19g			

Applicable Sockets

1 1			
Style	Part No.	Ordering Part No.	Package Quantity
Standard Screw Terminal	SJ2S-05B	SJ2S-05B	1
Finger-safe Screw Terminal	SJ2S-07L	SJ2S-07L	1
PC Board	SJ2S-61	SJ2S-61PN10	10
Terminal	SJ2S-61	SJ2S-61PN50	50

RJ Series Slim Power Relay Plug-in Terminal (bifurcated contacts)


Dimensions




All dimensions in mm.


Internal Connection (bottom view)

RJ22S-CL-* Standard (with LED indicator)







24V AC/DC or less **RJ22S-C-* Simple**




RJ22S-CLD-* With diode (with LED indicator)







RJ22S-CD-* With diode




RJ22S-CLD1-* With diode/reverse polarity (with LED indicator)







RJ22S-CD1-* With diode/reverse polarity




RJ22S-CLR-* With RC (with LED indicator)







RJ22S-CR-* With RC




Operating Temperature and Coil Temperature Rise



4





- The slanted dashed line indicates the allowable temperature rise for the coil at different ambient temperatures.
- The above temperature rise curves show the characteristics when 100% of the rated coil voltage is applied.


RJ Series Slim Power Relay PC Board Terminal (bifurcated contacts)

High contact reliability with bifurcated contacts (minimum applicable load: 1V DC, 100 μ A)

- DPDT, DPST-NO contacts are available.
- The smallest width for 2-pole/bifurcated contacts relay (based on IDEC research as of April 2011)
- IDEC's unique spring return mechanism ensures long life.
- Flux-tight structure

Applicable Standards

	Applicable of	uniuunu)		
	Standards	Mark	File No. or Organization		
ı	UL508	71	UL Recognition File No. E55996		
(CSA C22.2 No.14		CSA File No. LR35144		
	EN61810-1	VDE REGNr.B312	VDE No. 40015055		
Ľ	⊏IN0 I 0 I U- I	CE	EU Low Voltage Directive		



Relays

Bifurcated Contacts

		2-pole (bifurcated contacts DPDT)					
Туре	Contact	Part No. (Ordering Part No.)	Coil Voltage Code				
Plain	DPDT	RJ22V-C-*	A12, A24, A110, A115, A120, A220, A230,				
ΓΙΔΙΙΙ	DPST-NO	RJ22V-A-*	A240, D5, D6, D12, D24, D48, D100				

Coil Voltage Code

Code	Voltage
A12	12V AC
A24	24V AC
A110	110V AC
A115	115VAC
A120	120V AC
A220	220V AC
A230	230V AC
A240	240V AC
D5	5V DC
D6	6V DC
D12	12V DC
D24	24V DC
D48	48V DC
D100	100-110V DC

Contact Ratings

Allowable Co	ontact Power		Rated L	oad	Allowable	Allowable	Minimum Analicable
Resistive Load	Inductive Load	Voltage	Resistive Load	Inductive Load cosø=0.4 L/R=7ms	Switching Current	Switching Voltage	Minimum Applicable Load (Note)
250VA AC	100VA AC	250V AC	1A	0.4A	4 /	250V AC	1V DC
30W DC	15W DC	30V DC	1A	0.5A	IA	1A 125V DC	100µA (reference value)

Note: Measured at operating frequency of 120 operations per minute (failure rate level P, reference value)

Ratings

	Voltage	UL ratings				CSA Ratings							VDE Ratings	
		Resistive		General Use		Resistive		Inductive		General Use		Resistive		
		NO	NC	NO	NC	NO	NC	NO	NC	NO	NC	NO	NC	
	250V AC	_	_	1A	1A	_	_	_	_	1A	1A	1A	1A	
	30V DC	1A	1A	_	_	1A	1A	1A	1A	_	_	1A	1A	

RJ Series Slim Power Relay PC Board Terminal (bifurcated contacts)

Coil Ratings

		Coil	Rated Current (mA) ±15% (at 20°C)		Coil		erating Characteri est rated values at		
	Voltage V)	Voltage Code	50Hz	60Hz	Resistance (Ω) ±10% (at 20°C)	Pickup Voltage (initial value)	Dropout Voltage (initial value)	Maximum Continuous Applied Voltage (Note)	Power Consumption
	12V	A12	87.3	75.0	62.5		30% minimum	140%	Approx. 1.1VA (50Hz) 0.9 to 1.2VA (60Hz)
	24V	A24	43.9	37.5	243				
	110V	A110	9.6	8.2	5,270	80% maximum			
AC	115V	A115	9.1	7.8	6,030				
50/60 Hz	120V	A120	8.8	7.5	6,400				
	220V	A220	4.8	4.1	21,530				
	230V	A230	4.6	3.9	24,100				
	240V	A240	4.3	3.7	25,570				
	5V	D5	106 88.3		47.2	70% maximum	10% minimum	170%	Approx. 0.53 to 0.64W
	6V	D6			67.9				
	12V	D12	44.2		271				
DC	24V	D24	22.1		1,080				
	48V	D48	11.0		4,340				
	100-110V	D100	5.3-5.8		18,870			160%	

Note: Maximum continuous applied voltage is the maximum voltage that can be applied to relay coils.


Specifications

Specifica Relay		RJ22V					
Number of Po	oles	2-pole					
Contact Conf		DPDT (bifurcated), DPST-NO (bifurcated)					
Contact Mate		AgNi (gold clad)					
Degree of Pr	otection	Flux-tight structure					
Contact Resi	stance (initial value)	50 mΩ maximum (measured using 5V DC, 1A voltage drop method)					
Operating Tir	ne (at 20°C)	15 ms maximum (at the rated coil voltage, excluding contact bounce time)					
Release Time		10 ms maximum (at the rated coil voltage, excluding contact bounce time)					
Insulation Re	esistance	100 MΩ minimum (500V DC megger)					
Impulse With	stand Voltage	10,000V AC (between contact and coil)					
Dialastria	Between contact and coil	5,000V AC, 1 minute					
Dielectric Strength	Between contacts of the same pole	1,000V AC, 1 minute					
	Between contacts of the different poles	3,000V AC, 1 minute					
Vibration	Operating Extremes	10 to 55 Hz, amplitude 0.75 mm					
Resistance	Damage Limits	10 to 55 Hz, amplitude 0.75 mm					
Shock	Operating Extremes	NO contact: 200 m/s ² , NC contact: 100 m/s ²					
Resistance	Damage Limits	1,000 m/s ²					
Electrical Life	3	AC load: 100,000 operations minimum (operating frequency 1,800 per hour) DC load: 200,000 operations minimum (operating frequency 1,800 per hour)					
Mechanical L	Life	AC load: 10 million operations minimum (operating frequency 18,000 operations per hour) DC load: 20 million operations minimum (operating frequency 18,000 operations per hour)					
Operating Te (100% rated		-40 to +70°C (no freezing)					
Operating Hu	ımidity	5 to 85%RH (no condensation)					
Storage Tem	perature	-40 to +85°C (no freezing)					
Storage Hum	nidity	5 to 85%RH (no condensation)					
Weight (appr	ox.)	DPDT: 17g, DPST-NO: 16g					

RJ Series Slim Power Relay PC Board Terminal (bifurcated contacts)

Dimensions

RJ22V-C-*




29 max


(28.8)

Mounting Hole Layout

RJ22V-C-*



RJ22V-A-*




All dimensions in mm.


(12.7)

Internal Circuit Diagram (Bottom View)


RJ22V-C-*





RJ22V-A-*



Operating Temperature and Coil Temperature Rise







- The slanted dashed line indicates the allowable temperature rise for the coil at different ambient temperatures.
- The above temperature rise curves show the characteristics when 100% of the rated coil voltage is applied.


⚠ Safety Precautions

- Turn off the power to the RJ relay before starting installation, removal, wiring, maintenance, and inspection. Failure to turn power off may cause electrical shock or fire hazard.
- Observe the specifications and rated values, otherwise electrical shock or fire hazard may be caused.
- Use wires of the proper size to meet the voltage and current requirements.
- Tighten terminal screws to a proper tightening torque.

Instructions


1. Driving Circuit for Relays

- To make sure of correct relay operation, apply rated voltage to the relay coil.
- 2. Input voltage for DC coil: Complete DC voltage is best for the coil power to make sure of stable operation. When using a power supply containing a ripple voltage, suppress the ripple factor within 5%. When power is supplied through a rectification circuit, relay operating characteristics, such as pickup voltage and dropout voltage, depend on the ripple factor. Connect a smoothing capacitor for better operating characteristics as shown below.




Emax = Maximum of pulsating current
Emin = Minimum of pulsating current
Emean = DC mean value

3. Operating the relay in sync with an AC load: If the relay operates in sync with AC power voltage of the load, the relay life may be reduced. If this is the case, select a relay in consideration of the required reliability for the load. Or, make the relay turn on and off irrespective of the AC power phase or near the point where the AC phase crosses zero voltage.




4. Leakage current while relay is off:




When driving an element at the same time as the relay operation, special consideration is needed for the circuit design. As shown in the incorrect circuit below, leakage current (lo)

- flows through the relay coil while the relay is off. Leakage current causes coil release failure or adversely affects the vibration resistance and shock resistance. Design a circuit as shown in the correct example.
- 5. Surge suppression for transistor driving circuits: When the relay coil is turned off, a high-voltage pulse is generated. Be sure to connect a diode to suppress the counter electromotive force. Then, the coil release time becomes slightly longer. To shorten the coil release time, connect a Zener diode between the collector and emitter of the controlling transistor. Select a Zener diode with a Zener voltage slightly higher than the power voltage.




2. Protection for Relay Contacts

- The contact ratings show maximum values.
 Make sure that these values are not exceeded.
 When an inrush current flows through the load, the contact may become welded. If this is the case, connect a contact protection circuit, such as a current limiting resistor.
- 2. Contact protection circuit: When switching an inductive load, arcing causes carbides to form on the contacts, resulting in increased contact resistance. In consideration of contact reliability, contact life, and noise suppression, use of a surge absorbing circuit is recommended. Note that the release time of the load becomes slightly longer. Check the operation using an actual load. Incorrect use of a contact protection circuit will adversely affect switching characteristics. Four



Do not use a contact protection circuit as shown below:



Generally, switching a DC inductive load is more difficult than switching a DC resistive load. Using an appropriate arc suppressor will improve the switching characteristics of a DC inductive load.

3. Notes on PC Board Mounting

- When mounting 2 or more relays on a PC board, keep a minimum spacing of 5 mm in each direction.
- Manual soldering: Solder the terminals at 350°C within 3 sec., using a soldering iron of 60W (Sn-Ag-Cu type) is recommended.
- Auto-soldering: Solder at 250°C within 4 to 5 sec.
- Because the terminal part is filled with epoxy resin, do not excessively solder or bend the terminal. Otherwise, air tightness will degrade.
- terminal. Otherwise, air tightness will degrade.

 Avoid the soldering iron from touching the relay cover or the epoxy filled terminal part.
- · Use a non-corrosive resin flux.

4. Others

1. General notice:

- To maintain the initial characteristics, do not drop or shock the relay.
- The relay cover cannot be removed from the base during normal operation. To maintain the initial characteristics, do not remove the relay cover.
- Use the relay in environments free from dust, sulfur dioxide (SO₂), hydrogen sulfide (H₂S), or organic gases.
- Make sure that the coil voltage does not exceed the applicable coil voltage range.
- Connecting outputs to electronic circuits:
 When the output is connected to a load which
 responds very quickly, such as an electronic
 circuit, contact bouncing causes incorrect
 operation of the load. Take the following
 measures into consideration.
 - a. Connect an integration circuit.
 - b. Suppress the pulse voltage due to bouncing within the noise margin of the load.
- Do not use relays in the vicinity of strong magnetic fields, as this may affect relay operation.

Specifications and other descriptions in this catalog are subject to change without notice.



IDEC CORPORATION

7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan Tel: +81-6-6392-9731 E-mail: marketing@idec.co.jp

IDEC CORPORATION (USA) Tel: +1-408-747-0550 / (800) 262-IDEC (4332) Fax: +1-408-744-9055 / (800) 635-6246

E-mail: opencontact@idec.com IDEC CANADA LIMITED Tel: +1-905-890-8561, Toll Free: (888) 317-4332

Fax: +1-905-890-8562 E-mail: sales@ca.idec.com IDEC AUSTRALIA PTY. LTD.

Tel: +61-3-8523-5909, Toll Free: 1800-68-4332 Fax: +61-3-8523-5999 E-mail: sales@au.idec.com IDEC ELECTRONICS LIMITED
Tel: +44-1256-321000, Fax: +44-1256-327755
E-mail: sales@uk.idec.com

IDEC ELEKTROTECHNIK GmbH Tel: +49-40-25 30 54 - 0, Fax: +49-40-25 30 54 - 24 E-mail: service@idec.de

IDEC (SHANGHAI) CORPORATION
Tel: +86-21-5353-1000, Fax: +86-21-5353-1263

IDEC (BEIJING) CORPORATION
Tel: +86-10-6581-6131, Fax: +86-10-6581-5119
IDEC (SHENZHEN) CORPORATION
Tel: +86-755-8356-2977. Fax: +86-755-8356-2944

IDEC IZUMI (H.K.) CO., LTD. Tel: +852-2803-8989, Fax: +852-2565-0171 E-mail: info@hk.idec.com

IDEC TAIWAN CORPORATION Tel: +886-2-2698-3929, Fax: +886-2-2698-3931 E-mail: service@tw.idec.com

IDEC IZUMI ASIA PTE. LTD. Tel: +65-6746-1155, Fax: +65-6844-5995 E-mail: info@sg.idec.com

(110620)