## **Switch Mode Power Supply** S8VS (15/30/60/90/120/180/240/480-W Models)

CSM\_S8VS\_DS\_E\_6\_1

## 60/90/120/180/240/480-W Models

## Improved Versions of **Standard-type Power Supplies without Indication** Monitor (60 to 240 W). **EMI Class B Compliant.**

- New 90-W models that conform to UL Class 2 standards.
- New models with screwless terminal blocks and without indication monitor (except that 480-W models have an indication monitor).
- Status displayed on 3-digit, 7-segment display.

# 222 CEE

111

- · Safety standards: UL508/60950-1, CSA C22.2 No. 14/60950-1
  - (15-W, 30-W, 60-W to 240-W models with Indication monitor), CSA C22.2 No. 107.1/60950-1 (60-W to 240-W standard, 480-W models),
  - EN 50178 (= VDE0160),
- EN 60950-1 (= VDE0805 Teil 1)
- Compact:  $150 \times 115 \times 127.2$  mm (W  $\times$  H  $\times$  D) (480-W models).

## 15/30-W Models

## **Compact, Thin Power Supplies That Mount Just About Anywhere** to Contribute to Control Panel Downsizing

- Compact and thin:  $22.5 \times 85 \times 96.5$  mm (W  $\times$  H  $\times$  D).
- Three mounting directions (standard, horizontal, facing horizontal).
- Mounting directly to the panel is possible.
- · Safety standards: UL508/60950-1/1604, cUL: CSA C22.2 No. 14/60950-1/213, EN50178 (= VDE0160), EN60950-1 (= VDE0805 Teil 1).

## Features Common to All Models

- Mount to DIN Rail.
- Complies with SEMI F47-0200 (200-VAC input).
- RoHS-compliant.





## **Model Number Structure**

#### Model Number Legend

Note: Not all combinations are possible. Refer to List of Models in Ordering Information, below.

S8VS-				]	-
	1	2	34	5	6

#### 1. Power Ratings

015: 15 W 030: 30 W 060: 60 W 090: 90 W 120: 120 W 180: 180 W 240: 240 W 480: 480 W

#### 2. Output voltage

- 05: 5 V
- 12: 12 V
- 24: 24 V

#### 3. Indication monitor

- None: Without indication monitor (standard model)
- A: With indication monitor (maintenance forecast monitor)
- B: With indication monitor (total run time monitor)

#### 4. Alarm output

- None: Sinking \* P:
- Sourcing

Note: No alarm output possible with 60-W models.

\* Both sinking and sourcing outputs are available for 480-W models.

#### 5. UL Class 2 Standards

- None: Does not conform. \*
- S: Conforms.
- \*15-W, 30-W, and 60-W models conform to Class 2 standards.

#### 6. Terminal Block Form

- None: Screw terminal block
- F: Screwless terminal block

## **Ordering Information**

#### **List of Models**

Note: For details on normal stock models, contact your nearest OMRON representative.

#### Models without Indication Monitor (Standard Models)

Power ratings	Input voltage	Output voltage	Output current	Model number (screw terminal block)	Model number (screwless terminal block)	
		5 V	2.0 A	S8VS-01505 *1		
15 W		12 V	1.2 A	S8VS-01512		
		24 V	0.65 A	S8VS-01524		
	-	5 V	4.0 A	S8VS-03005 *2		
30 W		12 V	2.5 A	S8VS-03012		
		24 V	1.3 A	S8VS-03024		
60 W	-		2.5 A	S8VS-06024	S8VS-06024-F	
00.10/	100 to 240 VAC		3.75 A	S8VS-09024	S8VS-09024-F	
90 W				S8VS-09024S	S8VS-09024S-F	
120 W	-		5 A	S8VS-12024	S8VS-12024-F	
180 W	-	24 V	7.5 A	S8VS-18024	S8VS-18024-F	
240 W			10 A	S8VS-24024	S8VS-24024-F	
480 W			20 A Peak current 30 A (200 VAC)	S8VS-48024	S8VS-48024-F	

**\*1.** The output capacity of the S8VS-01505 is 10 W.

## **\*2.** The output capacity of the S8VS-03005 is 20 W.

#### Models with Indication Monitor (Maintenance Forecast Monitor)

Power ratings	Input voltage	Output voltage	Output current	Alarm output	Model number (screw terminal block)	Model number (screwless terminal block)	
60 W		0 VAC 24 V	2.5 A		S8VS-06024A		
90 W			3.75 A	Sinking	S8VS-09024A		
90 W				Sourcing	S8VS-09024AP	*	
120 W			5 A	Sinking	S8VS-12024A		
120 W				Sourcing	S8VS-12024AP		
100.10	100 to 240 VAC		7.5 A	Sinking	S8VS-18024A		
180 W				Sourcing	S8VS-18024AP		
240 W			10 A	Sinking	S8VS-24024A		
240 W				Sourcing	S8VS-24024AP		
480 W			20 A Peak current 30 A (200 VAC)	Sinking/ sourcing	S8VS-48024A	S8VS-48024A-F	


#### Models with Indication Monitor (Total Run Time Monitor)

Power ratings	Input voltage	Output voltage	Output current	Alarm output	Model number (screw terminal block)	Model number (screwless terminal block)	
60 W		o 240 VAC 24 V	2.5 A		S8VS-06024B	_	
90 W			3.75 A	Sinking	S8VS-09024B		
90 W				Sourcing	S8VS-09024BP		
120 W			5 A	Sinking	S8VS-12024B		
120 W				Sourcing	S8VS-12024BP		
180 W	100 to 240 VAC		7.5 A	Sinking	S8VS-18024B		
180 W	-			Sourcing	S8VS-18024BP		
240 W			10 A	Sinking	S8VS-24024B		
240 W				Sourcing	S8VS-24024BP		
480 W			20 A Peak current 30 A (200 VAC)	Sinking/ sourcing	S8VS-48024B	S8VS-48024B-F	


Note: Refer to pages 27 to 28 for the options that available.

		Power ratings		240 W			480 W			
Item		Туре	Standard	Maintenance forecast monitor	Total run time monitor	Standard	Maintenance forecast monitor	Total run time monitor		
Efficiency (	typical)		80% min.	10100000111011101		83% min.	101000011101101			
	Voltage *1		100 to 240 VAC (	85 to 264 VAC)		1				
	Frequency *1		50/60 Hz (47 to 63 Hz)							
	Current	100-V input	3.8 A max.	3.8 A max. 7.4 A max.						
	Current	200-V input	2.0 A max.	2.0 A max. 3.9 A max.						
Input	Power factor		0.95 min.							
	Harmonic current emission	1	Conforms to EN6	1000-3-2						
	Leakage current	100-V input	0.5 mA max.							
		200-V input 100-V input	1.0 mA max. 25 A max. (for a cold start at 25°C)							
	Inrush current *2	200-V input	50 A max. (for a cold start at 25°C)							
	Mallan	-	Models with indication monitor: ±10% (with V.ADJ)							
	Voltage adjustment range :	*3	Standard models	: -10% to 15% (with V.	ADJ)	-10% to 15% (W	itn v.ADJ)			
	Ripple		2.0% (p-p) max. (at rated input/output voltage)							
<b>.</b>	Input variation influence		0.5% max. (at 85- to 264-VAC input, 100% load)							
Output	Load variation influence (rated input voltage)		1.5% max. (with r	rated input, 0 to 100% lo	oad)					
	Temperature variation influ	ience	0.05%/°C max.							
	Startup time *2		1,000 ms max. (a	t rated input/output volt	age)					
	Hold time *2		20 ms min. (at ra	ted input/output voltage	)					
	Overload protection *2			rated load current, volt	age drop, automatic res	et				
	Overvoltage protection *2,		Yes			1				
	Output voltage indication *		No	Yes (selectable) *6		No	Yes (selectable) *6			
	Output current indication *		No	Yes (selectable) *7		No	Yes (selectable) *7			
	Peak-hold current indicatio		No No	Yes (selectable) *8 Yes (selectable)	No	No	Yes (selectable) *8 Yes (selectable)	No		
	Maintenance forecast monitor indication *5 Maintenance forecast monitor output		No	Yes (transistor output), 30 VDC	No		Yes (transistor output), 30 VDC	No		
Additional functions			-	max., 50 mA max. *9		1	max., 50 mA max.			
Tunctions	Total run time monitor indication *5		No Yes (selectable) Yes (transistor				Yes (selectable) Yes (transistor			
	Total run time monitor output *5		No			No output), 3		output), 30 VDC max., 50 mA max. *9		
	Undervoltage alarm indication *5		No	Yes (selectable)		No		Yes (selectable)		
	Undervoltage alarm output terminals		No	Yes (transistor output) max. *9	es (transistor output), 30 VDC max., 50 mA No			Yes (transistor output), 30 VDC max., 50 mA max. *9		
	Parallel operation		No							
	Series operation		Yes for up to 2 Power Supplies (with external diode)							
	Operating ambient tempera	ature	Refer to the derating curve in Engineering Data (60-W, 90-W, 120-W, 180-W, 240-W, and 480-W Models). (with no icing or condensation)							
	Storage temperature		-25 to 65°C							
	Operating ambient humidit	у	25% to 85% (Storage humidity: 25% to 90%)							
	Dielectric strength		<ul> <li>3.0 kVAC for 1 min. (between all inputs and outputs/alarm outputs; detection current: 20 mA)</li> <li>2.0 kVAC for 1 min. (between all inputs and PE terminals; detection current: 20 mA)</li> <li>1.0 kVAC for 1 min. (between all outputs/ alarm outputs and PE terminals; detection current for standard 240-W and 480-W models: 30 mA, detection current for 240-W models with indication monitor: 20 mA)</li> <li>500 VAC for 1 min. (between all outputs and alarm outputs; detection current: 20 mA)</li> </ul>							
	Insulation resistance		100 M $\Omega$ min. (between all outputs/ alarm outputs and all inputs/ PE terminals) at 500 VDC							
	Vibration resistance		10 to 55 Hz, 0.375-mm single amplitude for 2 h each in X, Y, and Z directions 10 to 150 Hz, 0.35-mm single amplitude (5 G max.) for 80 min each in X, Y, and Z directions: 240 W 10 to 150 Hz, 0.35-mm single amplitude (3 G max.) for 80 min each in X, Y, and Z directions: 480 W							
	Shock resistance		150 m/s <sup>2</sup> , 3 times each in ±X, ±Y, and ±Z directions							
	Output indicator		Yes (color: green)							
Other		Conducted Emissions	Models with indication monitor: Conforms to EN61204-3 EN55011 Class A and based on FCC Class A, Conforms to EN61204-3 EN55011 Class B *11 Standard models: Conforms to EN61204-3 EN55011 Group 1 Class B and based on FCC Class A			Conforms to EN61204-3 EN55011 Class A and based on FCC Class A Conforms to EN61204-3 EN55011 Class B *11				
	EMI	Radiated Emissions	Models with indication monitor: Conforms to EN61204-3 EN55011 Class A, Conforms to EN61204-3 EN55011 Class B *11 Standard models: Conforms to EN61204-3 EN55011 Group 1 Class B			Conforms to EN61204-3 EN55011 Class A Conforms to EN61204-3 EN55011 Class B <b>*</b> 11				
	EMS		Conforms to EN61204-3 high severity levels							
	Approved standards		UL: UL508 (Listing), UL60950-1 cUL for 240-W models with indication monitor: CSA C22.2 No.14, cUL for 240-W standard models and 480-W models: CSA C22.2 No.107.1, cUR: CSA No. 60950-1, EN/VDE: EN50178 (=VDE0160), EN00950-1 (SELV) (=VDE0805 Teil 1) According to VDE0106/P100, IP20 (except terminal block) KOSHA S Mark *10							
	SEMI		F47-0200 (200-V	AC input)		1				
	Weight		Weight         1,150 g max.         1,700 g max.           r to page 5 for notes 1 to 11.         1,700 g max.         1,700 g max.							

Note: Refer to page 5 for notes 1 to 11.




Note: The illustration shows the S8VS-24024A model.




### **Power Supplies with Screwless Terminal Blocks**

#### S8VS-06024-F (60 W)









S8VS-09024-F (90 W) S8VS-09024S-F (90 W) S8VS-12024-F (120 W)







Note: The illustration shows the S8VS-12024-F model.