
EE-SPX301/401 EE-SPY30/40

Photomicrosensor with light modulation is not influenced by external light.

- Voltage-output models with wide operating voltage range (5 to 24 VDC).
- Fitted with an easy-to-adjust optical axis mark.
- Easy adjustment and optical axis monitoring with a light indicator.





Be sure to read *Safety Precautions* on page 5.

((

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensing distance	Output type	Output configuration	Model
E MAN L	Through-beam type (with slot)			Dark-ON	EE-SPX301
		3.6 mm (slot width)		Light-ON	EE-SPX401
Horizontal type	Reflective type		NPN output	Dark-ON	EE-SPY301
Ø ARSAL L		5 mm		Light-ON	EE-SPY401
Vertical type	Reflective type			Dark-ON	EE-SPY302
		5 mm		Light-ON	EE-SPY402

Accessories (Order Separately)

Туре		Cable length	Model	Remarks
Connector			EE-1002	
Connector	Connector with Cable	1 m	EE-1003	
NPN/PNP Conversion Connector 0.46 m (total length)		EE-2001		
Connector Hold-down Clip			EE-1003A	For EE-1003 only.


OMRON

EE-SPX301/401 EE-SPY30/40


Ratings and Specifications


Sensing	method	Through-beam type (with slot)	Reflective type	
Item	Models	EE-SPX301, EE-SPX401	EE-SPY301, EE-SPY401 EE-SPY302, EE-SPY402	
Sensing distance		3.6 mm (slot width)	5 mm (Reflection factor: 90%; white paper 15 × 15 mm) *1	
Sensing object		Opaque: 1 × 0.5 mm min.		
Differential distance		0.05 mm max.	0.2 mm max. (with a sensing distance of 3 mm, horizontally)	
Light source		GaAs infrared LED with a peak wavelength of 940 nm		
Indicator *2		Light indicator (red)		
Supply voltage		5 to 24 VDC ±10%, ripple (p-p): 5% max.		
Current consumption		Average: 15 mA max., Peak: 50 mA max.		
Control output	NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max.			
Response frequency *3		500 Hz min.	100 Hz min.	
Ambient illumination		3,000 lx max. with incandescent light or sunlight on the surface of the receiver		
Ambient temperature range		Operating: -10 to +55°C Storage: -25 to +65°C (with no icing)		
Ambient humidity range		Operating: 5% to 85% Storage: 5% to 95% (with no condensation)		
Vibration resistance Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions		or 2 h each in X, Y, and Z directions		
Shock resistance		Destruction: 500 m/s² for 3 times each in X, Y, and Z directions		
Enclosure rating		IEC IP50		
Connecting method		Special connector (soldering not possible)		
Weight		Approx. 2.6 g		
Material Ca	se	Polycarbonate		

- *1. Operation may not be possible near the Sensor.
 *2. The indicator is a GaP red LED (peak wavelength: 700 nm).
 *3. The response frequency was measured by detecting the following rotating disk.









I/O Circuit Diagrams

NPN Output

Model	Output configuration	Timing charts	Output circuit
EE-SPX401 EE-SPY401 EE-SPY402	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases Load 2	Light indicator (red) 1.5 to 3 mA Load 1 Main T 5 to 24 VDC
EE-SPX301 EE-SPY301 EE-SPY302	Dark-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases Load 2 H	* Voltage output (when the sensor is connected to a transistor circuit)

Safety Precautions

Refer to Warranty and Limitations of Liability.



This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes



Precautions for Correct Use

Make sure that this product is used within the rated ambient environment conditions.


Mounting

The sensing distance for the EE-SPY Reflective-type Photomicrosensor with built-in amplifier varies from 8 to 20 mm depending on the product (90% reflective white paper). Do not place glossy objects in the background of the sensing object.

Wiring

- Connection is made using a connector. Do not solder to the pins (leads).
- When extending the cable, use an extension cable with conductors having a total cross-section area of 0.3 mm². The total cable length must be 2 m maximum.
- To use a cable length longer than 2 m, attach a capacitor with a capacitance of approximately 10 μ F to the wires as shown below. The distance between the terminal and the capacitor must be within 2 m

(Use a capacitor with a dielectric strength that is at least twice the Sensor's power supply voltage.)






Dimensions (Unit: mm)

Sensors









Terminal Arrangement

(1)	\oplus	Vcc
(2)	OUT	OUTPUT
(3)	Θ	GND (0 V)

EE-SPY301 EE-SPY401









Terminal Arrangement

(1)	⊕	Vcc
(2)	OUT	OUTPUT
(3)	\oplus	GND (0 V)

EE-SPY302 EE-SPY402







Terminal Arrangement

(1)	\oplus	Vcc
(2)	OUT	OUTPUT
(3)	\ominus	GND (0 V)

Accessories (Order Separately)