

GT3W Series — **Dual Time Range Timers**



Key features of the GT3W series include:

- Sequential start, sequential interval, on-delay, recycler, and interval ON timing functions
- 2 time settings in one timer
- 8 selectable operation modes on each model
- Mountable in sockets or flush panel
- Power and output status indicating LEDs
- Time ranges up to 300 hours



c-uL Listed UL Listed File No.E55996



			Ge	neral Specifications		
Operation System				Solid state CMOS Circuit		
Operation Type				Multi-Mode		
Time Range				1: 0.1sec to 6hours, 3: 0.1sec to 300hours		
Pollution Degree				2 (IE60664-1)		
	Itage cat			III (IE60664-1)		
			AF20	100-240V AC(50/60Hz)		
	perationa	al	AD24	24V AC(50/60Hz)/24V DC		
Voltage)		D12	12V DC		
			AF20	85-264V AC(50/60Hz)		
Voltage	Tolerand	e	AD24	20.4-26.4V AC(50/60Hz)/21.6-26.4V DC		
·			D12	10.8-13.2V DC		
Disengaging value of Input Voltage			t	Rated Voltage x10% minimum		
Range of Ambient Operating Temperature			ng	-10 to +50°C (without freezing)		
Range of Ambient Storage and Transport Temperature			and	-30 to +75°C (without freezing)		
Range o	of Relative	e Humidit	у	35 to 85%RH (without condensation)		
Atmosp	heric Pre	ssure		80kPa to 110kPa (Operating), 70kPa to 110kPa (Transport)		
Reset T	ime			60msec maximum		
Repeat	Error			±0.2%, ±10msec*		
Voltage	Error			±0.2%, ±10msec*		
Temper	ature Erro	or		±0.6%, ±10msec*		
Setting	Error			±10% maximum		
Insulati	on Resist	ance		100MΩ minimum (500V DC)		
Dielect	ric Streng	jth		Between power and output terminals: 2000V AC, 1 minute Between contacts of different poles: 2000V AC, 1 minute Between contacts of the same pole:750V AC, 1 minute		
Vibratio	n Resista	ince		10 to 55Hz amplitude 0.75mm2 hours in each of 3 axes		
Shock I	Resistanc	e		Operating extremes: 98m/sec ² (approx.10G) Damage limits: 490m/sec ² (approx. 50G) 3 times in each of 3 axes		
Degree	of Protec	tion		IP40 (enclosure), IP20 (socket) (IEC60529)		
		100V AC/60Hz		2.3VA		
Power Consumption (Approx.)	AF20	200V AC/60Hz		4.6VA		
Pow Cons App	AD24 (AC/DC)			1.8VA/0.9W		
Mounting Position				Free		
Dimensions				40Hx 36W x 70 mm		
Weight (Approx.)				72g		

Contact Ratings						
Allowa	able Contact Power	960VA/120W				
Allowa	able Voltage	250V AC/150V DC				
Allowa	able Current	5A				
	num permissible ing frequency	1800 cycles per hour				
		1/8HP, 240V AC				
Rated	l nad	3A, 240V AC (Resistive)				
Rated Load		5A, 120V AC/30V DC (Resistive)				
Condit	ional Short Circuit	Fuse 5A, 250V				
Life	Electrical	100,000 op. minimum (Resistive)				
	Mechanical	20.000.000 op. minimum				

GT3W Table of Contents

 $Specifications -\!\!\!\!\!- G-44$

Part Number List — G-45

Timing Diagrams / Schematics — G-46

Instructions: Setting Timer — G-47

GT3 Accessories — G-48

GT3 Instructions — G-50

GT3 Dimensions — G-52

Timing Diagrams Overview — G-4

^{**} For the value of the error against a preset time, whichever the largest.

IDEC Timers

Part Number List

Part Numbers

Mode of Operation	Output	Contact	Time Range*	Rated Voltage	Pin Configuration	New Part Numbers
	3A, 240V AC 5A, 120V AC/30V DC (Resistive Load)		1: 0.1sec - 6 hours *(See Time Range Settings for details.)	100 to 240V AC (50/60Hz)	8 pin	GT3W-A11AF20N
A: Sequential Start				100 to 240V AC (50/60H2)	11 pin	GT3W-A11EAF20N
B: On-delay with course & fine C: Recycler &				24V AC/DC	8 pin	GT3W-A11AD24N
instaneous D: Recycler outputs (OFF Start)					11 pin	GT3W-A11EAD24N
E: Recycler outputs (ON Start) F: Interval ON				12V DC	8 pin	GT3W-A11D12N
G: Interval ON Delay H: Sequential					11 pin	GT3W-A11ED12N
Interval			3: 0.1sec - 300 hours	100 to 240V AC (50/60Hz)		GT3W-A33AF20N
				24V AC/DC	8 pin	GT3W-A33AD24N




- 1. For schematics, see page G-46.
- $2.\ For\ socket\ and\ accessory\ part\ number\ information,\ see\ page\ G-48.$
- 3. 8- and 11-pin models differ only in the number of pins (extra pins are not used).
- 4. For the timing diagram overview, see page G-4.
- 5. *For details on setting time ranges, see the instructions on page G-47.


Time Range Table


Tim	e Range	Code: 1	Time Range Code: 3			
Time Range Selector		Time Range	Time Range Selector	Scale	Time Range	
1S		0.1 sec - 1 sec	1S		0.1 sec - 3 sec	
10S	0-1	0.3 sec - 10 sec	1M	0 - 3	3 sec - 3 min	
10M		15 sec - 10 min	1H		3 min - 3 hours	
1\$		0.1 sec - 6 sec	1S		0.6 sec - 30 sec	
10S		1 sec - 60 sec	1M		36 sec - 30 min	
1M	0 - 6	6 sec - 6 min	1H	0 - 30	36min - 30 hours	
10M		1 min - 60 min	10H		6 hours - 300 hours	
1H		6 min - 6 hours	1011		6 flours - 300 flours	




Timing Diagrams/Schematics







Instructions: Setting GT3W Timer



- 1. The switches should be securely turned using a flat screwdriver 4mm wide (maximum). Note that incorrect setting may cause malfunction. The switches, which do not turn infinitely, should not be turned beyond their
- 2. Since changing the setting during timer operation my cause malfunction, turn power off before changing.

Safety Precautions

Special expertise is required to use Electronic Timers.

DEC Timers

- All Electronic Timer modules are manufactured under IDEC's rigorous quality control system, but users must add a backup or fail safe provision to the control system when using the Electronic Timer in applications where heavy damage or personal injury may occur should the Electronic Timer fail.
- Install the Electronic Timer according to instructions described in this catalog.
- Make sure that the operating conditions are as described in the specifications. If you are uncertain about the specifications, contact IDEC in advance.
- In these directions, safety precautions are categorized in order of importance to Warning and Caution.

Warning

Warning notices are used to emphasize that improper operation may cause sever personal injury or death.

- Turn power off to the Electronic timer before starting installation, removal, Wiring, maintenance, and inspection on the Electronic
- Failure to turn power off may cause electrical shocks or fire hazard.
- Emergency stop and interlocking circuits must be configured outside the Electronic timer. If such a circuit is configured inside the Electronic Timer, failure of the Electronic timer may cause malfunction of the control system, or an accident.

Caution

Caution notices are used where inattention might cause personal injury or damage to equipment.

- The Electronic Timer is designed for installation in equipment. Do not install the Electronic Timer outside equipment.
- Install the Electronic Timer in environments described in the specifications. If the Electronic Timer is used in places where it will be subjected to high-temperature, high-humidity, condensation, corrosive gases, excessive vibrations, or excessive shocks, then electrical shocks, fire hazard, or malfunction could result.
- Use an IEC60127-approved fuse and circuit breaker on the power and output line outside the Electronic Timer.
- Do not disassemble, repair, or modify the Electronic Timer.
- When disposing of the Electronic Timer, do so as industrial waste.



Accessories: GT3 Series


DIN Rail Mounting Accessories


Part Numbers: DIN Rail/Surface Mount Sockets and Hold-Down Springs

Part Numbers: DIN Ra	Applicable Hold-Down Springs				
Style	Appearance	Use with Timers	Part No.	Appearance	Part No.
8-Pin Screw Terminal (dual tier)		GT3A-1, 2, 3 (8-pin) GT3D-1, 2, 3 (8-pin) GT3F-1, 2 (8-pin) GT3W (8-pin) GT3S	SR2P-05		SFA-203
11-Pin Screw Terminal (dual tier)		GT3A-1, 2, 3 (11-pin) GT3A-4, 5, 6 GT3D-1, 2, 3 (11-pin) GT3D-4, 8 GT3F-1, 2 (11-pin) GT3W (11-pin)	SR3P-05		
8-Pin Fingersafe Socket		GT3A-1, 2, 3 (8-pin) GT3D-1, 2, 3 (8-pin) GT3F-1, 2 (8-pin) GT3W (8-pin) GT3S	SR2P-05C	A ASS	31A-203
11-Pin Fingersafe Socket		GT3A-1, 2, 3 (11-pin) GT3A-4, 5, 6 GT3D-1, 2, 3 (11-pin) GT3D-4, 8 GT3F-1, 2 (11-pin) GT3W (11-pin)	SR3P-05C		
8-Pin Screw Terminal	ECEC .	GT3A-1, 2, 3 (8-pin) GT3D-1, 2, 3 (8-pin) GT3F-1, 2 (8-pin) GT3W (8-pin) GT3S	SR2P-06	A 40	
11-Pin Screw Terminal	ELECTION OF THE PARTY OF THE PA	GT3A-1, 2, 3 (11-pin) GT3A-4, 5, 6 GT3D-1, 2, 3 (11-pin) GT3D-4, 8 GT3F-1, 2 (11-pin) GT3W (11-pin)	SR3P-06	de son	SFA-202
DIN Mounting Rail Length 1000mm			BNDN1000		


Installation of Hold-Down Springs

DIN Rail Mount Socket





Panel Mount Socket



IDEC Timers

Panel Mounting Accessories

Part Numbers: Panel Mount Sockets and Hold-Down Springs

	Panel Mount S	Applicable HD Springs			
Style	Appearance	Use with Timers	Part No.	Appearance	Part No.
8-Pin Solder Terminal	1861	GT3A- (8-pin) GT3D- (8-pin) GT3W- (8-pin) GT3F- (8-pin) GT3S	SR2P-51	Α	
11-Pin Solder Terminal	() 500 () 500	GT3A- (11-pin) GT3D- (11-pin) GT3W- (11-pin) GT3F- (11-pin)	SR3P-51		SFA-402



1. For information on installing the hold-down springs, see page G-48.


Part Numbers: Flush Panel Mount Adapter and Sockets that use an Adapter

Accessory	lush Panel Mount Adapter and Description	Appearance	Use with Timers	Part No.
Panel Mount Adapter	Adaptor for flush panel mounting GT3 timers		All GT3 timers	RTB-G01
	8-pin screw terminal		All 8-pin timers	SR6P-M08G
	11-pin screw terminal	(Shown: SR6P-M08G for Wiring Socket Adapter)	All 11-pin timers	SR6P-M11G
Sockets for use with Panel Mount Adapter	8-pin solder terminal		All 8-pin timers	SR6P-S08
	11-pin solder terminal		All 11-pin timers	SR6P-S11



2. No hold down springs are available for flush panel mounting.

Dimensions: GT3 Series



NOTE: GT3W series are UL Listed when used in combination


with following IDEC's sockets: GT3W-A11, A33: SR2P-06*

GT3W-A11, A33: SR2P-06* pin type socket. GT3W-A11E, A33: SR3P-05* pin type socket.


(*-May be followed by A,B,C or U)
The socket to be used with these timers are rated:

- -Conductor Temperature Rating 60°C min.
 -Use 14AWG max.(2mm²max.) Copper conductors only
- -Terminal Torque 1.0 to 1.3 N-m


Analog GT3 Timer, 8-Pin with SR2P-06




Analog GT3 Timer, 11-Pin with SR3P-06




Digital GT3 Timer, 8-Pin with SR2P-06




Digital GT3 Timer, 11-Pin with SR3P-06



Analog GT3 Timer, 11-Pin with SR3P-05




Digital GT3 Timer, 11-Pin with SR3P-05




IDEC Timers

Panel Mount Adapter


Analog GT3 Timer, 8-Pin and 11-Pin with SR6P-S08 or SR6P-S11




Digital GT3 Timer, 8-Pin and 11-Pin with SR6P-S08 or SR6P-S11




Mounting Hole Layout



Analog and Digital GT3 Timer, 8-Pin with SR6P-M08G



Analog and Digital GT3 Timer, 11-Pin with SR6P-M11G





General Instructions for All Timer Series

Load Current

With inductive, capacitive, and incandescent lamp loads, inrush current more than 10 times the rated current may cause welded contacts and other undesired effects. The inrush current and steady-state current must be taken into consideration when specifying a timer.

Contact Protection

Switching an inductive load generates a counter-electromotive force (back EMF) in the coil. The back EMF will cause arcing, which may shorten the contact life and cause imperfect contact. Application of a protection circuit is recommended to safeguard the contacts.

Temperature and Humidity

Use the timer within the operating temperature and operating humidity ranges and prevent freezing or condensation. After the timer has been stored below its operating temperature, leave the timer at room temperature for a sufficient period of time to allow it to return to operating temperatures before use

Environment

Avoid contact between the timer and sulfurous or ammonia gases, organic solvents (alcohol, benzine, thinner, etc.), strong alkaline substances, or strong acids. Do not use the timer in an environment where such substances are prevalent. Do not allow water to run or splash on the timer.

Vibration and Shock

Excessive vibration or shocks can cause the output contacts to bounce, the timer should be used only within the operating extremes for vibration and shock resistance. In applications with significant vibration or shock, use of hold down springs or clips is recommended to secure a timer to its socket.

Time Setting

The time range is calibrated at its maximum time scale; so it is desirable to use the timer at a setting as close to its maximum time scale as possible. For a more accurate time delay, adjust the control knob by measuring the operating time with a watch before application.

Input Contacts

Use mechanical contact switch or relay to supply power to the timer. When driving the timer with a solid-state output device (such as a two-wire proximity switch, photoelectric switch, or solid-state relay), malfunction may be caused by leakage current from the solid-state device. Since AC types comprise a capacitive load, the SSR dielectric strength should be two or more times the power voltage when switching the timer power using an SSR.

Generally, it is desirable to use mechanical contacts whenever possible to apply power to a timer or its signal inputs. When using solid state devices, be cautious of inrushes and back-EMF that may exceed the ratings on such devices. Some timers are specially designed so that signal inputs switch at a lower voltage than is used to power the timer (models designated as "B" type).

Timing Accuracy Formulas

Timing accuracies are calculated from the following formulas:

Repeat Error

= ± 1 x Maximum Measured Value – Minimum Measured Value x 100%

Maximum Scale Value

Voltage Error

 T_{v} : Average of measured values at voltage V T_{r} : Average of measured values at the rated voltage

Temperature Error

$$=\pm \frac{\text{Tt} - \text{T20}}{\text{T20}} \times 100\%$$

 T_t : Average of measured values at °C T_{20} : Average of measured values at 20°C

Setting Error

= ± <u>Average of Measured Values - Set Value</u> x 100% Maximum Scale Value