Oiltight Switches & Pilot Devices

HW Series - 22mm IEC Style Global Pushbuttons





HW: The Best Engineered Switch in the World Key features include:

- Locking lever removable contact blocks
- Finger-safe IP20 contacts as standard, other terminal styles available
- Tamperproof construction
- All E-stops meet EN418 and are compliant with SEMI S2 standards
- Worldwide approvals
- Easy to assemble
- Available assembled or as sub-components
- Choice of black plastic or metallic front bezels
- Incandescent or LED illumination
- Transformer or full voltage
- Slow make double break self cleaning contacts

IDEC's HW switches are "The best engineered switch in the world" for a reason. Carrying the CE mark, UL, CSA, CCC (Chinese), and TUV approvals, these switches are designed for use in almost any part of the world.

Complete with finger-safe contact blocks offering IP20 protection, these 7/8" (22mm) switches include illuminated and non-illuminated pushbuttons, pilot lights, selector switches, and emergency stop switches.

All switches also incorporate mechanically keyed safety locking levers, ensuring correct installation and maintaining safety in high-vibration applications.









Certificate No. 2005010305145656

Registration No. J9650511 (Pilot Lights)

IDEC Oiltight Switches & Pilot Devices

	Conforming to	Standa	rds		EN60947-1 EN609	47-5-1 \		50-200 11	508 09	SA (.22-2	No 14			
	Conforming to Standards Approvals			EN60947-1, EN60947-5-1, VDE0660-200, UL508, CSA C22-2 No.14										
	Approvals File No. E68961 File No. LR92374 Certificate No. 2005010305145656 TÜV Rheinland Registration No. R9551089 (E-stops) Registration No. J9551458 (all other switches) Registration No. J9550511 (Pilot Lights)				 CSA: pushbuttons and selector switches: A600 pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V) UL: pushbuttons and selector switches: A600 pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V) TÜV: pushbuttons and selector switches: A600=P600 (N0, NC)/Q600 (N0-EM, NC-LB) pilot lights and illuminated pushbuttons, direct supply pilot lights and illuminated pushbuttons with integral transformer (100/110, 115, 120, 200/220, 230, 240, 380, 400/440, 480V) 									
	Operating Temperature				Operation: –25 to +50°C (without freezing), Storage: –40 to +70°C (without freezing)									
	Vibration Resistance				10 to 55Hz, 98m/sec ² (10G) conforming to IEC6068-2-6									
	Shock Resistance				980m/sec ² (100G) conforming to IEC6068-2-7									
	Electric Shock Protection			Class 0 conformin	-									
	Degree of Protection (conforming to IEC60529) (conforming to NEMA ICS6-110)				IP65 (from front of the panel) IP20 (Type HW-F contact block) NEMA 1, 2, 3, 3R, 3S, 4, 4X, 5, 12, 13 (from front of panel)									
	Mechanical Li				Momentary pushb					-			ches: 500,	,000
	Pollution Degree (conforming to IEC60947-1)			3 for switches not using a transformer, 2 for switches using a transformer										
	Rated Operational Characteristics			AC-15: A600 or Ue = 250V, le = 3A (N0, NC, N0-EM, NC-LB) DC-13: P600 or Ue = 125V, le = 1.1A (N0, NC) DC-13: Q600 or Ue = 125V, le = 0.9A (N0-EM, NC-LB)										
		Rated Insulation Voltage			600V									
	Rated Impulse Withstanding Voltage Rated Thermal Current				Less than 4kV, conforming to IEC60947-1									
					4kV for contact circuit, 2.5kV for lamp circuit									
					10 Amp 5 mA at 3V AC/DC									
	Contact Operation			Slow break NC or NO, self-cleaning										
					5.5mm to 10mm travel to latch 45N minimum force to latch 10mm maximum travel 1,800 operations per hour maximum for a Pushlock Turn Reset 900 operations per hour maximum for a Push-Pull									
	Operating Force			Flush and extended pushbuttons—with 1NO or 1NC contact: 6.2±2N (momentary), 7.0±2N (main- tained) Additional contacts—1NO or 1NC: +3.2N (momentary), + 3.3N (maintained)										
	Terminal Refer	Terminal Referencing			Conforming to CENELEC EN50005									
		Recommended Terminal Torque				0.8 N m (7.1 in lb.)								
	External Short		Protection	1	10A 250V fuse conforming to IEC60269-1									
	Applicable Wire Size				Minimum 1 x 22 AWG, max. 2 x 14 AWG or 1 x 12 AWG									
	Contact Resistance				Initial contact resistance of $50m\Omega$ or less									
	Contact Gap	ating			4mm (NO and NC), 2mm (NO-EM and NC-LB) Reference Value: 1/4 HP @ 120V (1ø non-reversing), 1HP @ 240V (3ø non-reversing)									
	Electrical Reliability			MTBF < 1 fault for 10 million operation cycles (3V DC, 5mA)										
				Incandescent: 1 W LEDs: 6V/17mA max, 12V & 24V/11mA max, 120 & 240V/10mA max										
	Maximum Inrush Current				40 A (40 ms)									
	Contact Mater	rial			Silver (gold plated contacts available - contact IDEC)									
	PushbuttonsContact BlockIlluminated Pushbuttons Selector Switches Illuminated Selector Switches Pushbutton SelectorsRated Insulation Voltage Rated Continuous CurreContact Ratings by Utiliz IEC 60947-5-1			Type HW-C/HW-F /HW-G										
				e 600V										
1				ent			10A							
								AC-15 (A600) DC-13 (P600)						
ĺ	Operational Vo	oltage				24V	48V	50V	110V	220V	440V			
	AC AC-12 Contr		Control of resistive loads &				10A	10A	6A	2A				
	Operational Current	50/60 Hz	AC-15 C	Control of electromagnetic	loads (> 72VA)	10A	-	7A	5A	3A	1A			
			DC-12 0	control of resistive loads &	k solid state loads	8A	5A	_	2.2A	1.1A	_			
		50	DC-13 (control of electromagnets		5A	2A	-	1.1A	0.6A	_			

1. For dimensions, see page A3-100.

2. For life expectancy derating curves, see page A3-105.

Pilot Lights (Assembled)

rait Numbers. Filot Lights					
Style			Plastic Bezel	Metal Bezel	
Round Flush	Full Voltage		HW1P-1FQ@-@-3	HW4P-1FQ4-2-3	
	Transformer	120V AC 240V AC 480V AC	HW1P-1FH2@-@ HW1P-1FM4@-@ HW1P-1FT8@-@	HW4P-1FH2@-@ HW4P-1FM4@-@ HW4P-1FT8@-@	
(Full Voltage type shown)	DC-DC Converter*	110V DC	HW1P-1D2@-@	-	
Dome	Full Voltage		HW1P-2FQ@-@-3	HW4P-2FQ4-2-3	
	Transformer	120V AC 240V AC 480V AC	HW1P-2FH2@-@ HW1P-2FM4@-@ HW1P-2FT8@-@	HW4P-2FH2@-@ HW4P-2FM4@-@ HW4P-2FT8@-@	
(Full Voltage type shown)	DC-DC Converter*	110V DC	HW1P-2D2④-②	-	
Square Flush	Full Voltage		HW2P-1FQ@-@-3	_	
	Transformer	120V AC 240V AC 480V AC	HW2P-1FH2@-@ HW2P-1FM4@-@ HW2P-1FT8@-@	-	
(Transformer type shown)	DC-DC Converter*	110V DC	HW2P-1D2@-@	_	
Jumbo Dome	Full Voltage**	LED	HW1P-504-@	_	
	24V AC/DČ	Incandescent	HW1P-507-@		

AN.

1. In place of ⁽²⁾, specify the Lens/LED Color Code.

 $2. \ \textit{In place of } \texttt{③specify the Full Voltage Code from table below. }$

3. In place of ④ specify Lamp Type Code.

4. *DC-DC convertor voltage input from 90-140V DC, comes with spring up terminals only.

5. **Available with spring up terminals and 24V only.

6. For nameplates and accessories, see page A3-96.

7 For dimensions, see page A3-100.

2 Lens/LED Color Code **3 Full Voltage Code**

		e i un vontago ot				
Color	Code	Voltage	Code	Lamp	Code	
Amber	А	6V AC/DC	6	Incandescent	Blank	
Green	G	12V AC/DC	12	LED	D	
Red	R	24V AC/DC	24			
Blue	S	120V AC (LED only)	120			
White	W	240VAC (LED only)	240			
Yellow	Y					

	④ Lamp Type Code						
ode	Lamp	Code					
	Incandescent	Blank					
2	LED	D					

Oiltight Switches & Pilot Devices


Dimensions — HW Series

* Round: 23.6mm

Square: 24.8mm


Non-Illuminated Pushbuttons






29.6mm

Panel Thickness 0.8mm to 6.mm Gasket



D1 D3




D1 = 13mm **D2** = 19mm **D3** = 23.2mm

1.18" (30mm)


Monolever

30mm



4mn

6





M3.5 Terminal Screws



M3.5 Terminal Screws

