# EE-SY671/672

# Photomicrosensor with sensitivity adjuster.

- Easy adjustment with a built-in sensitivity adjuster.
- Easy optical axis monitoring with a bright light indicator.
- Compact design incorporating a built-in amplifier and special IC enables direct switching capacity of up to 100 mA.
- Wide operating voltage range: 5 to 24 VDC
- Connection possible with a range of ICs, relays, and Programmable Controllers (PLCs).



Be sure to read *Safety Precautions* on page 4.





( (

### **Ordering Information**

Sensors Infrared light

Appearance		Sensing method	Sensing distance		nsing distance Output type		Model
Horizontal type	Silings France	Reflective type		1 to 5 mm	NPN output	Dark-ON or Light-ON	EE-SY671
Vertical type		Thenective type			TH TO GUIPAL	(Selectable) *	EE-SY672

<sup>\*</sup> The Dark-ON/Light-ON (selectable) models are normally used as dark-ON models. To use them as light-ON models, short-circuit the L terminal and positive (+) terminal.

#### **Accessories (Order Separately)**

	Туре	Cable length	Model	Remarks
Connector			EE-1001	
			EE-1001-1	L terminal and positive (+) terminal are already short-circuited.
			EE-1009	
		1 m	EE-1006	
	Connector with Cable		EE-1010	
	Connector with Cable	2 m	EE-1006	
			EE-1010	
	Connector with Debat Cable	1 m	EE-1010-R	
	Connector with Robot Cable	2 m	EE-1010-R	


OMRON


An EE-1001-1 Connector with the terminals already short-circuited is also available.

## **Ratings and Specifications**

Item Models		EE-SY671, EE-SY672		
Sensing distance		1 to 5 mm (Reflection factor: 90%; white paper 15 × 15 mm)		
Sensing object		Transparent or opaque: 15 × 15 mm min.		
Differential distance		0.5 max. (with a sensing distance of 3 mm, horizontally)		
Light source		GaAs infrared LED with a peak wavelength of 940 nm		
Indicator *	1	Light indicator (red)		
Supply vol	tage	5 to 24 VDC ±10%, ripple (p-p): 10% max.		
Current co	nsumption	40 mA max.		
Control output		NPN open collector: Load power supply voltage: 5 to 24 VDC Load current: 100 mA max. 100 mA load current with a residual voltage of 0.8 V max. 40 mA load current with a residual voltage of 0.4 V max.		
Response frequency *2		50 Hz min. (Average: 500 Hz)	_	
Ambient illumination *3		1,500 lx max. with fluorescent light on the surface of the receiver		
Ambient temperature range		Operating: -25 to +55°C Storage: -30 to +80°C		
Ambient humidity range		Operating: 5% to 85% Storage: 5% to 95%		
Vibration resistance		Destruction: 20 to 2,000 Hz (peak acceleration: 100 m/s²) 1.5-mm double amplitude for 2 h (4-min periods) each in X, Y, and Z directions		
Shock resistance		Destruction: 500m/s² for 3 times each in X, Y, and Z directions		
Enclosure rating		IEC IP50		
Connecting method		Special connector (direct soldering possible)		
Weight		Approx. 3.5 g (including screwdriver for adjustment)		
Material	Case	Polybutylene phthalate (PBT)	-	
	Emitter/ receiver	Polycarbonate	-	
Accessories		Screwdriver for adjustment	-	

- . The indicator is a GaP red LED (peak wavelength: 690 nm).
  . The response frequency was measured by detecting the following rotating disk.






EE-SY672 . The ambient illuminance is measured on the surface of the receiver.


### **Engineering Data (Typical)**

# Operating Range Characteristics (Max. Sensitivity)


#### EE-SY67□




#### EE-SY67



# Sensing Distance vs. Object Area Characteristics



# Sensing Distance vs. Sensitivity Volume



## I/O Circuit Diagrams


#### **NPN Output**

Model	Output configuration	Timing charts	Terminal connections	Output circuit
EE-SY671 EE-SY672	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases	Short-circuited between  © terminal and positive  ⊕ terminal	Light indicator (red) Load 1
	Dark-ON	Light indicator ON (red) OFF Output transistor OFF Load 1 Operates (relay) Releases	Open between © terminal and positive ⊕ terminal	Main circuit ⊕



**Dimensions** (Unit: mm)

#### **Sensors**



**Accessories (Order Separately)**