Switch Mode Power Supply S8VS (15/30/60/90/120/180/240/480-W Models)

CSM_S8VS_DS_E_6_1

60/90/120/180/240/480-W Models

Improved Versions of **Standard-type Power Supplies without Indication** Monitor (60 to 240 W). **EMI Class B Compliant.**

- New 90-W models that conform to UL Class 2 standards.
- New models with screwless terminal blocks and without indication monitor (except that 480-W models have an indication monitor).
- Status displayed on 3-digit, 7-segment display.

222 CEE

111

- · Safety standards: UL508/60950-1, CSA C22.2 No. 14/60950-1
 - (15-W, 30-W, 60-W to 240-W models with Indication monitor), CSA C22.2 No. 107.1/60950-1 (60-W to 240-W standard, 480-W models),
 - EN 50178 (= VDE0160),
- EN 60950-1 (= VDE0805 Teil 1)
- Compact: $150 \times 115 \times 127.2$ mm (W \times H \times D) (480-W models).

15/30-W Models

Compact, Thin Power Supplies That Mount Just About Anywhere to Contribute to Control Panel Downsizing

- Compact and thin: $22.5 \times 85 \times 96.5$ mm (W \times H \times D).
- Three mounting directions (standard, horizontal, facing horizontal).
- Mounting directly to the panel is possible.
- · Safety standards: UL508/60950-1/1604, cUL: CSA C22.2 No. 14/60950-1/213, EN50178 (= VDE0160), EN60950-1 (= VDE0805 Teil 1).

Features Common to All Models

- Mount to DIN Rail.
- Complies with SEMI F47-0200 (200-VAC input).
- RoHS-compliant.





Model Number Structure

Model Number Legend

Note: Not all combinations are possible. Refer to List of Models in Ordering Information, below.

S8VS-]	-
	1	2	34	5	6

1. Power Ratings

015: 15 W 030: 30 W 060: 60 W 090: 90 W 120: 120 W 180: 180 W 240: 240 W 480: 480 W

2. Output voltage

- 05: 5 V
- 12: 12 V
- 24: 24 V

3. Indication monitor

- None: Without indication monitor (standard model)
- A: With indication monitor (maintenance forecast monitor)
- B: With indication monitor (total run time monitor)

4. Alarm output

- None: Sinking * P:
- Sourcing

Note: No alarm output possible with 60-W models.

* Both sinking and sourcing outputs are available for 480-W models.

5. UL Class 2 Standards

- None: Does not conform. *
- S: Conforms.
- *15-W, 30-W, and 60-W models conform to Class 2 standards.

6. Terminal Block Form

- None: Screw terminal block
- F: Screwless terminal block

Ordering Information

List of Models

Note: For details on normal stock models, contact your nearest OMRON representative.

Models without Indication Monitor (Standard Models)

Power ratings	Input voltage	Output voltage	Output current	Model number (screw terminal block)	Model number (screwless terminal block)	
15 W 30 W	_	5 V	2.0 A	S8VS-01505 *1		
		12 V	1.2 A	S8VS-01512	Ť	
		24 V	0.65 A	S8VS-01524		
		5 V	4.0 A	S8VS-03005 *2	 - -	
		12 V	2.5 A	S8VS-03012		
		24 V	1.3 A	S8VS-03024		
60 W	-		2.5 A	S8VS-06024	S8VS-06024-F	
00.10/	100 to 240 VAC		3.75 A	S8VS-09024	S8VS-09024-F	
90 W				S8VS-09024S	S8VS-09024S-F	
120 W	-		5 A	S8VS-12024	S8VS-12024-F	
180 W	-	24 V	7.5 A	S8VS-18024	S8VS-18024-F	
240 W			10 A	S8VS-24024	S8VS-24024-F	
480 W			20 A Peak current 30 A (200 VAC)	S8VS-48024	S8VS-48024-F	

***1.** The output capacity of the S8VS-01505 is 10 W.

***2.** The output capacity of the S8VS-03005 is 20 W.

Models with Indication Monitor (Maintenance Forecast Monitor)

Power ratings	Input voltage	Output voltage	Output current	Alarm output	Model number (screw terminal block)	Model number (screwless terminal block)
60 W			2.5 A		S8VS-06024A	
90 W			3.75 A	Sinking	S8VS-09024A	
90 W				Sourcing	S8VS-09024AP	*
120 W			5 A	Sinking	S8VS-12024A	
120 W		24 V		Sourcing	S8VS-12024AP	
100.10/	100 to 240 VAC		7.5 A	Sinking	S8VS-18024A	
180 W				Sourcing	S8VS-18024AP	
240 W	-		10 A	Sinking	S8VS-24024A	
240 W				Sourcing	S8VS-24024AP	
480 W			20 A Peak current 30 A (200 VAC)	Sinking/ sourcing	S8VS-48024A	S8VS-48024A-F

Models with Indication Monitor (Total Run Time Monitor)

Power ratings	Input voltage	Output voltage	Output current	Alarm output	Model number (screw terminal block)	Model number (screwless terminal block)
60 W		VAC 24 V	2.5 A		S8VS-06024B	-
90 W			3.75 A	Sinking	S8VS-09024B	
90 W				Sourcing	S8VS-09024BP	
120 W			5 A	Sinking	S8VS-12024B	
120 W				Sourcing	S8VS-12024BP	
180 W	100 to 240 VAC		7.5 A	Sinking	S8VS-18024B	
180 W				Sourcing	S8VS-18024BP	
240 W			10 A	Sinking	S8VS-24024B	
240 W				Sourcing	S8VS-24024BP	
480 W			20 A Peak current 30 A (200 VAC)	Sinking/ sourcing	S8VS-48024B	S8VS-48024B-F

Note: Refer to pages 27 to 28 for the options that available.

Specifications

Ratings/Characteristics

		Power ratings	15 W	30 W			
Item		Туре	Standard	Standard			
Efficiency (typical) 5-V models		5-V models	72% min.	70% min.			
			74% min.	76% min.			
24-V models			77% min. 80% min.				
	Voltage *1		100 to 240 VAC (85 to 264 VAC)				
	Frequency *1		50/60 Hz (47 to 450 Hz)				
	Current	100-V input	0.45 A max.	0.9 A max.			
		200-V input	0.25 A max.	0.6 A max.			
Input	Power factor						
	Harmonic current emiss		Conforms to EN61000-3-2				
	Leakage current	100-V input	0.5 mA max.				
	-	200-V input	1.0 mA max.				
	Inrush current *2	100-V input	25 A max. (for a cold start at 25°C)				
		200-V input	50 A max. (for a cold start at 25°C)				
	Voltage adjustment rang	je *3	-10% to 15% (with V.ADJ)				
	Ripple		2.0% (p-p) max. (at rated input/output voltage)				
	Input variation influence		0.5% max. (at 85- to 264-VAC input, 100% load)				
Dutput	Load variation influence (rated input voltage)		2.0% max. (5 V), 1.5% max. (12 V, 24 V), (with rated input, 0 to 100% load)				
	Temperature variation in	fluence	0.05%/°C max.	1			
	Startup time *2		100 ms max. (at rated input/output voltage)	1,000 ms max. (at rated input/output voltage)			
	Hold time *2		20 ms min. (at rated input/output voltage)				
	Overload protection *2		105% to 160% of rated load current, voltage drop, automatic reset	105% to 160% of rated load current, voltage drop, intermitten operation, automatic reset			
	Overvoltage protection *2		Yes (a zener diode clamp) *4	Yes *5			
	Output voltage indication		No				
	Output current indication		No				
	Peak-hold current indication		No				
dditional	Maintenance forecast monitor indication						
unctions	Maintenance forecast monitor output		No				
	Total run time monitor indication		No				
	Total run time monitor o	utput	No				
	Undervoltage alarm indication		Yes (color: red)				
	Undervoltage alarm outp	out	No				
	Parallel operation		No				
	Series operation		Models with 24-V output: Possible for up to 2 Power Supplies (with external diode) Models with 5- or 12-V output: Not possible				
	Operating ambient temp	erature	Refer to the derating curve in Engineering Data (15-W, 30-W Models). (with no icing or condensation)				
	Storage temperature		-25 to 65°C				
	Operating ambient humi	dity	25% to 85% (Storage humidity: 25% to 90%)				
	Dielectric strength		 3.0 kVAC for 1 min. (between all inputs and outputs; detection current: 20 mA) 2.0 kVAC for 1 min. (between all inputs and PE terminals; detection current: 20 mA) 1.0 kVAC for 1 min. (between all outputs and PE terminals; detection current: 20 mA) 				
	Insulation resistance		100 M Ω min. (between all outputs and all inputs/ PE terminals) at 500 VDC				
	Vibration resistance		10 to 55 Hz, 0.375-mm single amplitude for 2 h each in X, Y, and Z directions				
	Shock resistance		150 m/s ² , 3 times each in ±X, ±Y, and ±Z directions				
	Output indicator		Yes (color: green)				
Other		Conducted					
	EMI	Emissions Radiated	Conforms to EN61204-3 EN55011 Class B and based on FCC Class A				
		Emissions	Conforms to EN61204-3 EN55011 Class B				
	EMS		Conforms to EN61204-3 high severity levels				
	Approved standards		UL: UL508 (Listing; Class 2: Per UL1310), UL60950-1, UL1604 (Class I/Division2) cUL: CSA C22.2 No.14 (Class 2), No.60950-1, No.213 (Class I/Division2) EN/VDE: EN50178 (=VDE0160), EN60950-1 (SELV) (=VDE0805 Teil 1) According to VDE0106/P100, IP20 (except terminal block)				
	SEMI		F47-0200 (200-VAC input)				
	Weight		160 g max. 180 g max.				

*1. Do not use an inverter output for the Power Supply. Inverters with an output frequency of 50/60 Hz are available, but the rise in the internal temperature of the Power Supply may result in ignition or burning.


*2. Refer to Engineering Data (15-W, 30-W Models) on page 12 for details.

*2. Refer to Engineering Data (15-W, 30-W Models) on page 12 for details.
*3. If the output voltage adjuster (V. ADJ) is turned, the voltage will increase by more than +15% of the voltage adjustment range. When adjusting the output voltage, confirm the actual output voltage from the Power Supply and be sure that the load is not damaged.
*4. The overvoltage protection of the S8VS-015 uses a zener diode clamp. If the internal feedback circuit is destroyed by any chance, the load may be destroyed by the clamped output voltage (approx. 140% to 190% of the rated output voltage).
*5. To reset the protection, turn OFF the input power for three minutes or longer and then turn it back ON.


Dimensions

Power Supplies with Screw Terminal Blocks


Note: All units are in millimeters unless otherwise indicated.



Note: The illustration is the S8VS-03024 model.




Note: The illustration is the S8VS-06024A model.



Note: The illustration is the S8VS-12024A model.

S8VS-18024 (180 W) S8VS-18024A (180 W) S8VS-18024B (180 W)





Seven, M4 terminal screws with square washers +10+ 8.8.8. 888 115 00 4.5 -75 Rail stopper (Sliding: 15 max.) Screwless block (2.5-mm pitches)