
Sensor Controller

Offers High-speed Input Response of 0.1 ms and Equipped with Built-in Timer

- High-speed response of 0.1 ms.
- Ideal as a two-input Controller.
- Lineup includes the S3D2-BK with flip-flop functions convenient for level control, the S3D2-AKD/CKD/CCD with 24-V power supply, and the S3D2-DK/EK with one input/output OFF-delay (two circuits) useful for load control and lamp display
- Power source for the Sensor can be supplied up to 200 mA.
- Ultra-slim body with 30-mm width.
- Multi-function model equipped with timer functions also available.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Ordering Information

Power supply voltage	Output	Timer function	Features	Model
	Relay	No	Single function with one input/output (two eirouite)	S3D2-DK
		Yes	Single-function with one input/output (two circuits)	S3D2-EK
100 to 240 VAC		No	Single-function with two inputs/one output (AND/OR operation)	S3D2-AK *
100 10 240 VAC		No	Flip-flop function with two inputs/one output	S3D2-BK
		Yes	Multi function with two inputs/one output	S3D2-CK *
	Transistor	Yes	Multi-function with two inputs/one output	S3D2-CC *
	Relay	No	Single-function with two inputs/one output	S3D2-AKD
24 VDC		Yes	Multi function with two inputs/one output	S3D2-CKD
	Transistor Yes		Multi-function with two inputs/one output	S3D2-CCD

* Models compatible with Sensors for PNP connections are also available. These model numbers have the suffix B (e.g., S3D2-AKB)

Differences from NPN Models

In		ON	8 to 12 V (2 mA max.)			
	Input signals	OFF	0 to 4 V (5 mA min.)			
		Maximum applied voltage	12 V			

Note: S3D2-AK(B)/-CK(B)/-CC(B) models with UL certification are available. These model numbers have the suffix US (e.g., S3D2-AK-US).

S3D2


Ratings and Specifications

Туре		Two inputs/ Two inputs/one output two outputs								
		Single- function	Single-func- tion (with OFF-delay)	Single-func- tion (AND/OR operation)	Flip-flop function	Mul	lti-function	Single-func- tion (AND/OR operation)	Multi-fur	nction (24 VDC)
tem	Model	S3D2-DK	S3D2-EK	S3D2-AK	S3D2-BK	S3D2-CK	S3D2-CC	S3D2-AKD	S3D2-CKD	S3D2-CCD
Rated sup voltage	pply	100 to 240 VAC ± 10% 50/60Hz						24 VDC ± 10%		
Power consumption 15 VA max.							2.5 VA max. (excluding Sensor power supply)			
Power su Sensor	ipply for	12 VDC ± 10% (includes all variations), 200 mA max. (with short-circuit protection) 24 VDC (supplied from power supply)						er supply)		
Connecte	ed Sensor	NPN transistor output (with sinking current of 18 mA min.) or contact output								
	ON	0 to 4 V (5 mA min.)								
	OFF	8 to 12 V (2 mA max.)						8 to 30 V (2 mA max.)		
nput signals	Short- circuit current	11 mA TYP (18 mA max.)								
	Maximum applied voltage	30 V								
nput res	ponse time	0.1 ms			IN1 2 ms IN2 2 ms	0.1 ms				
Output m oulse wid		10 ms max					0.5 ms max.	10 ms max.		0.5 ms max.
Control output		× 2	ut SPST-NO A (cosø = 1)	Relay output SPDT (shared common) 250 VAC, 3 A (cos∳ = 1)			NPN open collector output, 30 VDC, 100 mA (NO, NC) Residual voltage (ON)1.5 V max. Leakage current (OFF): 0.1 mA max.	Relay output SPDT 250 VAC, 3 A (cosø = 1)		NPN open collector output, 30 VDC, 100 m/ (NO, NC) Residual voltage (ON): 1.5 V max Leakage current (OFF): 0.1 mA ma
life ex-	Mechanical	50,000,000	operations min.	in. (switching frequency: 18,000 operations				50,000,000 ope (switching frequ operations/h)		
cy (relay output)	Electrical	100,000 op	erations min. (switching frequ	ency: 1,800 ope	erations/h)		100,000 operations min. (switching frequency: 1,800 operations/h)		
Output response time 10 ms max.						0.5 ms max.	10 ms max. 0.5 ms max		0.5 ms max.	
Timer functions *			OFF-delay	One-sh and Of			N-delay, Iay		One-shot, ON-delay, and OFF-delay	
			0.1 to 1 s 1 to 10 s selectable			0.1 to 1 s 1 to 10 s selectable	0.01 to 0.1 s 0.1 to 1 s selectable		0.1 to 1 s 1 to 10 s selectable	0.01 to 0.1 s 0.1 to 1 s selectable
Other functions		Signal inpu	t reverse	(Output reversible) AND/OR operating mode selection• Signal input reverse • Flip-flop function		 Signal input reverse Sync mode selection AND/OR operating mode selection 		 Signal input reverse AND/OR operating mode selection 	 Signal input reverse Sync mode selection AND/OR operating mode selection 	
	n allowable Iomentary Ilure	20 ms max	-							
Ambient temperati	ure range	Operating: -10 to +55°C, Storage: -25 to +65°C (with no icing)								
Ambient I ange	humidity	Operating/storage: 35% to 85%								
Noise imr	munity	Operating power supply: 1,500 V (p-p) min.; pulse width: 100 ns, 1 µs; rise time: 1 ns Input/output: 1,200 V (p-p) min.; pulse width: 100 ns, 1 µs; rise time: 1 ns 						e: 1 ns		
Dielectric	strength	1,500 VAC min. (between power supply terminals and I/O terminals, and between non-cur- rent-carrying parts) 1,500 VAC min. (between power supply terminals and non-cur- rent-carrying parts)						ninals and non-cu		
/ibration destructi		10 to 55 Hz	, double-ampli	tude of 0.75 m	m for 2 hours ea	ch of the X, Y	, and Z directions			
		Approx. 140) a							

* The timer will not operate in response to input signals received within 50 ms after the Controller power is turned ON.


Output Circuit Diagrams

Note: Numbers in parentheses indicate terminal pin numbers. Relay Output Model S3D2-AK/-AKD/ S3D2-DK/-EK




Open Collector Model


S3D2-CC/-CCD



Input Circuit Diagrams


Note: Numbers in parentheses indicate terminal pin numbers.





Connections

Connection Methods



(1), (2): Power supply terminals(3): FG terminal


Ground with a ground resistance of 100 Ω max. in locations subject to excessive noise.

(4) to (6): Output terminals

- (7), (10): Power supply terminals for S3D2-AKD/-CKD/-CCD Sensors (+24 V), and other models (+12 V)
- (9), (12): Power supply terminals for the Sensor (0 V)
- (8), (11): Output terminals for the Sensor
 - Connect the Sensor output lines.

Sensor Connections

Two-wire Sensors (NPN Models)




Note: Numbers in parentheses indicate terminal pin numbers.


Contact Output Sensors

• The S3D2 has a high-speed input response of 0.1 ms, which may cause contact output models (relay output, micro-switches, etc.) to receive unnecessary input from contact bounce and chattering.

Example of Unconnectable Sensor Model



Wired OR Transistor Output




Note: Numbers in parentheses indicate terminal pin numbers.


- Wired OR for "Object Detected" Signals
- (e.g., Proximity Sensors with NO Outputs)
- The input would be an OR of "object detected" signals using a wired OR of Sensors that turn ON the output transistor when an object is detected. The S3D2's input signal selector switch can be set to reverse this operation and produce an input that would be an AND of "object not detected" signals.
- Wired OR for "Object Not Detected" Signals (e.g., Proximity Sensors with NC Outputs) The input would be an OR of "object not detected" signals using a wired OR of Sensors that turn ON the output transistor when an object is not detected. The S3D2's input signal selector switch can be set to reverse this operation and produce an input that would be an AND of "object detected" signals.

Load Connection

Connecting Loads to Collector Side




Connecting Loads to Emitter Side



- Note: 1. Numbers in parentheses indicate terminal numbers.
 - Connect either the NC or NO terminals for the Emitter common. The solid line indicates the NC terminal and the broken line indicates the NO terminal.

S3D2

Nomenclature



No.	Name	Functions	
(1)	POWER indicator (green)	Lights when the operating power is turned ON and the Sensor power supply is output. Not lit when the operating power is turned OFF, or the Sensor power supply is short circuited (between the +12-V or +24-V terminal and 0-V terminal).	
(2)	IN1 indicator (red)	Lights when the output from the Sensor connected to IN1 is received by IN1 as an input.	
(3)	IN2 indicator (red)	Lights when the output from the Sensor connected to IN2 is received by IN2 as an input.	
(4)	OUT indicator (red)	Lights when the output turns ON.	
(5)	IN1 input signal selector switch	NORM: Input as a signal when the Sensor's output transistor (or contact output) is ON.	
(6)	IN2 input signal selector switch	INV: Input as a signal when the Sensor's output transistor (or contact output) is OFF.	
(7)	MODE (AND/OR operation selector switch)	AND: The output is turned ON when IN1 and IN2 input signals are both ON. OR: The output is turned ON when either IN1 or IN2 input signal is ON.	
(8)	SYNC (synchronous mode selector switch) (This switch is enabled only when the AND/OR operation selector is set to AND.)	 The output is turned ON while both IN1 and IN2 input signals are ON. If the input signal of IN2 is turned ON (at the rising edge) while the IN1 input signal is ON, th output is turned ON.* 	
(9)	TIMER switch	Turns timer operation ON/OFF. ON: Timer enabled OFF: Timer disabled	
(10)	RANGE (Timer timing selector switch)	Changes the range for the timer setting time. • S3D2-CK/-EK 1 s: Setting time is in range from 0.1 to 1s. 10 s: Setting time is in range from 1 to 10s. • S3D2-CC 0.1 s: Setting time is in range from 0.01 to 0.1s. 1 s: Setting time is in range from 0.1 to 1s.	
(11)	TIMER MODE (Timer operation mode switch)	O. S: One-shot timer ON. D: ON-delay timer OFF. D: OFF-delay timer	
(12)	TIME ADJ. (Timer setting adjuster)	Setting time can be adjusted with the provided screwdriver. The adjuster rotates 190°.	


* Be sure to set the one-shot timer.

Operation


Basic Operation

S3D2-AK : Basic Operation


One Sensor



Two Sensors (AND Operation)




Two Sensors (OR Operation)




S3D2-AK□ default settings: IN1·····NORM, IN2·····INV. I If AND operation is used, set IN2 to NORM.

S3D2-BK: Flip-flop Operation

_ _ _ _ _ _ _ _ _ _ _ _ _ _ _





Note: 1. IN1 and IN2 send OR outputs.


- 2. IN1 and IN2 send AND outputs.3. IN1 and IN2 send AND outputs for T seconds from the rising edge.
- IN1 and IN2 send AND outputs for 1 seconds from the fising edge.
 IN1 and IN2 send AND outputs after a delay of T seconds from the
- rising edge. 5. IN1 and IN2 send AND outputs for T seconds from the falling edge.

When only one Sensor is connected to the S3D2-CK□ and S3D2-CC□, always set the AND/OR selector switch to OR MODE .

S3D2-DK/-EK: Basic Operation


Two Input Signals Output Independently

The S3D2-EK is equipped with an OFF-delay Timer.



S3D2-DK/-EK: One Sensor with Two Outputs

Terminals (8) and (11) are short-circuited.



- Note: 1. The time chart above shows the operation for an S3D2-EK when the timer 1 switch is OFF and the timer 2 switch is ON.
 - 2. Terminals (8) and (11) are short-circuited, and the current from the S3D2 to the Sensor is 18 × 2 = 36 mA max. (TYP 22 mA).

S3D2-CK /-CC : Timer Operation (AND)

Safety Precautions

Refer to Warranty and Limitations of Liability.

<u> WARNING</u>

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Precautions for Safe Use

 Be sure to connect the power supply to the power supply terminals correctly. Use a power supply with a voltage range of 100 to 240 VAC ± 10%.


Precautions for Correct Use

Do not use the product in atmospheres or environments that exceed product ratings.

• Wiring

Ground

- FG is a ground terminal. Ground this terminal at a ground resistance of 100 Ω max. when installing in locations subject to excessive noise, or if the S3D2 malfunctions.
- Do not share a ground line with other devices, or connect it to a structural beam of a building. Doing so will have the opposite effect, and may adversely affect the Sensor.




Storing in a Protective Case

 Take measures to provide adequate heat dissipation. Otherwise, heat radiation from the body of the S3D2 may cause the insides of protective casing to heat up.


S3D2-AKD/-CKD/-CCD

• Do not connect a load of 1 A min. to models for which the S3D2 power supply inputs are to be used as is for the Sensor power supply outputs. Connecting a load of 1 A min. to the Sensor's power supply outputs will cause the fuse in the case to break.



Output

- Connect a surge suppressor or diode in parallel to the load if an inductive load or other electrical part that generates noise is connected to the output.
- \bullet Connect the cathode side of the diode to the \oplus side of the power supply.



Output Relay Contact

(Not Including S3D2-CC/-CCD/-DK/-EK)

- When using a load (e.g., contactor or valve) that generates an arc when the circuit is broken, the NC (NO) contact may turn ON before the NO (NC) contact has opened (turned OFF).
- When using both NO and NC outputs at the same time, incorporate an arc suppressor (use the CR method, varistor, or other countermeasure).

Mounting

Tightening Torque


Using the provided M3.5 screws, tighten the terminal block to a torque of 0.59 N·m max.

For direct mounting, use M4 screws, and tighten them to a torque of 0.78 N·m max.

Side-by-side Mounting

- When two or more S3D2 are mounted side by side, be sure to provide a minimum distance of 10 mm between them.
- Note: Use the PFP-M End Plate for a space of 10 mm.
- space of 10 mm.

unavoidable, refer to the following load derating curve.



Ambient temperature (°C)


End Plate

(PFP-M)

DIN Track

\$3D2

S3D2



Cat. No. E846-E1-03

In the interest of product improvement, specifications are subject to change without notice.

Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- · Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- · Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

2012.8

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company