Pushbutton Switch (Detachable) (Lighted/Non-Lighted) (Cylindrical 16-dia.)

A16

Separate Construction with Cylindrical 16-dia. Body

- Miniature design of 28.5 mm, the smallest class in the industry.
- Detachable Switch Unit.
- The same contacts can be used for both standard loads and microloads.
- Easy-to-wire terminal arrangement.
- Certified for EN 60947-5-1 and IEC 60947-5-1.




	Model					
	Rectangular	Square	Round			
Solder terminals	A16-J Series	A16-A Series	A16-T Series			
PCB terminals	A16-J Series	A16-A Series	A16-T Series			
Voltage- reduction lighting solder terminals	A16-J Series	A16-A Series	A16-T Series			
Screw-less clamp models	A16-J Series	A16-A Series	A16-T Series			

List of Models

Model Number Structure

Model Number Legend The model numbers used to order sets of Units are illustrated below. One set comprises the Pushbutton, Lamp (lighted models only), Case, and Switch. For information on combinations, refer to Ordering Information on pages 3 to 7.




• Solder terminals are available only with 100-V models.

 The Voltage Reduction Unit is not available for models with PCB terminals.

"T2" is available only for the Screw-less Clamp type.

Ordering Information



Appearance	Classification			Model
			Rectangular (2-way guard)	A16-J M
		Momentary operation	Square (2-way guard)	A16-A M
•	IP40	operation	Round (projected)	A16-T
	1F40		Rectangular (2-way guard)	A16-J□A
		Alternate operation	Square (2-way guard)	A16-A A
			Round (projected)	A16-T
			Rectangular (2-way guard)	A165-J_M
		Momentary operation	Square (2-way guard)	A165-A M
	Oil-resistant IP65	operation	Round (projected)	A165-T M
	OII-resistant 1P05		Rectangular (2-way guard)	A165-J_A
		Alternate operation	Square (2-way guard)	A165-A A
			Round (projected)	A165-T⊡A

Insert one of the following symbols into the box (\Box).

	0,		
Symbol Color		Remarks	
R	Red		
Y	Yellow		
PY	Pure yellow	LED indicator, incandescent	
А	Blue	lamp, or nor lighted	
W	White		
GY	Green	LED only	
G	Green	Incandescent lamp or non-lighted	
В	Black	Non-lighted only	

Approved Standard Ratings UL, cUL (File No. E41515)

5 A at 125 VAC, 3 A at 250 VAC (general use) 3 A at 30 VDC (resistive)

Ratings Contacts

Rated voltage	Resistive load
125 VAC	5 A
250 VAC	3 A
30 VDC	3 A

Minimum applicable load: 1 mA at 5 VDC

Rated values are obtained from tests conducted under the following conditions.

1. Load: Resistive load

2. Mounting conditions: No vibration and no shock

3. Temperature: 20 ±2 °C

4. Operating frequency: 20 operations/min

Contact Form

Name	Contact	
DPDT	COM NC	

Characteristics

Socket Unit

Item	Туре	Pushbutton Switch		
Allowable Mechanical		Momentary operation: 120 operations/minute max.		
operating	Mechanical	Alternate operation: 60 operations/minute max. *1		
frequency	Electrical	20 operations/minute max. *1		
Insulation r	esistance	100 MΩ min. (at 500 VDC)		
	Between terminals of same polarity	1,000 VAC, 50/60 Hz for 1 minute		
Dielectric	Between terminals of different polarity	2,000 VAC, 50/60 Hz for 1 minute		
strength	Between each ter- minal and ground	2,000 VAC, 50/60 Hz for 1 minute		
	Between lamp ter- minals	1,000 VAC, 50/60 Hz for 1 minute *2		
Vibration resistance Malfunction		10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)		
Shock	Destruction	500 m/s ²		
resistance	Malfunction	150 m/s ² max. (malfunction within 1 ms)		
Durability	Mechanical	Momentary operation: 2,000,000 operations min. Alternate operation: 200,000 operations min. *1		
	Electrical	100,000 operations min. *1		
Electric sho	ock protection class	Class II		
PTI (trackin	g characteristic)	175		
Degree of c	ontamination	3 (IEC947-5-1)		
Weight		Approx. 10 g (in the case of a lighted DPDT switch with solder terminals)		
Degree of protection		IP40: A16, Oil-resistant IP65: A165 *3		
Ambient operating temperature		-10 °C to 55 °C (with no icing or condensation)		
Ambient operating humidity		35% to 85%RH		
Ambient storage temperature		-25 °C to 65 °C (with no icing or condensation)		

*1. Set and reset constitute one operation.
*2. With LED and incandescent lamp not mounted.
*3. Degree of protection from the front of the panel.

Operating Characteristics

Туре	Pushbutton Switch		
Characteristics	IP40	Oil-resistant IP65	
Operating force (OF) max.	4.41 N	4.91 N	
Releasing force (RF) min.	0.29 N		
Total travel (TT)	Approx. 3 mm		
Pretravel (PT) max.	2.5 mm		
Lock travel alternate (LTA) min. *	0.5 mm		

* Alternate operation models only.

EN60947-5-1 (Low Voltage Directive)

3 A at 250 VAC (AC12), 3 A at 30 VDC (DC12)

Super-bright LED

Rated voltage	Rated current	Operating voltage	Internal limiting resistor
5 VDC		5 VDC ±5%	Red, yellow, white : 300 Ω Green, blue, pure white : 160 Ω
12 VAC/VDC	8 mA	12 VAC/VDC ±5%	Red, yellow, white : 1 k Ω Green, blue, pure white : 910 Ω
24 VAC/VDC		24 VAC/VDC ±5%	2.4 kΩ

Incandescent Lamp

Rated voltage	Rated current	Operating voltage
6 VAC/VDC	60 mA	5 VAC/VDC
14 VAC/VDC	40 mA	12 VAC/VDC
28 VAC/VDC	24 mA	24 VAC/VDC

Voltage-reduction Unit (LED Lamp)

Rated voltage	Operating voltage	Applicable lamp
110 VAC/VDC	100/110 VAC/VDC (90 to 121 V)	A16-24DS
220 VAC/VDC	200/220 VAC/VDC (180 to 242 V)	LED Lamp

Screw-less Clamp

Item		Screw-Less Clamp				
Recommended wire size		0.5 mm ² tv	0.5 mm ² twisted wire or 0.8 mm-dia. solid wire			
	Twisted wire	0.3 mm ²	0.5 mm ²	0.75 mm ²	1.25 mm ²	
Usable wires and tensile strength	Solid wire	0.5 mm dia.	0.8 mm dia.	1.0 mm dia.	—	
	Tensile strength	10 N	20 N	30 N	40 N	
Length of exposed wire		10 ±1mm				
Compliant standards		JIS C 2811 Terminal Blocks for Industrial Use				

Dimensions

• The lamp terminal is also provided with non-lighted models.

• Solder terminals and tab terminals (#110) can be both used with Lighted and Non-lighted Pushbutton Switches.

