Products & Services Te

**Technical Support** 



Industries

**About Agilent** 



# E3646A 60W Dual Output Power Supply, Two 8V, 3A or 20V, 1.5A

Product Status: Currently Orderable | Currently Supported

#### Overview

#### **Key Specifications**

## Output Ratings (@ 0°C to 40°C) 2 Outputs

Range 1: 0 to 8 V / 3 A

• Range 2: 0 to 20 V / 1.5 A

# Programming Accuracy (@ 25°C ±5°C), ±(% output + offset)

Voltage: <0.05% + 10 mV (<0.1% + 25 mV for output 2 of E3646/47/48/49A)</li>

• Current: <0.2% + 10 mA

## Ripple & Noise 20 Hz to 20 MHz

• Normal Mode Voltage: <5 mVpp / 0.5 mVrms

Normal Mode Current: <4 mArms</li>Common Mode Current: <1.5 uArms</li>

#### Readback Accuracy (@ 25°C ±5°C), ±(% output + offset)

• Voltage: <0.05% + 5 mV (<0.1% + 25 mV for output 2 of E3646/47/48/49A)

Current: <0.15% + 5 mA (<0.15% + 10 mA for output 2 of E3646/47/48/49A)</li>

#### Description

Agilent basic DC power supplies offer essential features for a tight budget. The single & dual output, 30-100 W GPIB E3640 series provide small, compact size for bench and system use; low output ripple and noise; and built-in measurements and basic programmable features with GPIB and RS232 interface. The Agilent 54W, multiple output E3646A is a clean, reliable power supply for general purpose applications, and combine convenient benchtop capabilities with flexible system features in a compact, multi-output package.

## Reliable Power, Repeatable Results

- · Single and dual outputs
- · Dual range output
- 30 W to 100 W output power
- Front and rear output terminals
- Over-voltage protection
- Remote Sensing
- · GPIB and RS-232 standard
- Save and recall functions



With the output power of 30 to 100 W, the Agilent E364xA Series programmable DC power supplies provide great performance at a great price. All ten models deliver clean power, excellent regulation, fast transient response and built-in GPIB and RS-232 interfaces. They are designed to meet the needs of R&D design verification, production testing, QA verifications, and other demanding applications with Agilent Technologies's quality and reliability.

# **Steady Output**

With 0.01 percent load and line regulation, Agilent E364xA power supplies are able to maintain a steady output when power line and load changes occur. They also specify normal mode voltage noise and low common mode current noise. The low normal mode noise specification assures clean power for precision circuitry applications, and the low common mode current provides isolation from power line current injection. Agilent E364xA power supplies specify less than 90 msec of voltage settling time at any output load condition.



# **Remote Interface**

Agilent E364xA power supplies support any PC with a GPIB (IEEE-488) card or RS-232 interface. Every model ships standard with both GPIB and RS-232. The easy-to-use SCPI (Standard Commands for Programmable Instruments) allow fast and simple programming procedures. Besides, the user manual provides sufficient information on programming for all end users, from beginners to veterans.

# **Broad Support**

VXI plug and play software drivers are available for Agilent VEE, National Instruments LabView™ and LabWindows™. With these drivers, integration of the E364xA into your system can never be any easier. The drivers are supported under Microsoft® Windows 98® and NT®.

# **Front Panel Operation**

An easy-to-use rotary knob and self-guiding keypads allow you to set the output at your desired resolution without any effort. Also, both voltage and current levels can be set to a maximum resolution of 10 mV/1 mA from the front panel. In addition, you can store and recall for up to five complete power supply setups using the internal non-volatile memory.

The output on/off button sets the output to zero. If you own a dual output model, you can view two voltages or currents that are displayed simultaneously.

## **Versatile Power**

Agilent E364xA power supplies give you the flexibility to select from dual output ranges. Output load is protected against overvoltage, which can be easily monitored and adjusted from the front panel and remote interface. Remote sensing is available in the rear terminal to eliminate errors caused by voltage drops on the load leads. These power supplies offer new versatile binding posts on the front panel and screw-type terminals on the rear panel. New front panel binding posts allow you to use safety test leads as well as conventional banana clips and stripped wires. An optional rackmount kit is available. The Agilent E364xA Series employs a cooling fan with automatic speed control to reduce the acoustic noise.

LabView and LabWindows are registered trademarks of National Instruments.

Microsoft Windows 98 and Windows NT are US registered trademerks of Microsoft Corporation.

# Agilent E3640A — E3649A Programmable DC Power Supply Specifications

Model Number	E3640A	E3641A	E3642A	E3643A	E3644A	E3645A
Maximum Power	30 W		50 W		80 W	
# of Outputs	1	1	1	1	1	1
DC Output Rating (@ 0 °C to 40 °C)	0 to 8 V/3 A or 0 to 20 V/1.5 A	0 to 35 V/0.8 A or 0 to 60 V/0.5 A		0 to 35 V/1.4 A or 0 to 60 V/0.8 A	0 to 8 V/8 A or 0 to 20 V/4 A	0 to 35 V/2.2 A or 0 to 60 V/1.3 A
Net Weight	5.3 kg	5.2 kg	6.3 kg	6.2 kg	6.6 kg	6.7 kg
Dimensions (without bumper)	212.6 mm W x 88.5 mm H x 348.3 mm D					

Model Number	E3646A	E3647A	E3648A	E3649A	
Maximum Power	60	W	100 W		
# of Outputs	2	2	2	2	
DC Output Rating (@ 0 °C to 40 °C)	Two 0 to 8 V/3 A or 0 to 20 V/1.5 A	Two 0 to 35 V/0.8 A or 0 to 60 V/0.5 A	Two 0 to 8 V/5 A or 0 to 20 V/2.5 A	Two 0 to 35 V/1.4 A or 0 to 60 V/0.8 A	
Net Weight	8.2 kg	8.0 kg	9.2 kg	9.1 kg	
Dimensions (without bumper)		212.8 mm W x 133.0 ı	mm H x 348.3 mm D		

Load and Line Regulation $\pm$	(% of output + offset)		
Voltage	< 0.01% + 3 mV		
Current	< 0.01% + 250 μA		
Ripple and Noise (20 Hz to	20 MHz)		
Normal Mode Voltage	< 5 mVpp/0.5 mVrms for 8 V/20 V models < 8 mVpp/1 mVrms for 35 V/60 V models		
Normal Mode Current	< 4 mArms		
Common Mode Current	< 1.5 μArms		
Accuracy <sup>1</sup> 12 Months (@ 25	°C ± 5 °C), ± (% output + offset)		
Programming			
Voltage	< 0.05% + 10 mV (< 0.1% + 25 mV for output 2 of E3646/47/48/49 A)		
Current	< 0.2% + 10 mA		
Readback			
Voltage	< 0.05% + 5 mV (< 0.1% + 25 mV for output 2 of E3646/47/48/49 A)		
Current	< 0.15% + 5 mA (< 0.15% + 10 mA for output 2 of E3646/47/48/49 A)		
Resolution	·		
Program	< 5 mV/1 mA		
Readback	< 2 mV/1 mA		
Meter	10 mV/1 mA		
Transient Response	Less than 50 µsec for output to recover to within 15 mV following a change in output current from full load to half load or vice versa.		
Settling Time <sup>2</sup>	< 90 msec		
OVP Accuracy, ± (% output + offset)	< 0.5% + 0.5 V		
Activation Time <sup>3</sup>	< 1.5 msec, OVP ≥ 3 V/< 10 msec, OVP < 3 V		
Temperature Coefficient pe	r °C ± (% output + offset)		
Voltage	< 0.01% + 3 mV (< 0.02% + 5 mV for output 2 of E3646/47/48/49A)		
Current	< 0.02% + 3 mA		

 $<sup>^{\</sup>rm 1}$  Accuracy specifications are valid after a 1-hour warm-up with no load and calibration at 25  $^{\rm o}{\rm C}.$ 

<sup>&</sup>lt;sup>2</sup> Maximum time required for the output voltage to change from 1% to 99% or vice versa following the receipt of VOLTage or APPLy command via direct GPIB or RS-232 interface.

 $<sup>^{\</sup>rm 3}$  Average time for output to start and drop after an OVP condition occurred.

Stability, constant load & temperature ± (% output + offset), 8 hrs				
Voltage	< 0.02% + 2 mV			
Current	< 0.1% + 1 mA			
<b>Remote Sensing</b> Max. voltage drop in each load lead	1 V			
<b>AC Input</b> (47 Hz – 63 Hz)	100 Vac $\pm$ 10% (Opt 0E9)/115 Vac $\pm$ 10% (Std)/230 Vac $\pm$ 10% (0E3)			
Warranty	1 year			
Product Regulation	Designed to comply with UL3111-1; certified to CSA 22.2 No. 1010.1; conforms to IEC 1010-1; complies with EMC directive 89/336/EEC (Group 1, Class A)			

Agilent E364xA Series Power Supplies E3640A 30-Watt Single Power Supply E3641A 30-Watt Single Power Supply E3642A 50-Watt Single Power Supply E3643A 50-Watt Single Power Supply E3644A 80-Watt Single Power Supply E3645A 80-Watt Single Power Supply E3646A 60-Watt Dual Power Supply E3647A 60-Watt Dual Power Supply E3648A 100-Watt Dual Power Supply E3649A 100-Watt Dual Power Supply

#### **Accessories Included**

User's Guide, Quick Reference Guide and AC power cord

## **Power Options**

Opt. 0E3 230 Vac ± 10% Opt. 0EM 1150 Vac ± 10% Opt. 0E9 100 Vac ± 10%

#### **Other Options**

Opt. 1CM Rackmount kit\*

- Single Output (P/N 5063-9240)

- Dual Output (P/N 5063-9243)

Opt. 0L2 Extra Manual

Opt. UK6 Commercial calibration with test result data

E3600A-100 Test lead kit

#### **Rackmount Kits\***

Agilent E3640A/41A/42A/43A/44A/45A
To rackmount two instruments side-by-side
Lock-link Kit (P/N 5061-9694)
Flange Kit (P/N 5063-9212)
To rackmount one or two instruments in a
sliding support shelf
Support Shelf (P/N 5063-9255)
Slide Kit (P/N 1494-0015) required for
support shelf
For a single instrument, also order
Filter Panel (P/N 5002-3999)

Agilent E3646A/47A/48A/49A

To rackmount two instruments side-by-side Lock-link Kit (P/N 5061-9694)
Flange Kit (P/N 5063-9214)

To rackmount two instruments in a sliding support shelf
Support Shelf (P/N 5063-9256)
Silde Kit (P/N 1494-0015)

\* Rackmounting with 1CM or lock-link/ flange kit requires Agilent or customer support rails Agilent Support Rails-E3663AC