



■ Dimensions

Note: All units are in millimeters unless otherwise indicated.



Internal Circuit



| Terminal No. | Name |
|--------------|-----------|
| A | Anode |
| K | Cathode |
| C | Collector |
| E | Emitter |

Unless otherwise specified, the tolerances are as shown below.

| Dimensions | Tolerance |
|--------------------------|-------------|
| 3 mm max. | ± 0.3 |
| $3 < \text{mm} \leq 6$ | ± 0.375 |
| $6 < \text{mm} \leq 10$ | ± 0.45 |
| $10 < \text{mm} \leq 18$ | ± 0.55 |
| $18 < \text{mm} \leq 30$ | ± 0.65 |

■ Features

- Wide model with a 8-mm-wide slot.
- PCB mounting type.
- High resolution with a 0.5-mm-wide aperture.

■ Absolute Maximum Ratings (Ta = 25°C)

| Item | Symbol | Rated value |
|-----------------------|---------------------------|------------------------------------|
| Emitter | Forward current | I _F 50 mA (see note 1) |
| | Pulse forward current | I _{FP} 1 A (see note 2) |
| | Reverse voltage | V _R 4 V |
| Detector | Collector-Emitter voltage | V _{CEO} 30 V |
| | Emitter-Collector voltage | V _{ECO} --- |
| | Collector current | I _C 20 mA |
| | Collector dissipation | P _C 100 mW (see note 1) |
| Ambient temperature | Operating | Topr -25°C to 95°C |
| | Storage | Tstg -30°C to 100°C |
| Soldering temperature | | Tsol 260°C (see note 3) |

- Note:
- Refer to the temperature rating chart if the ambient temperature exceeds 25°C.
 - The pulse width is 10 µs maximum with a frequency of 100 Hz.
 - Complete soldering within 10 seconds.

■ Electrical and Optical Characteristics (Ta = 25°C)

| Item | Symbol | Value | Condition |
|--------------|--------------------------------------|--|--|
| Emitter | Forward voltage | V _F 1.2 V typ., 1.5 V max. | I _F = 30 mA |
| | Reverse current | I _R 0.01 µA typ., 10 µA max. | V _R = 4 V |
| | Peak emission wavelength | λ _P 940 nm typ. | I _F = 20 mA |
| Detector | Light current | I _L 0.5 mA min., 14 mA max. | I _F = 20 mA, V _{CE} = 10 V |
| | Dark current | I _D 2 nA typ., 200 nA max. | V _{CE} = 10 V, 0 lux |
| | Leakage current | I _{LEAK} --- | --- |
| | Collector-Emitter saturated voltage | V _{CE} (sat) 0.1 V typ., 0.4 V max. | I _F = 20 mA, I _L = 0.1 mA |
| | Peak spectral sensitivity wavelength | λ _P 850 nm typ. | V _{CE} = 10 V |
| Rising time | | tr 4 µs typ. | V _{CC} = 5 V, R _L = 100 Ω, I _L = 5 mA |
| Falling time | | tf 4 µs typ. | V _{CC} = 5 V, R _L = 100 Ω, I _L = 5 mA |