CSM G7Z DS E 5 1

Multi-pole Power Relay for Contactor Current Range Capable of Carrying and Switching 40 A at 440 VAC



- One pole, 40 A can be carried and switched.
- The maximum load capacity of 160 A when using 4-pole parallel connections.
- All materials used are compliant with the RoHS Directive
- EN 60947-4-1 certification for mirror contact mechanisms has been obtained by using a combination of the relay and auxiliary contact blocks.
- A design with a small number of openings makes it difficult for dust or foreign matter to enter.
- Ideal for supply power to industrial inverters, servo drivers, and other devices, and switching power to motors and other equipment.
- Conforms to European PV standard (VDE0126).



Be sure to read the "Safety Precautions" on page 6 and the "Precautions for All Relays with Forcibly Guided Contacts".



Model Number Structure

Model Number Legend Relay with Auxiliary Contact Block



1. Relay Contact Configuration

4A: 4PST-NO

3A1B: 3PST-NO/SPST-NC 2A2B: DPST-NO/DPST-NC

2. Contact Configuration of Auxiliary Contacts

20: DPST-NO

11: SPST-NO/SPST-NC

02: DPST-NC

3. Contact Mechanism of Auxiliary Contacts

Z: Bifurcated crossbar contact

Relay

1. Contact Configuration

4A: 4PST-NO

3A1B: 3PST-NO/SPST-NC 2A2B: DPST-NO/DPST-NC

Auxiliary Contact Block

1. Contact Configuration of Auxiliary Contacts 20: DPST-NO

11: SPST-NO/SPST-NC

02: DPST-NC

2. Contact Mechanism of Auxiliary Contacts

Z: Bifurcated crossbar contact

Ordering Information

Relay with Auxiliary Contact Block

Relay with Auxiliary Contact Block (for Screw Terminals)

	Structure	Contact configuration			
Classification		Relay	Relay Auxiliary Contact Block		Model
			DPST-NO		G7Z-4A-20Z
		4PST-NO	SPST-NO/SPST-NC		G7Z-4A-11Z
	4 poles + 2 poles 3PS		DPST-NC		G7Z-4A-02Z
Deleverelth Assellians		. I 3PS I-NO/SPS I-NO	DPST-NO		G7Z-3A1B-20Z
Relay with Auxiliary Contact Block			SPST-NO/SPST-NC	12, 24 VDC	G7Z-3A1B-11Z
			DPST-NC		G7Z-3A1B-02Z
			DPST-NO		G7Z-2A2B-20Z
		DPST-NO/DPST-NC	SPST-NO/SPST-NC		G7Z-2A2B-11Z
			DPST-NC		G7Z-2A2B-02Z

Note: 1. Relay contact terminals are M5, and the coil terminals are M3.5.

- 2. Auxiliary contact block terminals are M3.5.
- 3. When placing an order, specify the model number and rated supply voltage (12 VDC or 24 VDC).

Relay

Structure Classification		Contact configuration	Rated Voltage	Model
		4PST-NO		G7Z-4A
Relay 4 poles		3PST-NO/SPST-NC	12, 24 VDC	G7Z-3A1B
		DPST-NO/DPST-NC		G7Z-2A2B

Note: 1. Relay contact terminals are M5, and the coil terminals are M3.5.

2. When placing an order, specify the model number and rated supply voltage (12 VDC or 24 VDC).

Accessories (Order Separately)

Auxiliary Contact Block

Classification Structure		Contact Configuration	Model
Auxiliary Contact Block	2 poles	DPST-NO	G73Z-20Z
		SPST-NO/SPST-NC	G73Z-11Z
		DPST-NC	G73Z-02Z

Specifications

Ratings

Coil

Item	Rated current	Coil resistance	Must operate voltage	Must release voltage	Maximum voltage	Power consumption
Rated voltage	(mA)	(Ω)	Percei	entage of rated voltage		(W)
12 VDC	308	39	75% max.	10% min.	110%	Approx 2.7
24 VDC	154	156		10% Milli.	110%	Approx. 3.7

Note: 1. Rated current and coil resistance were measured at a coil temperature of 23°C with coil resistance of ±15%.

2. Operating characteristics were measured at a coil temperature of 23°C.

3. The maximum allowable voltage is the maximum value of the fluctuation range for the Relay coil operating power supply and was measured at an ambient temperature of 23°C.

There is, however, no continuous allowance.

Contacts

Relay

	Model	G7Z-4A-□Z, G7Z-3A1B-□Z, G7Z-2A2B-□Z		
Item	Load	Resistive load	Inductive load cos 0.3	Resistive load L/R = 1 ms
Contact structure			Double break	
Contact material			Ag alloy	
Rated load	NO	40 A at 440 VAC	22 A at 440 VAC	5 A at 110 VDC
nateu loau	NC	25 A at 440 VAC	10 A at 440 VAC	5 A at 110 VDC
Rated carry current	NO	40 A		
nateu carry current	NC	25 A		
Maximum contact volta	age	480 VAC 12		125 VDC
Maximum contact	NO	40 A	22 A	5 A
current	NC	25 A	10 A	5 A
Maximum switching	NO	17,600 VA	9,680 VA	550 W
capacity	NC	11,000 VA	4,400 VA	550 W
Failure rate P value (reference value)			2 A at 24 VDC	

Note: The ratings for the auxiliary contact block mounted on the G7Z are the same as those for the G73Z auxiliary contact block.

Auxiliary Contact Block

Model	G73Z-20Z, G73Z-11Z, G73Z-02Z		
Load Item	Resistive load	Inductive load cos 0.3	Resistive load L/R = 1 ms
Contact structure		Double break	
Contact material	Au clad + Ag		
Rated load	1 A at 440 VAC	0.5 A at 440 VAC	0.5 A at 110 VDC
Rated carry current	1 A		
Maximum contact voltage	480 VAC 125 VDC		
Maximum contact current	1 A	1 A 0.5 A	
Maximum switching capacity	440 VA	220 VA	55 W
Failure rate P value (reference value)		1 mA at 5 VDC	;

Characteristics

	Classification	Relay * 5	Auxiliary contact block	
Item	Model	G7Z-4A-□Z, G7Z-3A1B-□Z, G7Z-2A2B-□Z	G73Z-20Z, G73Z-11Z, G73Z-02Z	
Contact resistance *1		$400 \text{ m}\Omega \text{ max}.$ $100 \text{ m}\Omega \text{ max}.$		
Operating time *2		50 ms max.		
Release time *2		50 ms max.		
Maximum operating	Mechanical	1,800 operations/h		
frequency	Rated load	1,200 operations/h		
Insulation resistance	k 3	1,000 MΩ min.		
Dielectric strength	Between coil and contacts	4,000 VAC, 50/60 Hz for 1 min		
	Between contacts of different polarity	4,000 VAC, 50/60 Hz for 1 min		
	Between contacts of the same polarity	2,000 VAC, 50/60 Hz for 1 min		
Impulse withstand voltage	Between coil and contacts	10 kV, 1.2 × 50 μs		
	Between contacts of different polarity	10 kV, 1.2 × 50 μs		
	Between contacts of the same polarity	4.5 kV, 1.2 × 50 μs		
	Destruction	10 to 55 to 10 Hz, 0.5-mm single amplitude (1.0-mm double amplitude)		
Vibration resistance	Malfunction	NO: 10 to 55 to 10 Hz, 0.5-mm single amplitude (1.0-mm double amplitude) NC: 10 to 32 to 10 Hz, 0.5-mm single amplitude (1.0-mm double amplitude)		
	Destruction	Screw mounting: 700 m/s ² , DIN Track mounting	g: 500 m/s ²	
Shock resistance	Malfunction	NO: 100 m/s ² NC: 25 m/s ²		
	Mechanical	1,000,000 operations min. (at 1,800 operations/h, contact no load)		
Durability	Electrical *4	AC resistive load: 80,000 operations AC inductive load: 80,000 operations DC resistive load: 100,000 operations (at 1,200 operations/h, rated load)		
Failure rate (P level) (r	reference value) *6	2 A at 24 VDC		
Ambient operating temperature		-25 to 60°C (with no icing or condensation)		
Ambient operating hu	midity	5% to 85%		
Weight		Approx. 330 g	Approx. 18 g	

Note: The above values are initial values.

- *1. The contact resistance for the Relay (G7Z) was measured with 1 A at 5 VDC using the voltage drop method.
 - The contact resistance for the auxiliary contact block (G73Z) was measured with 0.1 A at 5 VDC using the voltage drop method.
- *2. The operate time was measured with the rated voltage imposed with any contact bounce ignored at the ambient temperature of 23°C.
- *3. The insulation resistance was measured with a 1,000-VDC megohmmeter applied to the same places as those used for checking the dielectric strength.
- ***4.** The electrical endurance was measured at an ambient temperature of 23°C.
- *5. The specifications for the auxiliary contact block mounted on the G7Z are the same as those for the G73Z auxiliary contact block.
- ***6.** The failure rate is based on an operating frequency of 1,800 operations/h.

Approved Standards

UL Standard: UL508, UL840 (File No. E41643)

Model	Coil ratings	Contact ratings		Number of test operations
	12, 24 VDC	NO contact	40 A, 480 VAC, 60 Hz (Resistive)	80,000
			5 A, 120 VDC (Resistive)	100,000
			22 A, 480 VAC, 60 Hz (General Use)	100,000
G7Z			D300* (1-A current applied)	
		NC contact	25 A, 480 VAC, 60 Hz (Resistive) 5 A, 120 VDC (Resistive) 10 A, 480 VAC, 60 Hz (General Use)	100,000
			D300* (1-A current applied)	

* Auxiliary contact ratings

	-				
	Model	Contact ratings			
G73Z	NO contact	D300 (1-A current applied)			
G/3Z		NC contact	– D300 (1-A current applied)		

CSA Standard: CSA Certification by CSA C22.2 No. 14

CCC Certification (File No.2009010304361493) GB14048.4 (((s))

EN Standard/TÜV Certification: EN 60947-4-1 (Certification No. R50079155) △

Model	Coil ratings	Contact ratings		
G7Z	12, 24 VDC	NO contact	AC-1: 40 A, 440 V, 50/60 Hz AC-3: 16 A, 440 V, 50/60 Hz DC-1: 5 A, 110 V *AC-15: 0.5 A, 440 V, 50/60 Hz *DC-13: 0.5 A, 110 V	
		NC contact	AC-1: 25 A, 440 V, 50/60 Hz DC-1: 5 A, 110 V *AC-15: 0.5 A, 440 V, 50/60 Hz *DC-13: 0.5 A, 110 V	
G73Z		NO contact	AC-15: 0.5 A, 440 V , 50/60 Hz	
		NC contact	DC-13: 0.5 A, 110 V	

* Auxiliary contact ratings

< Reference > Information

UL 508: Industrial control devices

UL 840: Insulation coordination including clearance and

creepage distance for electrical devices

CSA C22.2 No. 14: Industrial control devices

EN 60947-4-1: Contactors


Dimensions (Unit: mm)


Dimensions


Relay (12 VDC, 24 VDC) with Auxiliary Contact Block

4 Poles









Four, M3.5

Eight, M5

Two, M3.5


75.7


Note: The dimensions are typical values.


Relay (12 VDC, 24 VDC)


4 Poles













Note: The dimensions are typical values.

Contact Block








Note: The dimensions are typical values.


Auxiliary DIN Track Mounting Height (when using the PFP-100N or PFP-50N mounting rail)



Note: The dimensions are typical values.


Terminal Arrangement/Internal Connections Relay with Auxiliary Contact Block

G7Z-4A-20Z




Note: The coil has no polarity.

G7Z-3A1B-20Z




Note: The coil has no polarity.

G7Z-2A2B-20Z




Note: The coil has no polarity.

G7Z-4A-11Z




 $\textbf{Note:} \ \mathsf{The} \ \mathsf{coil} \ \mathsf{has} \ \mathsf{no} \ \mathsf{polarity}.$

G7Z-3A1B-11Z




Note: The coil has no polarity.

G7Z-2A2B-11Z




Note: The coil has no polarity.

G7Z-4A-02Z




Note: The coil has no polarity.

G7Z-3A1B-02Z



Note: The coil has no polarity.

G7Z-2A2B-02Z




Note: The coil has no polarity.

Auxiliary Contact Block

G73Z-20Z



G73Z-11Z



G73Z-02Z



Safety Precautions

Refer to the "Precautions for All Relays" and "Precautions for All Relays with Forcibly Guided Contacts".

/!\ WARNING


Take measures to prevent contact with charged parts when using the Relay for high voltages.




/!\ CAUTION

Do not touch the terminal section (charged parts) when power is being supplied.

Always use the Relay with terminal covers mounted. Contact with charged parts may result in electric shock.









Precautions for Correct Use

Installation


• Mount the G7Z with the coil terminal at the top.




• Do not use the Relay with the terminal screw surfaces facing down.




To mount the Relay, secure M4 screws in two locations.
 Use a screw-tightening torque of 1.2 to 1.3 N·m.




- The Relay can be mounted directly on a mounting rail (PFP) or a DIN Track (EN 50022-35 × 7.5, 15). The Relay cannot be mounted, however, to some reinforced rails (e.g., those produced by Kameda Denki or Toyogiken).
- Mount the Relay sideways when it is mounted on a rail.
- Use End Plates (PFP-M) on both sides of the Relay to make sure that it is properly secured.



 Provide at least 5 mm of space between the sides and top of the Relay and nearby grounded metal surfaces.




 Provide at least 30 mm of space between Relays when two or more Relays are mounted in a row.



• The auxiliary contact block (G73Z) can be mounted on the Relay.

Mounting and Removal Mounting


Insert the tab on the auxiliary contact block into the groove on the Relay and press down until the hook on the auxiliary contact block catches in the mounting hole on the Relay.



Removing

Slide the auxiliary contact block, remove the auxiliary contact block tab from the groove on the Relay, and remove the auxiliary contact block hook from the Relay.


Be careful not to apply excessive force on the hook




Connecting

 Use round or open-end (Y-type) crimp terminals and connect the terminals with the appropriate tightening torque. Refer to the terminal section space in the following figure for the crimp terminal dimensions.


Relay Contacts (Unit: mm)



Relay Coil



Auxiliary Contact Block



 One crimp terminal can be used for the Relay contact section (M5 screw). Two crimp terminals can be connected for the coil terminal and auxiliary contact block.

Recommended Crimp Terminals and Wire

Location	Crimp terminals	Appropriate wire size
Contact	5.5-5	2.63 to 6.64 mm ² (AWG12, 10)
section	8-5	6.64 to 10.52 mm ² (AWG8)
Coil section	1.25-3.5	0.5 to 1.65 mm ² (AWG20 to 16)

 Use the following tightening torque when tightening screws. Loose screws may result in fire caused by abnormal heat generated when the power is being supplied.

M5 screws: 2.0 to 2.2 N·m M3.5 screws: 0.8 to 0.9 N·m


 Allow suitable slack on leads when wiring, and do not subject the terminals to excessive force.

Microloads

The G7Z is used for switching power loads, such as current carry for device power supplies and heater loads. Use an auxiliary contact block (G73Z) if microloads are required for signal applications and operation status feedback.

Coil

(Internal Connections of Coils) DC Coil




- If a transistor drives the G7Z, check the leakage current and connect a bleeder resistor if necessary.
- The must operate voltage is the minimum value for the Relay armature to operate and the contacts to turn ON. Therefore, fundamentally apply the rated voltage to the coils, taking into consideration the increases in coil resistance caused by voltage fluctuation and coil temperature rise.
- Counter-electromotive voltage generated by the coil when the coil
 is OFF may destroy semiconductor elements or cause
 malfunctions. Attach surge-absorbing diodes to both ends of the
 coil as a countermeasure. Particularly, when driving G7Z with
 semiconductor elements, always attach the surge-absorbing
 diodes

Note that the relay reset time will be extended, so always use after verifying implementation under actual usage conditions. Use surge-absorbing diodes with a minimum of 600 V reverse voltage resistance, and a forward current of approximately 1A. G7Z does not have coil polarity so attach surge-absorbing diodes so that the polarity is reverse to the applied voltage of the coil.

Mirror Contact Mechanism

By combining a Relay with an auxiliary contact block, all NC contacts of the auxiliary contact block will satisfy an impulse withstand voltage of 2.5 kV or higher or maintain a gap of 0.5 mm or greater when the coil is de-energized even if at least one NO contact (main contact) of the Relay is welded.

Description of Mirror Contact Mechanism



Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

2010.8

In the interest of product improvement, specifications are subject to change without notice.

