

User-Friendly Fiber-Optic Amplifier

Solve Your Basic Sensing Challenges Easily with the E3X-NA Series

- Streamlined features provide basic sensing immediately after plug-in
- *Wire-saving* amplifiers reduce installation time and minimize space requirements
- Master/slave connector design affords connectivity for up to 16 wire-saving amplifiers
- Use the LED bar display to quickly confirm sensor performance
- Optical communication design prevents mutual interference for up to 5 amplifiers
- Green LED models address mark-detecting applications
- High-speed models have a response time of 50 µs
- Select a water-resistant model (IP66 rating) using an M8 connector
- Prewired water-resistant models are available

Ordering Information: Amplifier Units, Connectors, Accessories and Fiber-Optics

Amplifier Units with Cables

Туре	Part number		Control output	Appearance	
	NPN output	PNP output			
Standard	E3X-NA11	E3X-NA41	ON/OFF	E I	
High-speed	E3X-NA11F	E3X-NA41F			
Mark-detection	E3X-NAG11	E3X-NAG41			
Water-resistant	E3X-NA11V	E3X-NA41V			



Connector-Ready Amplifiers (Order Connector Separately)

Item	Part number	Part number		Applicable connector		Appearance
	NPN output	PNP output	(order separa	ately)		
Wire-saving	E3X-NA6	E3X-NA8	Master E3X-CN11 (Slave E3X-CN12		ON/OFF output	
Water-resistant (M8 connectors)	E3X-NA14V	E3X-NA44V	XS3F-M421-40⊡-A XS3F-M422-40⊡-A			

Amplifier Unit Connectors (Order Separately)

Note: Stickers for Connectors are included as accessories.

Item	Appearance	Cable length	No. of conductors	Part number
Master Connector	Ĩ.	2 m	3	E3X-CN11
Slave Connector			1	E3X-CN12

+

+

Combining Amplifier Units and Connectors (Each Sold Separately)

Refer to the following tables when placing an order. Amplifier Units and Connectors are sold separately.

Amplifier Units				
Type NPN PNP				
Wire-saving models	E3X-NA6	E3X-NA8		

Applicable Connectors (Order Separately)				
Master Connector Slave Connector				
E3X-CN11 (3-wire)	E3X-CN12 (1-wire)			

Example: When Using 5 Amplifier Units

Amplifier Units (5 Units)

1 Master Connector + 4 Slave Connectors

Sensor I/O Connectors (Order Separately)

Size	Cable specifications	Appearance	Cable type		Part number
M8	Standard cable	Straight connector	2 m	Four-core cable	XS3F-M421-402-A
			5 m	1	XS3F-M421-405-A
		L-shaped connector	2 m	1	XS3F-M422-402-A
			5 m	1	XS3F-M422-405-A

Accessories (Order Separately)

Mounting Brackets

Appearance	Applicable models	Quantity	Part number
	E3X-NA E3X-NA E3X-NAG	1	E39-L143
Se Se	E3X-NA□V		E39-L148

End Plate

Appearance	Quantity	Part number
5	1	PFP-M

Fiber-Optic Cables

The E3X-NA amplifiers use Omron's E32-series fiber-optic cables. With a choice of over 80 sensing heads, you are sure to find one that matches your application requirements. Refer to the selection of E32 cables (listed with their respective sensing distances) in the fiber section at the end of this data sheet. Order fiber-optic cables separately.

Specifications

Amplifier Units

Ratings/Characteristics

Item		Amplifier Units with Cable	s			Connector-rea	Connector-ready amplifier units		
		Standard models	High-speed detection models	Mark-detecting models	Water-resistant models	Wire-saving models	Water-resistant models (use M8 connectors)		
Output type	NPN output	E3X-NA11	E3X-NA11F	E3X-NAG11	E3X-NA11V	E3X-NA6	E3X-NA14V		
	PNP output	E3X-NA41	E3X-NA41F	E3X-NAG41	E3X-NA41V	E3X-NA8	E3X-NA44V		
Light source (wa	avelength)	Red LED (680 nm)		Green LED Red LED (680 nm) (520 nm)					
Supply voltage		12 to 24 VDC ±10%, rippl	e (p-p): 10% max.		•				
Current consum	ption	35 mA max.	35 mA max. (for 24-VDC power supply)	35 mA max.					
Control output		NPN/PNP (depends on m	odel) open collect	tor; load current: 50) mA max.; residual	voltage: 1 V ma	IX.		
Operation mode	Switch- selectable	Light-ON/Dark-ON operat	ion						
Response time		200 µs max. for operation and reset respectively (See note.)	Operation: 20 μs max. Reset: 30 μs max.	200 μs max. for operation and reset respectively (See Note.)			e Note.)		
Sensitivity adjus	tment	8-turn sensitivity adjuster	8-turn sensitivity adjuster (with indicator)						
Circuit protection Reverse polarity, output short-circuit, mutual inter- ference prevention (opti- cally synchronized) Reverse polarity, output short-circuit, mutual interference short-circuit short-circuit				ence prevention					
Timer function		OFF-delay timer: 40 ms (fixed)							
Ambient illumina (receiver side)	ation	Incandescent lamp:10,000 Sunlight:20,000 lux max.) lux max.						
Ambient temper	ature	Operating: Groups of 1 to 3 Amplifiers: -25°C to 55°C (-13°F to 131°F) Groups of 4 to11 Amplifiers: -25°C to 50°C (-13°F to 122°F) Groups of 12 to16 Amplifiers: -25°C to 45°C (-13°F to 113°F) with no icing or condensation Storage: -30°C to 70°C (-22°F to 158°F) with no icing or condensation							
Ambient humidit	ty	Operating and storage: 35% to 85% (with no condensation)							
Insulation resist	ance	20 MΩ min. (at 500 VDC)							
Dielectric streng	th	1,000 VAC at 50/60 Hz fo	r 1 minute				500 VAC at 50/ 60 Hz for 1 minute		
Vibration resista	ince	10 to 55 Hz with a 1.5-mm double amplitude for 2 hrs each in X, Y and Z directions							
Shock resistanc	e	500 m/s ² , for 3 times each in X, Y and Z directions							
Enclosure rating		IEC60529 IP50 (with Prot	60529 IP50 (with Protective Cover attached)		IEC60529 IP66 (with Protective Cover attached)	IEC60529 IP50 (with Protective Cover at- tached)	IEC60529 IP66 (with Protective Cover attached)		
Connection met	hod	Prewired (standard cable	Prewired (standard cable length: 2 m)			Connector	M8 connector		
Weight (packed)	Approx. 100 g			Approx. 110 g	Approx. 55 g	Approx. 65 g		
Material	Case	Polybutylene terephthalate	e (PBT)						
	Cover	Polycarbonate			Polyethersulfone (PES)	Polycarbon- ate	Polyethersulfone (PES)		
Accessories		Instruction Sheet							


Note: When there are 8 or more Amplifier Units mounted side-by-side, the response time will be 350 μs max.

Amplifier Unit Connectors

Item		E3X-CN11 E3X-CN12		
Rated current		2.5 A		
Rated voltage		50 V		
Contact resista	nce	20 mΩ max. (20 mVDC max., 100 mA max.) (The above figure is for connection to the Amplifier Unit and the adjacent Connector. It does not include the conductor resistance of the cable.)		
Number of inse	ertions	50 times (for connection to the Amplifier Unit and	d the adjacent Connector)	
Material	Housing	Polybutylene terephthalate (PBT)		
	Contact	ntact Phosphor bronze/gold-plated nickel		
Weight (packed	d)	Approx. 55 g	Approx. 25 g	

Nomenclature


Amplifier Units



LED Bar Display

Indicators

In addition to an operation indicator (orange), the E3X-NA also has incident level indicators (4 green and 1 red). Use these indicators for optical axis adjustments and maintenance.




Note: The indicator farthest to the right will be lit even if the incident level is 0.

Operation

Output Circuits

Output	Model	Mode selector	Timing chart	State of output transistor	Output circuit
NPN	E3X-NA11 E3X-NA6 E3X-NA611 E3X-NA11F E3X-NA11V E3X-NA14V	LIGHT ON (L/ON)	Incident light No incident light Operation indicator ON (orange) OFF Output ON transistor OFF Load (relay) Operate Release (Between brown and black)	Light ON	Operation indicator (orange) Photo- electric Sensor main circuit Black Black Control output 3
		DARK ON (D/ON)	Incident light No incident light Operation indicator ON (orange) OFF Output transistor OFF Load (relay) Operate Release (Between brown and black)	Dark ON	M8 Connector Pin Arrangement
PNP	E3X-NA41 E3X-NA8 E3X-NA641 E3X-NA41F E3X-NA41V E3X-NA41V E3X-NA44V	LIGHT ON (L/ON)	Incident light No incident light Operation indicator ON (orange) OFF Output transistor OFF Load (relay) Operate Release (Between brown and black)	Light ON	Brown indicator (orange) electric sensor main circuit Black Control output Black Control output Load Blue Blue
		DARK ON (D/ON)	Incident light No incident light Operation indicator ON (orange) OFF Output ON transistor OFF	Dark ON	M8 Connector Pin Arrangement
			Release (Between brown and black		Note: Pin 2 is not used.

Connectors (Sensor I/O Connectors)



XS3F-M421-402-A, XS3F-M422-402-A XS3F-M421-405-A, XS3F-M422-405-A

Classification	Color of cable conductors	Connection pin number	Application
DC	Brown	1	Power supply (+V)
	White	2	
	Blue	3	Power supply (0 V)
	Black	4	Output

Note: Pin 2 is not used.