
# Photoelectric Sensor with Built-in Amplifier (Ultracompact and Thin Type)

Additions to the Series

# Small but Sharp Slimmest BGS\* Reflective Sensors in the Market

- Series now includes BGS reflective model with black/ white error of 15%
- Easy optical axis adjustment with emitter axis accuracy of ±2° (Through-beam Model)
- Noise and external light resistance enhanced to that of E3Z or equivalent
- Complete Compliance with RoHS
- The Series includes models with M12 Smartclick prewired connectors (-M1TJ) Smartclick
- \* BGS (Background Suppression) technology prevents detecting background objects.





# Features

## The Slimmest BGS (Background Suppression) Reflective Photoelectric Sensors in the World

Ultra slim at 3.5 mm and black/white error of only 15%.

For example, the E3T-FL1 can stably detect a black object at 12 mm without being affected by a white background at 20 mm.

**OMRON** provides BGS performance sharper than the previous Convergentreflective Sensors.

the ultimate in miniature

mounting technology for

E3T-FL possible.

attaching IC chips without


even with a two-part light receiving element on the surface

covering them in resin, is what


makes the slim structure of the

The E3T-FL is just 3.5 mm wide,

of the circuit board and a signal



### **Dramatic Improvement in Black/White Error**




## State-of-the-Art Technology Achieved Ultra Thin BGS

## First Mounted Flip Chip in Industry Patent Pending

This shape and slimness make a massive contribution to resolving issues, such as sensor space constraints. Flip-chip mounting technology,

Flip chip (IC) Light receiving element



### High-precision Alignment Technology Patent Pending

High-precision alignment technology is greatly contributing to reducing installation and adjustment work onsite.

The E3T-FL sensing distances are subtly controlled using high-precision alignment technology, which aligns the optical axes of more than one part.

The light receiving lens with its unique thinwalled structure is automatically adjusted inline to keep sensing distance fluctuations to a minimum.



processing IC on the rear. Flip-chip mounting of the IC has enabled the mounting volume to be kept to the absolute minimum.

## **Upgraded Products**

#### E3T-ST Through-beam (Side View) Models/ E3T-FT Through-beam (Flat) Models

Long-distance detection Side-view Models: 1 m, Flat Models: 500mm 300-mm Models are also available to prevent mutual interference. Minimum detection object: 0.5 mm dia. (with slit attached) Optical axis accuracy of  $\pm 2^{\circ}$  for installation reliability. Easily distinguish between color-coded Emitter and Receiver lenses.




#### E3T-SL Convergent-reflective Models (Side-view)

Minimum detection object: 0.15 mm dia. Resistant to background and surrounding metal



#### E3T-SR Retro-reflective Models (Side-view) \* Twin-lens Optical System

Two models for different reflector characteristics. E3T-SR2: With E39-R4, Sensing distance: 200 mm E3T-SR3: With E39-R37, Sensing distance: 100 mm




#### E3T-FD Diffuse-reflective Models (Flat)

Minimum detection object: 0.15 mm dia. Only 3.5 mm wide for installation in small gaps.




## **Reliability to the Performance Improved by Product Upgrades**



# Complete Compliance with RoHS

Lead, mercury, cadmium hexachrome, polybrominated biphenyl (PBB), and polybrominated diphenyl ether (PBDE) have all been removed. And burnable polyethylene packaging has been used.





Models with PNP Output



# **Ordering Information**

Sensors							Red light
Sensing	Арреа	arance	Connection	Sensing	Operation	Mod	lel
method	Apper		method	distance	mode	NPN output	PNP output
		Side-view		1 m	Light-ON	E3T-ST11*2*3	E3T-ST13
	8			(Sensitivity Adjustment Unit can be used.)	Dark-ON	E3T-ST12*2*3	E3T-ST14
	TT			300 mm	Light-ON	E3T-ST21*3	E3T-ST23
Through-			-		Dark-ON	E3T-ST22 <sup>*3</sup>	E3T-ST24
beam		Flat		500 mm	Light-ON	E3T-FT11*2*3	E3T-FT13
				500 mm	Dark-ON	E3T-FT12*2*3	E3T-FT14
				200 mm	Light-ON	E3T-FT21*3	E3T-FT23
				300 mm	Dark-ON	E3T-FT22*3	E3T-FT24
	<b>(</b>	Side-view		For E39-R4 only	Light-ON	E3T-SR21 <sup>*2*3</sup>	E3T-SR23
Retro-				200 mm (10 mm)*1	Dark-ON	E3T-SR22*2*3	E3T-SR24
reflective		Side-view	Pre-wiredv	For E39-R37 only	Light-ON	E3T-SR31 <sup>*2*3</sup>	E3T-SR33
				100 mm (10 mm) <sup>*1</sup>	Dark-ON	E3T-SR32 <sup>'2'3</sup>	E3T-SR34
Diffuse-	LET - POL	Flat			Light-ON	E3T-FD11'2'3	E3T-FD13
reflective				5 to 30 mm	Dark-ON	E3T-FD12'2'3	E3T-FD14
		Side-view			Light-ON	E3T-SL11*2*3	E3T-SL13
Convergent-	8	ก 🗸 เ		5 to 15 mm	Dark-ON	E3T-SL12*2*3	E3T-SL14
reflective				5 to 30 mm	Light-ON	E3T-SL21*2*3	E3T-SL23
					Dark-ON	E3T-SL22*2*3	E3T-SL24
		Flat		1 to 15 mm	Light-ON	E3T-FL11*2*3	E3T-FL13
BGS reflective	East-96.99				Dark-ON	E3T-FL12 *2*3	E3T-FL14
renective	T			1 to 30 mm	Light-ON	E3T-FL21*2*3	E3T-FL23
					Dark-ON	E3T-FL22 <sup>*2*3</sup>	E3T-FL24

Note: Models with M12 Smartclick pre-wired connectors are also available for all models in the table. The cable is 0.3 m long. When ordering, add "-M1J" to the end of the model number (e.g., E3T-ST11-M1TJ 0.3M)
\*1. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
\*2. A Robotics Cable is provided for models in the table marked with "2. These models have an R suffix. (Example: E3T-ST11R)
\*3. An e-CON Pre-wired Connector with a 0.3 m or 2 m cable is provided for models in the table marked with "3. These models have an -ECON suffix. (Example: E3T-ST11-ECON 2M). The connector is the E-39-ECON with a 2-m or 5-m cable and a connector on one end or the E39-ECONW with a 0.5-m to 2-m cable (length increases in 0.1-m increments) and connectors at both ends. The length of the cable is marked on the box. (Example: E39-ECON2M) This e-CON specification is rapidly becoming the standard for FA equipment and connector manufacturers.

#### Accessories (Order Separately) Slits

Slit width	Sensing distance (typical) (Sensor model)	Minimum detectable object (typical)	Model	Quantity	Remarks	
0.5-mm dia.	100 mm (E3T-ST1⊡)	0.5-mm dia.				
0.5-mm dia.	30 mm (E3T-ST2⊡)	0.5-mm dia.	E39-S63		Plug-in type round slits Can be used with E3T-ST	
1-mm dia.	300 mm (E3T-ST1⊡)	1-mm dia.	E39-303		Through-beam Models.	
I-min uia.	100 mm (E3T-ST2⊡)	- I-min ula.		One each for Emitter and Receiver; common with Slit		
0.5-mm dia.	50 mm (E3T-FT1⊡)	0.5 mm dia		widths of 1 dia. and 0.5 dia. (total of 2)		
0.5-mm uia.	30 mm (E3T-FT2⊡)	0.5-mm dia.	E39-S64	500.004		Plug-in type round slits Can be used with E3T-FT□□
1-mm dia.	100 mm (E3T-FT1⊡)	1-mm dia.		39-504	Through-beam Models.	
r-min ula.	50 mm (E3T-FT2⊡)	i -inin ula.				

### Reflectors

Name	Sensing distance (Sensor model)	Minimum detectable object (typical)	Model	Quantity	Remarks
Small	200 mm (10 mm) * (E3T-SR2⊡)	2 mm dia.	E39-R4		Provided with the E3T-SR2 Retro-reflective Models.
Reflectors	100 mm (10 mm) * (E3T-SR3⊡)	2 mm uia.	E39-R37		Provided with the E3T-SR3D Retro-reflective Models.

\* Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

### Sensitivity Adjustment Unit

Appearance	Sensing distance (typical)	Model	Quantity	Remarks
	300 to 800 mm	E39-E10	1	Can be used with the E3T-ST1□ Through-beam Models.

### **Mounting Brackets**

Appearance	Model	Quantity	Remarks
	E39-L116		Can be used with the
	E39-L117		E3T-S Side-view Models. (A securing nut plate is provided with the
	E39-L118	1	Mounting Bracket.)
	E39-L119		Can be used with the
	E39-L120		E3T-F

Note: When using Through-beam models, order one bracket for the Receiver and one for the Emitter.

### Sensor I/O Connectors

Size	Cable	Appearance	Cable	type	Model
M12 (For -M1TJ	Standard	Straight	2 m	4-wire	XS5F-D421-D80-A
models)	Standard	or angle	5 m	4-0016	XS5F-D421-G80-A
		Connector on one end	2 m		E39-ECON2M
			5 m		E39-ECON5M
e-CON	Standard cable	Connector on both ends	0.5 to 1 m	4-wire	E39-ECONW□M
			1.1 to 1.5 m		Replace $\Box$ with the cable length in
			1.6 to 2 m		0.1-m increments.

# OMRON

# **Ratings and Specifications**

			Throug	h-beam		Retro	-reflective (witl	nout M.S.R. fun	iction)	
		Side	view	F	lat		Side	-view		
Sonoing m	othod	NPN	PNP	NPN	PNP	NPN	PNP	NPN	PNP	
Sensing m	letiloù	E3T-ST11 E3T-ST12 E3T-ST21 E3T-ST22	E3T-ST13 E3T-ST14 E3T-ST23 E3T-ST24	E3T-FT11 E3T-FT12 E3T-FT21 E3T-FT22	E3T-FT13 E3T-FT14 E3T-FT23 E3T-FT24	E3T-SR21 E3T-SR22	E3T-SR23 E3T-SR24	E3T-SR31 E3T-SR32	E3T-SR33 E3T-SR34	
Sensing d	istance	E3T-ST1□ E3T-ST2□	1 m 300 mm	E3T-FT1 E3T-FT2	500 mm 300 mm	E3T-SR2□ 200 (For E39-R4 of	```	E3T-SR3□ 100 (For E39-R37 0	```	
Standard s object	sensing	Opaque, 2-mn	n dia. min.	Opaque, 1.3-r	mm dia. min.	Opaque, 27-m	m dia. min.			
Minimum o able objec		2-mm dia opa	que object	1.3-mm dia op	paque object	2-mm dia. (ser	ising distance o	f 100 mm)		
Hysteresis (white pap										
Black/whit	e error									
Directiona	l angle	Emitter: 2° t Receiver: 2° t	to 20° to 70°	Emitter: 3° Receiver: 3°	to 25° min.	2° to 20°				
Light sour (waveleng		Red LED ("Pir	η-point" LED) $\lambda$	= 650 nm						
Power sup voltage	ply	12 to 24 VDC	±10%, ripple (p	p-p) 10% max.						
Current consumpt	ion		Emitter 10 mA r		20 mA max.)	20 mA max.				
Control ou	Itput	Load current: Open-collecto Light ON: E3T		sidual voltage: 2 3T-□□□3	V max. for load	current of 10 to 50	) mA, 1 V max. fo	r load current of l	ess than 10 mA)	
Protection	circuits		and control out		arity protection			ut reverse polar Mutual interfere		
Response	time	Operate or reset: 1 ms max.								
Ambient illuminatio	n	Incandescent Sunlight:	lamp: 5,000 lx 10,000 lx							
Ambient temperatu	re range	Operating: -25 to 55°C Storage: -40 to 70°C (with no icing or condensation)								
Ambient h range	umidity	Operating: 35% to 85% Storage: 35% to 95% (with no condensation)								
Insulation resistance		20 M $\Omega$ min. at	20 MΩ min. at 500 VDC							
Dielectric	strength	1,000 VAC, 50/60 Hz for 1 min								
Vibration resistance		Destruction: 10 to 2,000 Hz, 1.5-mm double amplitude or 300 m/s <sup>2</sup> for 0.5 hrs each in X, Y, and Z directions								
Shock res	istance	Destruction: 1,000 m/s <sup>2</sup> 3 times each in X, Y, and Z directions								
Degree of protection		IP67 (IEC6052	29)							
Connection method		Pre-wired (sta	ndard length: 2	m)						
Weight		Approx. 40 g				Approx. 20 g				
	Case	PBT (polybuty	lene terephthal	ate)		1				
Materials	Display window	Denatured pol	yarylate							
	Lens	Denatured pol	yarylate			Methacrylic res	sin			
Accessori	es		nual, Installatio ·R4 (E3T-SR2□			dels: M2 × 14, F only)	lat Models: M2 >	< 8), Nuts, Spring	g washers, Flat	

\* Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

		Diffuse-r	eflective		Converger	t-reflective			BGS re	flective		
		FI	at		Side	-view	Flat					
<b>.</b>		NPN	PNP	NPN	PNP	NPN	PNP	NPN	PNP	NPN	PNP	
Sensing m	ietnoa	E3T-FD11 E3T-FD12	E3T-FD13 E3T-FD14	E3T-SL11 E3T-SL12	E3T-SL13 E3T-SL14	E3T-SL21 E3T-SL22	E3T-SL23 E3T-SL24	E3T-FL11 E3T-FL12	E3T-FL13 E3T-FL14	E3T-FL21 E3T-FL22	E3T-FL23 E3T-FL24	
Sensing di	istance	5 to 30 mm (50 × 50 mm		5 to 15 mm (50 × 50 mm		5 to 30 mm (50 × 50 mm		1 to 15mm (50 × 50 mm	white paper)	1 to 30mm (50 × 50 mm	white paper)	
Standard s object	sensing											
Minimum of able object		0.15-mm di	a. (sensing o	listance of 1	0 mm)				a non-glossy stance of 10			
Hysteresis (white pap		6 mm max.		2 mm max.		6 mm max.		0.5 mm ma	х.	2 mm max.		
Black/whit	e error							15% max.				
Directiona	l angle											
Light sour (waveleng		Red LED ("	Pin-point" LE	ED) λ = 650	nm							
Power sup voltage	ply	12 to 24 VD	0C ±10%, rip	ple (p-p) 10º	% max.							
Current consumpti	ion	20 mA max										
Control ou	itput	Load currer Open-collec Light ON: E		x. (residual v and E3T- $\Box\Box$	oltage: 2 V m ⊡3	ax. for load cu	urrent of 10 to	50 mA, 1 V m	ax. for load c	urrent of less	than 10 mA)	
Protection	circuits		Power supply and control output reverse polarity protection Dutput short-circuit protection, Mutual interference prevention									
Response	time	Operate or reset: 1 ms max.										
Ambient illuminatio	'n	Incandescent lamp: 5,000 lx max. Sunlight: 10,000 lx max.										
Ambient temperatu	re range	Operating: -25 to 55°C Storage: -40 to 70°C (with no icing or condensation)										
Ambient h range	umidity	Operating: 35% to 85% Storage: 35% to 95% (with no condensation)										
Insulation resistance	1	20 MΩ min. at 500 VDC										
Dielectric	strength	1,000 VAC, 50/60 Hz for 1 min										
Vibration resistance	!	Destruction: 10 to 2,000 Hz, 1.5-mm double amplitude or 300 m/s <sup>2</sup> for 0.5 hrs each in X, Y, and Z directions										
Shock resistance		Destruction: 1,000 m/s <sup>2</sup> 3 times each in X, Y, and Z directions										
Degree of protection		IP67 (IEC60529)										
Connection method		Pre-wired (standard length: 2 m)										
Weight		Approx. 20	g									
	Case	PBT (polyb	utylene terep	ohthalate)								
Materials	Display window	Denatured	polyarylate									
	Lens	Denatured	polyarylate									
Accessori	es	Instruction r washers	nanual, Insta	allation philli	p screws (Sid	de-view Mod	els: M2 $ imes$ 14,	Flat Models	: M2 × 8), Nu	ts, Spring wa	shers, Flat	

# I/O Circuit Diagrams

NPN	Output	
	Output	


Model	Operation mode	Timing charts	Output circuit
E3T-0001	Light-ON	Light incident Light interrupted Operation indicator ON (orange) OFF Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	Through-beam Receivers, Retroreflective and Reflective Models Operation (orange) (crange) Hoto- electric Sensor (indicator (crange) Hoto- electric Sensor (control output) Black Blue 0 V
E3T-002	Dark-ON	Light incident Light interrupted Operation indicator ON (orange) OFF Output transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	Connector Pin Arrangement Through-beam Emitters Photo- electric Bensor Main Crcuit Blue Blue Blue Blue Note: Pin 2 is not used. Pins 2 and 4 are not used with Through-beam Emitters.

### **PNP Output**

Model	Operation mode	Timing charts	Output circuit
E3T-□□□3	Light-ON	Light incident Light interrupted Operation indicator ON (orange) OFF Output transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	Through-beam Receivers, Retroreflective and Reflective Models Operation (orange) Photo- electric Sensor Control output Black Black Black Black Control output Black Control output Control output Contr
E3T-□□□4	Dark-ON	Light incident Light interrupted Operation indicator ON (orange) OFF Output ON Load Operate (e.g., relay) Reset (Between blue and black leads)	Connector Pin Arrangement Through-beam Emitters M12 e-CON M12 e-CON 12 to 24 VDC Blue Note: Pin 2 is not used. Pins 2 and 4 are not used with Through-beam Emitters.

# Plugs (Sensor I/O Connectors) M12 Connector

E39-ECON M



	Classification	Wire color	Connector pin No.	Application
		Brown	1	Power supply (+V)
9-ECON□M	DC	White	2	
<b></b> A	DC	Blue	3	Power supply (0 V)
		Black	4	Output

Note: Pin 2 is not used.

OMRON

e-CON

[]]; [

0 15.8

## Dimensions

