







DATE

DESCRIPTION

REV.

5.31.11 CHANGE AS PER ECN 11-075

A



Notes:

Shell: Matt'l: Phosphor Bronze,

Finish: Nickel Plate

Insulator: Matt'l: Glass fiber

UL 94V-0

Contacts: Matt'l: Phosphor Bronze

Finish: Gold Plate over Nickel on contact area.

Tin Plate over nickel on solder Tail.

Electrical Specifications

Contact Resistance: 30 milliohms Max.

Insulation Resistance: 1000 Mega Ω min.

Dielectric Voltage: 500V AC

KEYSTONE ELECTRONICS CORP.

www.keystec.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

USB MINI TYPE HORIZONTAL SOCKET

MATERIAL

AS NOTED

FINISH

AS NOTED

TOLERANCES	INCH	[MM]	CODE
DECIMAL	$\pm .010$	[± 0.25]	C/M
ANGULAR	$\pm 1^\circ$		

DRN BY	DATE	APP'D	DWG NO.
NT	12.17.08	LN	934

SCALE 5X

THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.