
#### Magnecraft

#### Item # 782XBX3M4L-24A, 782 Ice Cube Relays / DPDT, 3-10 Amp Rating





# <u>SPECIFICATIONS</u> · <u>COIL CHARACTERISTICS</u> · <u>PERFORMANCE CHARACTERISTICS</u> · <u>ENVIRONMENT</u>

## SPECIFICATIONS

Terminal Style	Plug-in
Contact Configuration	DPDT
Thermal (Carrying) Current	3 A
Control	AC
Coil Resistance	180 Ohm
Load Type	Low Level
Contact Materials	Bifurcated
Maximum Switching Voltage	300 V
Switching Current at Voltage (AC, Resistive)	3 A at 120 V 50/60 Hz 3 A at 277 V 50/60 Hz
Switching Current at Voltage (DC, Resistive)	3 A at 30 V
Switching Current at Voltage	1/16 at 120 VAC hp
Minimum Switching Requirement	10 mA at 5 VDC (0.05W)

Features	Locking push button Bi-polar LED Removable ID tag Mechanical flag indicator
Cover Options	Full Featured
Pilot Duty	B300

## COIL CHARACTERISTICS

Coil Voltage	24 VAC 50/60 Hz
Operating Range - % of Nominal (AC)	85 to 110 %
Operating Range - % of Nominal (DC)	80 to 110 %
Average Consumption (AC)	1.2 VA
Average Consumption (DC)	0.9 W
Drop-out Voltage Threshold (AC)	15 %
Drop-out Voltage Threshold (DC)	10 %

## PERFORMANCE CHARACTERISTICS

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
Mechanical Life, Unpowered	1000000
Operating Time (Response Time)	20 ms
Dielectric Strength - Between Coil and Contact (AC)	1500 V(rms)
Dielectric Strength - Between Poles (AC)	1500 V(rms)
Dielectric Strength - Between Contacts (AC)	1500 V(rms)

#### ENVIRONMENT

Product Certifications, Standard Version	CE CSA RoHS UL
Ambient Air Temperature around the Device - Storage	-40 to +85 °C
Ambient Air Temperature around the Device - Operation	-40 to +55 °C
Vibration Resistance - Operational	3 g-n at 10-55 Hz
Shock Resistance	10 g-n
Degree of Protection	IP 40
Weight	36 G