


- ▶ **Product Category**
- ▶ Sensors
- ▶ Photoelectric Sensors
- ▶ Optical Fiber Sensors
- ▶ Fiber Units
- ▶ E32 Series
- ▶ **Item list**

- ▶ **Product Category**
- ▶ A to Z Index
- ▶ Applications
- ▶ Cautions

Fiber Sensors

E32-T11

Through-beam , Break-resistant , Standard size , M4 screw , Minimum bending radius R4



CG Image [3D-CAD]

[about this Product Family](#)

[Inquiry of this Product](#)

[Ratings / Performance](#)

[Dimensions](#)

As of June 24, 2011

Product outline	M4 screw head through-beam fiber, Flex-resistant fiber
Sensing method	Through-beam
Shape	Screw-shaped Top view
Fiber cable type	Break-resistant
Standard Length	2m
Minimum bending radius	R 4 mm Min.
Free-cut	Possible
Degree of protection	IEC60529: IP67
Opening size	1 dia.
Ambient temperature	Operating: -40 to 70 CEL Storage: -40 to 70 CEL (with no icing or condensation)
Ambient humidity	Operating: 35 to 85 %RH Storage: 35 to 95 %RH (with no icing)
Vibration resistance	10 to 55 Hz1.5-mm double amplitude for 2 hours each in X, Y, and Z directions
Shock resistance	500m/s ² for 3 times each in X, Y, and Z directions
Weight (packedstate)	Approx. 40 g
Material (Sensing head)	Brass nickel plating
Material (Fiber sheath)	Plastic (PVC coating)
Material (Fiber core)	Acrylic resin (PMMA)
Material (Clamping nuts)	Brass nickel plating
Material (Toothed washer)	Iron nickel plating
Tensile strength	29.4 N Max.
Clamping torque	0.78 N.m Max.
Accessories	Hexagonal nut, Toothed washer, Fiber cutter(E39-F4)

As of June 24, 2011