A165K

Separate Construction with Cylindrical 16-dia. Body

- Short mounting depth, less than 28.5 mm below panel
- Wide range of switching capacity from standard to microload
- Oil-resistant IP65 models





List of Models


	Model							
	Rectangular	Square	Round					
Solder terminals	A165K-J Series	A165K-A Series	A165K-T Series					
Screw- less clamp connector	A165K-J Series	A165K-A Series	A165K-T Series					

OMRON 1

Model Number Structure

Model Number Legend......The model numbers used to order sets of Units are illustrated below. One set comprises the Selector, Switch, and 2 Keys.

For information on combinations, refer to Ordering Information on page 3.



(1) Shape of Selector —

Symbol	Shape	Color
J	Rectangular	
Α	Square	Black
Т	Round	

(2) Number of Notches/Resetting Method

· ·						
Symbol	No. of notches	Reset method	Key release position			
2ML			Left			
2MR	2 notches	Manual	Right			
2M	2 110101165		Left and right			
2AL		Automatic	Left			
ЗМС		hes Manual	Center			
3MR			Right			
3ML	3 notches		Left			
ЗМ			Left, right, and center			
ЗАС	3 notches	Automatic	Center			

(3) Contact Configuration

Symbol Type		Terminal
1	SPDT	Solder Terminal
2	DPDT	Solder reminal
2S	DPDT	Screw-less Clamp

Note: Only DPDT contacts are available with 3-notch models.

Ordering Information

Ordering as a SetThe model numbers used to order sets of Units are given in the following tables. One set comprises the Selector, Switch and 2 Keys.

Solder Terminals

Rectangular Models

Oil-resistant IP65



Number of notches	Output	Reset method		Key release position	Model
				Left	A165K-J2ML-1
	SPDT	Manual	\checkmark	Right	A165K-J2MR-1
	SEDI			Left and right	A165K-J2M-1
2 notches		Automatic	\Diamond	Left	A165K-J2AL-1
2 notches	DPDT		<u> </u>	Left	A165K-J2ML-2
		Manual		Right	A165K-J2MR-2
				Left and right	A165K-J2M-2
		Automatic	\Diamond	Left	A165K-J2AL-2
			\	Center	A165K-J3MC-2
2 notoboo	DPDT	Manual		Right	A165K-J3MR-2
3 notches	וטאט	ivialiual		Left	A165K-J3ML-2
				Left, right, and center	A165K-J3M-2

Square Models

Oil-resistant IP65



Number of notches	Output	Reset method		Key release position	Model
				Left	A165K-A2ML-1
	SPDT	Manual	\\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	Right	A165K-A2MR-1
	SPDT			Left and right	A165K-A2M-1
2 notches		Automatic	\Diamond	Left	A165K-A2AL-1
2 notches	DPDT		~	Left	A165K-A2ML-2
		Manual		Right	A165K-A2MR-2
				Left and right	A165K-A2M-2
		Automatic	\Diamond	Left	A165K-A2AL-2
				Center	A165K-A3MC-2
O notoboo	DPDT	Manual		Right	A165K-A3MR-2
3 notches	וטייט	Manual	\vee	Left	A165K-A3ML-2
				Left, right, and center	A165K-A3M-2

Round Models




Oil-resistant IP65


Number of notches	Output	Reset method		Key release position	Model
				Left	A165K-T2ML-1
	SPDT	Manual	\sim	Right	A165K-T2MR-1
	SPDT			Left and right	A165K-T2M-1
2 notches		Automatic	\Diamond	Left	A165K-T2AL-1
2 Holdnes	DPDT	Manual	<u> </u>	Left	A165K-T2ML-2
				Right	A165K-T2MR-2
				Left and right	A165K-T2M-2
		Automatic	\Diamond	Left	A165K-T2AL-2
				Center	A165K-T3MC-2
3 notches	DPDT	Manual		Right	A165K-T3MR-2
3 HOICHES	וטוטו	ivialiual	\\ \	Left	A165K-T3ML-2
				Left, right, and center	A165K-T3M-2

Ordering Information

Ordering Individually....... Selectors and Switches can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.







Ordering Information

Ordering Individually Selectors and Switches can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

Selectors

Appearance	Number of notches	Reset method	Key release position	Model
Rectangular			\bigcirc	A165K-J2ML
(A165K-J)	2 notches	Manual	Ø	A165K-J2MR
	2 Holdries		\otimes	A165K-J2M
		Automatic 🕥	\bigcirc	A165K-J2AL
			1	A165K-J3MC
		Manual	\bigcirc	A165K-J3MR
	3 notches	Manual	\bigcirc	A165K-J3ML
			*	A165K-J3M
		Automatic (i)	1	A165K-J3AC
Square (A165K-A)			\bigcirc	A165K-A2ML
	2 notches	Manual	Ø	A165K-A2MR
	2 notches		\otimes	A165K-A2M
		Automatic 🕥	\bigcirc	A165K-A2AL
			1	A165K-A3MC
1 3 Ell		Manual	Ø	A165K-A3MR
	3 notches	Manual	\bigcirc	A165K-A3ML
			*	A165K-A3M
		Automatic (i)	(1)	A165K-A3AC
lound		<u> </u>	<u> </u>	A165K-T2ML
A165K-T)	0	Manual	Ø	A165K-T2MR
	2 notches		\otimes	A165K-T2M
		Automatic 🕥	<u> </u>	A165K-T2AL
		<u> </u>	1	A165K-T3MC
		Manual	\bigcirc	A165K-T3MR
	3 notches	Manual	\bigcirc	A165K-T3ML
			*	A165K-T3M
		Automatic (i)		A165K-T3AC

Switches

Appearance		Classif	fication		Model
		2 notches	SPDT		A16S-2N-1
		2 Holdnes	DPDT	Solder terminal	A16S-2N-2
	Switch	3 notches	DPDT		A16S-3N-2
		2 notabos	SPDT	DCP terminal	A16S-2N-1P
		2 notches	DPDT	PCB terminal	A16S-2N-2P

Switches with Screw-less Clamp

Appearance		Model	Remarks			
	Common to standard	DPDT	2 notches	- Non-lighted -	A16-2S	Common to ones for pushbutton switches.
	load and microload.	DFD1	3 notches		A16S-3N-2LS	

OMRON

Specifications

Approved Standard Ratings UL, cUL (File No. E41515)

5 A at 125 VAC, 3 A at 250 VAC (general use) 3 A at 30 VDC (resistive)

EN60947-5-1 (Low Voltage Directive)

3 A at 250 VAC 3 A at 30 VDC

Ratings Contacts

Rated voltage Resistive load 125 VAC 5 A 250 VAC 3 A 30 VDC

Minimum applicable load: 1 mA at 5 VDC

Rated values are obtained from tests conducted under the following conditions.

3 A

- 1. Load: Resistive load
- 2. Mounting conditions: No vibration and no shock 3. Temperature: 20±2°C
- 4. Operating frequency: 20 times/min

Characteristics Socket Units

Item	Туре	Key-type Selector Switch
Allowable	Mechanical	20 operations/minute max.
operating frequency	Electrical	10 operations/minute max.
Insulation re	sistance	100 MΩ min. (at 500 VDC)
	Between terminals of same polarity	1,000 VAC, 50/60 Hz for 1 minute
Dielectric strength	Between terminals of different polarity	2,000 VAC, 50/60 Hz for 1 minute
	Between each ter- minal and ground	2,000 VAC, 50/60 Hz for 1 minute
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)
Shock resistance	Destruction	500 m/s ²
	Malfunction	150 m/s ² max. (malfunction within 1 ms)
Durability	Mechanical	250,000 operations min. (durability of key: 10,000 operations min.)
	Electrical	100,000 operations min.
Electric shoo	ck protection	Class II
PTI (tracking	characteristic)	175
Degree of co	ntamination	3 (IEC60947-5-1)
Weight		Approx. 26.5 g (in the case of a DPDT switch key)
Ambient operating temperature		−10°C to 55°C (with no icing or condensation)
Ambient ope	rating humidity	35% to 85%RH
Ambient sto temperature	rage	−25°C to 65°C (with no icing or condensation)

Screw-less Clamp

Item	Туре	Screw-less Clamp					
Recomme	nded wire size	0.5 mm ² t	0.5 mm² twisted wire or 0.8 mm-dia. solid wire				
Usable	Twisted wire	0.3 mm ²	0.5 mm ²	0.75 mm ²	1.25 mm ²		
wires and tensile strength	Solid wire	0.5 mm dia.	0.8 mm dia.	1.0 mm dia.			
	Tensile strength	10 N	20 N	30 N	40 N		
Length of	exposed wire	10 ±1 mm					
Complian	t standards	JIS C 2811 Terminal Blocks for Industrial Use					


Contact Form

Name	Contact form		
SPDT	COM NO		

Operating Characteristics

Туре	Key-type Selector Switch			
Characteristics	2 notches	3 notches		
Operating force (OF) max.	0.1 N·m			
Set position (SP)	90±5°	45° +10		

Operation Angle



Note: The angle used for automatic reset is shown in parentheses. FP: Free position


Contact Configuration


		Contact configuration							
	No. of	SPDT		DPDT					
	notches	Posi- tion	sw	Posi- tion	SW1	SW2			
	2 notches	0	•	0	•	•			
		\odot	%	\odot	%	<i>و</i> ا			
	3 notches		\odot	م	•				
			\bigcirc	••	•				
				\bigcirc	90	• 6			




Dimensions (Unit: mm)

Rectangular A165K-J Solder terminals (tab terminals #110)












Square A165K-A


Solder terminals (tab terminals #110)







* Refer to the A165S/W for Panel cutouts.



/M16×1

Round A165K-T

Solder terminals (tab terminals #110)



