

HIGH TEMPERATURE LEAD WIRE

TYPE MG - UL STYLE 5107

450°C-600 VOLTS

| UL LISTED | |
|--------------------|------------|
| CSA APPLIED | FOR |

DESCRIPTION:

Flexible, stranded, 27% nickel-clad copper conductor, glass reinforced mica tapes insulation, glass braid jacket impregnated with high temperature finisher (tan), optional colors available on request

PHYSICAL PROPERTIES:

Superior resistance to high temperature and the effects of radiation, insulating materials retain their integrity after exposure to 10^{12} Roentgens of radiation

APPLICATION:

For wiring in ovens and other high temperature equipment where temperatures do not exceed 450°C NON UL

NOMINAL THICKNESSES:

Insulation: 22-12 AWG .025", 10-4 AWG .030", 2-4/0 AWG .035" Jacket: 22-12 AWG .007", 10-4 AWG .015", 2-4/0 AWG .020"

| OLYMPIC NO. | CO AWG | NDUCTOR STRANDING | NOM. O.D. | NOM. BEND RADIUS |
|----------------|-----------|----------------------|--------------|---------------------|
| 500 | 22 | 7 x 30 | .10" | .60" |
| 501 | 20 | 10 x 30 | .11" | .66" |
| 502 | 18 | 16 x 30 | .12" | .72" |
| 503 | 16 | 26 x 30 | .13" | .78" |
| 504 | 14 | 41 x 30 | .14" | 1.12" |
| 505 | 12 | 65 x 30 | .15" | 1.20" |
| 516 | 10 | 105 x 30 | .22" | 1.76" |
| 507 | 8 | 133 x 29 | .26" | 2.60" |
| 508 | 6 | 133 x 27 | .31" | 3.10" |
| 509 | 4 | 133 x 25 | .36" | 4.32" |
| 510 | 2 | 133 x 23 | .45" | 5.40" |
| 511 | 1 | 259 x 25 | .50" | 6.00" |
| 512 | 1/0 | 259 x 24 | .54" | 6.48" |
| 513 | 2/0 | 259 x 23 | .60" | 7.20" |
| 514 | 3/0 | 259 x 22 | .66" | 7.92" |
| 515 | 4/0 | 259 x 21 | .72" | 8.64" |
| | | | | |

TYPE MG - UL STYLE 5128

UL LISTED

NOTE:

Description, physical properties and application are same as 600V above

NOMINAL THICKNESSES:

Insulation: 22-12 AWG .015", 10-4 AWG .020" Jacket: 22-12 AWG .007", 10-4 AWG .015"

450°C-300 VOLTS

| 520 | 22 | 7 x 30 | .080" | .60" |
|-----|----|----------|-------|-------|
| 521 | 20 | 10 x 30 | .090" | .66" |
| 522 | 18 | 16 x 30 | .100" | .72" |
| 523 | 16 | 26 x 30 | .110" | .78" |
| 524 | 14 | 41 x 30 | .130" | 1.12" |
| 525 | 12 | 65 x 30 | .150" | 1.20" |
| 526 | 10 | 105 x 30 | .200" | 1.76" |
| 527 | 8 | 133 x 29 | .240" | 2.60" |
| 528 | 6 | 133 x 27 | .290" | 3.10" |
| 529 | 4 | 133 x 25 | .340" | 4.32" |
| | | | | |

TYPE TGGT - UL STYLE 5251, CSA TYPE C3

250°C-600 VOLTS

UL LISTED AND CSA

DESCRIPTION:

Flexible, stranded, 10% nickel-plated copper conductor, Teflon (TFE) tape wrapped, ceramic tape insulation, Teflon impregnated glass braid jacket (tan), optional colors available on request

PHYSICAL PROPERTIES:

The ceramic tape insulation combines high dielectric strength with excellent flexibility and ease of stripping to achieve a lead wire of superior resistance to high temperatures, abrasion, chemicals and moisture

APPLICATION

For internal wiring of heating equipment, cooking equipment and heat producing appliances in domestic, industrial and cooking applications

NOMINAL THICKNESSES:

TFE Tape: All sizes .015"

Insulation: 24-8 AWG .010", 6-4/0 AWG .015"

Jacket: 24-8 AWG .005", 6-2 AWG .0075", 1-4/0 AWG .010"

| OLYMPIC NO. | CO AWG | NDUCTOR STRANDING | NOM. O.D. | NOM. BEND RADIUS |
|----------------|-----------|----------------------|--------------|---------------------|
| 531 | 22 | 7 x 30 | .090" | .54" |
| 532 | 20 | 10 x 30 | .100" | .60" |
| 533 | 18 | 16 x 30 | .110" | .66" |
| 534 | 16 | 26 x 30 | .120" | .72" |
| 535 | 14 | 41 x 30 | .140" | 1.12" |
| 536 | 12 | 65 x 30 | .160" | 1.28" |
| 537 | 10 | 105 x 30 | .185" | 1.48" |
| 538 | 8 | 133 x 29 | .230" | 2.30" |
| 539 | 6 | 133 x 27 | .285" | 2.85" |
| 540 | 4 | 133 x 25 | .340" | 4.08" |
| 541 | 2 | 133 x 23 | .410" | 4.92" |
| 542 | 1 | 259 x 25 | .470" | 5.64" |
| 543 | 1/0 | 259 x 24 | .515" | 6.18" |
| 544 | 2/0 | 259 x 23 | .570" | 6.84" |
| 545 | 3/0 | 259 x 22 | .625" | 7.50" |
| 546 | 4/0 | 259 x 21 | .690" | 8.28" |
| | | | | 7.50" |