Special-beam Models

Detection with Increased Reliability

A variety of heads incorporating the latest optical technology makes it possible to solve common problems related to detection and to increase reliability.


- Resistant to dust and dirt
- Capable of detecting small workpieces
- Resistant to workpiece vibration
 Use these models to handle
 unstable detection conditions.



Environmentresistive Models

High Resistance to External Conditions with Fiber P1[∠]

We have developed model variations for adapting to a variety of environmental conditions. These models enable detection in high-temperature environments and vacuums.



- High-temperature environmentsEnvironments subject to the
- splattering of chemicals
- Vacuums

Use these models to handle applications in special environments.

Applicationcorresponding Models

Fiber Units for the Food-packaging,
Semiconductor, and FPD Industries P16

These models, which were developed for specific applications, offer top-quality detection performance.

- Label detectionLiquid-level detectionAlignment and mapping of glass substrates
- Wafer mapping Use these models for specific applications.





Liquid-level detection models E32-D36T

Fiber Units with Reflective Sensors

High-resolution mode Standard mode High-speed mode (Super-high-speed mode) * When used in combination with the E3X-DA-S Amplifier Unit (general-purpose).

Ту	pe	Appearance (mm) *3 Sensing distance (mm) *1		mm) *1	(Min. sensing object) (mm) *2	Min. bending radius (mm)	Features	Model number			
	Convergent-reflective	(Free-cut)		3.3					R25	Small level dif- ferences, high power, side-view	E32-L25
		Free-cut		3.3 3.3 (3.3	3)				1120	Small level dif- ferences, top- view	E32-L25A
odels		Free-cut		0 to 4 0 to 4 0 to 4	0 to 4)					Ultracompact, flat-view	E32-L24S
Special-beam models		Free-out		2 to 6 (d	center: 4 center: 4 2 to 6) (c		1	(0.005 dia.)	R10	Heat resistant up to 105°C *4, top-view	E32-L24L
Special	Conve	Free-cut	<u>L</u>	5.4 to 9	(center (center (5.4 to		r: 7.2)			Heat resistant up to 105°C *4, top-view	E32-L25L
		Free-cut		4 to 10 4 to 10 4 to 10)			R25	Heat resistant up to 200°C, flat- view	E32-L86
				0 to 15 0 to 15 0 to 12)				Wide-range sensing, flat- view	E32-L16
	Heat-resistant	150°C*5	Free-cut M6		230 0 (72)	0			R35	Heat resistant up to 150°C	E32-D51
odels		200°C*6	—————————————————————————————————————	15 90	0			(0.005 dia.) -	R10	Heat resistant up to 200°C	E32-D81R-S E32-D81R
sistive mo		350°C*6	M 6	1 160 (21	7)				R25	Heat resistant up to 350°C	E32-D61-S E32-D61
Environment-resistive models		400°C*6	M4 1.25 dia. Min. bending radius of sleeve: 10	100 60 40 (18					1120	Heat resistant up to 400°C, with sleeve	E32-D73-S E32-D73
Enviro	sistant	Free-cut	6 dia.	16 95 165 (3						Fluororesin cov- er, long distance	E32-D12F
	Chemical-resistant	Free-cut	↓ → 7 dia.	70 40 30 (10))			(0.005 dia.)	R40	Fluororesin cov- er, side-view	E32-D14F

- *1. The sensing distances are for white paper.
 *2. The values for the minimum sensing object are representative values that indicate values obtained in standard mode with the sensing distance and sensitivity set to optimum values.
- *3. Free-cut Indicates models that allow free cutting.
- *4. For continuous operation, use the products within a temperature range of -40°C to 90°C.
- $^{\star}5.~$ For continuous operation, use the products within a temperature range of $-40^{\circ}C$ to $130^{\circ}C.$
- *6. The maximum temperature that can be withstood varies with the location

Fiber Units

Туре	Environment-resistive models							
Item	Heat-resistant							
	E32-T5□ E32-D5□	E32-T8□R-S E32-D8□R-S	E32-T84S-S	E32-T6□-S E32-D6□-S	E32-D73-S			
Ambient operating temperature range *1	-40°C to 150°C *4	-40°C to 200°C *3		-60°C to 350°C *3	-40°C to 400°C *3			
Ambient humidity range *1	35% to 85%							
Fiber material Plastic Glass (fluororesin coating)			Glass (SUS spiral coating)					
Degree of protection	IEC standard: IP67							

Туре	Environment-resistive models					
Item		Chemical-resistant	Vacuum-resistant			
	All other models	E32-T51F	E32-T81F-S	All other models	32-T84SV	
Ambient operating temperature range *1	−40°C to 70°C	-40°C to 150°C *4	-40°C to 200°C *3	-25°C to 120°C	–25°C to 200°C	
Ambient humidity range *1	35% to 85%					
Fiber material	Plastic (fluororesin coating)		Glass (fluororesin coating)	Glass (fluororesin coating)	Glass (SUS spiral coating)	
Degree of protection	IEC standard: IP67					

Туре	Application-corresponding models							
Item			Liquid-level detection		Wafer-mapping			
	Label-detection	All other models	E32-A01 E32-A02	E32-D82F				
Ambient operating temperature range *1	-40°C to 70°C		-40°C to 200°C *3	-40°C to 70°C				
Ambient humidity range *1	35% to 85%							
Fiber material	Plastic (polyethylene	coating)	Plastic (fluororesin coating)	(Fluororesin coating)	Plastic (polyethylene coating)			
Degree of protection	IEC standard: IP67	IEC standard: IP50		IEC standard: IP68	IEC standard: IP50			
Other		Repeat accuracy: 1 m	nm max.	Repeat accuracy: 0.5 mm max.				

Туре	Application-corresponding models						
Item	Glass-substra	ate-alignment	Glass-substrate-mapping				
	All other models	E32-L66	E32-A09	E32-A09H	E32-A09H2		
Ambient operating temperature range *1	-40°C to 70°C	0°C to 300°C *3, *5	-40°C to 70°C	-40°C to 150°C *4	-40°C to 300°C *3		
Ambient humidity range *1	33% 10 83%						
Fiber material	Plastic (polyethylene coating)	Glass (SUS spiral coating)	Plastic (polyethylene coating)	Plastic (fluororesin coating)	Glass (SUS spiral coating)		
Degree of protection	IEC standard: IP40						

^{*1.} There must be no icing or condensation within the range specified for the ambient operating temperature.

 $^{^{\}star}2$. For continuous operation, use the products within a temperature range of $-40^{\circ}C$ to $90^{\circ}C$.

^{*3.} The maximum temperature that can be withstood varies with the location. Refer to dimensions diagrams for details.


^{*4.} For continuous operation, use the products within a temperature range of -40°C to 130°C .

^{*5.} These values are based on the assumption that there are no repeated sudden changes in temperature.

Fiber Units with Reflective Sensors

Convergent-reflective Models

Free-cut Indicates models that allow free cutting.




Sensing head (stainless steel)


*1 Material: Stainless steel

Note: The maximum allowable temperatures for sections A and B are 200°C and 110°C, respectively. The section inserted into the Amplifier Unit (indicated by *2), however, must stay within the Amplifier Unit's operating temperature range.


Heat-resistant Models




Note: The maximum allowable temperature is 150°C. The maximum allowable temperature for continuous operation is 130°C.



Note 1. The maximum allowable temperatures for sections A and B are 200°C and 110 $^{\circ}\text{C},$ respectively. The section inserted into the Amplifier Unit (indicated by *2), however, must stay within the Amplifier Unit's operating temperature range.



Note 1. The maximum allowable temperatures for sections A and B are 350°C and 110°C, respectively. The section inserted into the Amplifier Unit (indicated by *2), however, must stay within the Amplifier Unit's operating temperature range.



Note 1. The maximum allowable temperatures for sections A, B, and C are 400°C, 300°C, and 110°C, respectively. The section inserted into the Amplifier Unit (indicated by *2), however, must stay within the Amplifier Unit's operating temperature range.

Chemical-resistant Models

