



### MATERIALS:

Body: Gold Plated Beryllium Copper,  
Male Contact - Gold Plated Brass,  
Female Contact - Gold Plated Beryllium Copper

Dielectric: Teflon

Finish: Body and Contacts - Gold plated

Marking: "Pomona 4298"

### RATINGS:

Voltage: Shield/Earth: 30VAC/60VDC Max.

Inner Conductor/Shield: 335VRMS Max.

Operating Temperature:  $-65^{\circ}\text{C}$  ( $-85^{\circ}\text{F}$ ) to  $+165^{\circ}\text{C}$  ( $+329^{\circ}\text{F}$ )

Nominal Impedance: 50 Ohms

Frequency Range: 0-12.4 GHz.

### ORDERING INFORMATION: Model 4298

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA