

**JUNIOR  
FOOTSWITCH**



**Junior Footswitch**

**Environmental Ratings:**

EN 60529 Degree of Protection IP20

**Key Benefits**

The low, sleek styling of this foot switch reduces operator fatigue. Each foot switch is provided with a reversible strain relief clamp that accommodates a wide range of cable sizes. The aluminum casting is painted black with nonskid base pads.



Size: 5-1/2" x 3-1/4" x 1-1/4"

Weight: 1 lb.

**SPECIFICATIONS**




(Special variations are available to the O.E.M. on special order on the models listed below)

**⚠ WARNING**

	CATALOG NUMBER	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS
	121-S	Momentary	SPDT	C	20 A 125-250 VAC 1 H.P. 125-250 VAC
	124-S	Momentary	DPDT	C	15 A 125-250 VAC 1/2 H.P. 125-250 VAC

# Junior Model

NOTE: ALL DIMENSIONS ARE FOR REFERENCE ONLY.



**EN 60529 Degree of Protection IP20 (IP68 Upon Request)**

**Splash Resistant (Available)  
LOW PROFILE ERGONOMIC DESIGN**

**Materials of Construction:**


- Constructed of cast aluminum cover and base
- Provided with a reversible strain relief clamp that accommodates a wide range of cable sizes
- Painted black

**Features & Benefits:**

- The low, sleek styling of this model reduces operator fatigue
- Nonskid base pads

**Options:**

- 24" wide version available on special order
- AirVal Models available on special orders



Size (HxWxD):	1.25 x 3.25 x 5.50 In.
Weight:	1.00 lbs.

<b>⚠ WARNING SEE PRODUCT WARNING ON PAGE 8</b>						
SPECIFICATIONS (Special variations are available to the O.E.M. on special order on the models listed below)						
AGENCY APPROVALS	EN 60529 Degree of Protection	CATALOG NUMBER	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS
cULus CE	IP20	121-S	Momentary	SPDT	C	20 A 125-250 VAC 1 H.P. 125-250 VAC
cULus CE	IP20	124-S	Momentary	DPDT	C	15 A 125-250 VAC 1/2 H.P. 125-250 VAC