


KRPA-14DY-24 Product Details



KRPA-14DY-24

TE Internal Number: 9-1393104-3



Industrial Relays (General Purpose)

 [Always EU RoHS compliant but not ELV Compliant](#)
([Statement of Compliance](#))

Product Highlights:

- Relay Type = General Purpose
- Relay Style = General
- KRPA Series
- Contact Arrangement = 3 Form C, 3PDT, 3 C/O
- Contact Current Rating = 5 A

[View all Features](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Schematic](#)
- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = 11 Pin Octal-Style Plug

Electrical Characteristics:

- [Contact Current Rating \(A\)](#) = 5
- [Coil Resistance \(Ω\)](#) = 472
- [Actuating System](#) = DC
- [Coil Power, Nominal \(W\)](#) = 1.20
- [Input Voltage \(VDC\)](#) = 24

Body Related Features:

- [Series](#) = KRPA
- Polarized = No
- Enclosure Color = Clear
- Type = Ice Cube

Contact Related Features:

- Relay Type = General Purpose
- [Mounting Options](#) = Socket
- [Enclosure Type](#) = Enclosed
- FCC Part 68 Isolation = No
- [Contact Base Material](#) = Silver
- Approx. Dimensions (L x W x H) (mm [in]) = 48.80 x 37.30 x 34.90 [1.922 x 1.469 x 1.375]
- Pin Configuration = Industry Standard
- Wiring Diagram = K-14

Configuration Related Features:

- Relay Style = General
- [Contact Arrangement](#) = 3 Form C, 3PDT, 3 C/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS not ELV compliant
- Approved Standards = UL Recognized, CSA Certified

Other:

- Brand = Potter & Brumfield