Advantages of a Full Featured 700 Series Relay

Since the launch of the 700 series relays in 2000, this product line has continuously evolved both functionally and visually. The 700 series product line has the perfect mix of historical Magnecraft relay quality combined with a dynamic arsenal of options. When mated with the Magnecraft sockets and accessories, these RoHs compliant relays provide a complete modular system that will meet all your plugin relay requirements in a package that is both visually appealing and functionally outstanding.



Removable Lock-Down Door

When Activated, Locks Push Button and Contacts in the Powered Position.

Color-Coded Push Button


Allows Manual Operation of Relay. AC Coils Red or DC Coils Blue.


Finger Grip Cover

Easy Removal of -Relay from Socket.

Gold Flashed Contacts

Prevents Premature Oxidation and Increases Shelf-life.





- Plug-In switching capabilities from 10 mA to 20 Amps.
- Several Feature Code and Operation combinations available for all budgets.
- Ejector clips, ribbed relay housings and space-saving sockets allow for easy removal from crowded DIN rails.
- Color and appearance designed for high visibility in all environments.
- Wiring diagrams include NEMA and IEC standards.
- Engineering availability allows for customized relay solutions.



Contact Viewing Window - Shows Position of Contacts.

Isolated Input and Output Terminals

Separates Control Circuits from Load Circuits.

Slim Design


Minimizes Space on DIN Rail.



Module Compatible
Allows for Optional
Protection or LED Modules
to be Used With Sockets.



2-Way Side or DIN
Rail Mounting System
Retrofits Existing Panel
Mounting and 35mm DIN Rail.



Advantages of a Plain Cover 700 Series Relay

The Plain Cover Super Series relays support budget minded applications with premium performance. Maintaining the same ratings and internal components as the Full Feature Series; the Plain Cover Series perform as well as premium relays while maintaining low costs by offering several option configurations.

Finger Grip Cover

Easy Removal of Relay from Socket.

Contact Viewing Window Shows Position of Contacts.



Gold Flashed Contacts

Prevents Premature Oxidation and Increases Shelf-life.

- Offers a "one stop solution" for your power management system.
- Several Contact configurations and materials to meet your individual needs.
- Plug-In switching capabilities from 10 mA to 20 Amps.
- Several Feature Code and Operation combinations available for all budgets.
- Ejector clips, ribbed relay housings and space-saving sockets allow for easy removal from crowded DIN rails.
- Color and appearance designed for high visibility in all environments.
- Wiring diagrams include NEMA and IEC standards.
- Engineering availability allows for customized relay solutions.

Isolated Input and Output Terminals

Separates Control Circuits from Load Circuits.

Slim Design

Minimizes Space on DIN Rail.




Module Compatible

Allows for Optional
Protection or LED Modules
to be Used With Sockets.



2-Way Side or DIN Rail Mounting System

Retrofits Existing Panel Mounting and 35mm DIN Rail.




RoHs 70.782D14-1


Finger-Safe
Protects Operators from Live Circuits.

Safely Secures Relay to Socket.

784 Ice Cube Relays/4PDT, 15 Amp Rating (DC & AC)



General Specifications (UL 508) **784XDX Contact Characteristics** Units Number and type of Contacts 4PDT Silver Alloy Contact materials Thermal (Carrying) Current 15 Maximum Switching Voltage Switching Current @ Voltage 300 15A @ 120V 50/60Hz 12A @ 277V 50/60Hz Resistive Resistive 12A @ 28V Resistive 1/2 @ 120VAC HP HP 3/4 @ 250 VAC B300 Pilot Duty 100 @ 5VDC (.5W) Minimum Switching Requirement mΑ **Coil Characteristics** 6....240 6....125 Voltage Range ٧ Operating Range % of Nominal 85% to 110% 80% to 110% Average consumption ~ VA 1.5 W == 1.5 Drop-out voltage threshold 15% 10% **Performance Characteristics** Operations @ Rated Current Electrical Life (UL508) (Resistive) 200,000 Mechanical Life 10,000,000 Unpowered 20 Operating time (response time) ms 2500 Dielectric strength Between coil and contact V(rms) 2500 Between poles V(rms) 2500 Between contacts V(rms) **Environment** UL, CSA, CE Product certifications Standard version Ambient air temperature -40...+85 Storage around the device Operation °C -40...+55 3, 10 - 55 Hz Vibration resistance Operational g-n Shock resistance g-n 10 Degree of protection IP 40 Weight 80



grams





Standard Part Numbers

BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED

Nominal Voltage	Coil Resistance	4PDT Part Number	4PDT Part Number			
		(Full Feature) 15 Amp	(Plain Cover) 15 Amp			
AC Operated		·	•			
6 VAC 50/60 Hz	5.4 Ohms	784XDXM4L-6A	784XDXC-6A			
12 VAC 50/60 Hz	21.2 Ohms	784XDXM4L-12A	784XDXC-12A			
24 VAC 50/60 Hz	84.5 Ohms	784XDXM4L-24A	784XDXC-24A			
120 VAC 50/60 Hz	2220 Ohms	784XDXM4L-120A	784XDXC-120A			
220-230 VAC 50/60 Hz	7360 Ohms	784XDXM4L-220/230A	784XDXC-220/230A			
240 VAC 50/60 Hz	9120 Ohms	784XDXM4L-240A	784XDXC-240A			
DC Operated						
6 VDC	24 Ohms	784XDXM4L-6D	784XDXC-6D			
12 VDC	96 Ohms	784XDXM4L-12D	784XDXC-12D			
24 VDC	388 Ohms	784XDXM4L-24D	784XDXC-24D			
48 VDC	1550 Ohms	784XDXM4L-48D	784XDXC-48D			
110-125 VDC	7340 Ohms	784XDXM4L-110/125D	784XDXC-110/125D			

Custom Relay Part Number Builder

COSIOIII KEK	ay rai i Nolliber bollaei				
784	XDX		T	M4L-	240A
Series	Contact Configuration	Cover Options	Terminal Style	Feature Options	Coil Voltage
784	XDX = 4PDT	Full Feature = No Code	Plug In = No Code	Side Push Button = M	VAC = 6 - 240A
		Plain Cover = C	PC terminal = T	Locking Push Button = M4	VDC = 6 - 125D
				Bi-Polar IFD = I	

