Solving Your Relay Requirements Since 1922



Amperite Co. 567 52nd Street P.O. Box 329 West New York, NJ 07093 (800) 752-2329

www.Amperite.com

SST1-Series

Solid State Time Delay Relay



Adjustment knob for 0.1 to 8 minutes
Operates from 19 to 288 volts AC or DC
Totally solid state
Encapsulated circuitry
Q.C. terminals for easy connections
Good repeat accuracy

SPECIFICATIONS				
Time Delay				
Туре	Adjustable knob with dial			
Range	0.1 to 8 minutes (Reference Dial)			
Repeat Accuracy	± 2%			
Recycle time	100 milliseconds maximum			
Input				
Operating Voltage	19 to 288 volts AC or DC			
Line frequency	50 to 60 Hertz			
Minimum holding current	40 Milliamperes			
Voltage Drop	2.5 Volts typical at 1 ampere			
Output				
Туре	Solid State			
Form	Normally open			
Max. Load Current	1 Ampere steady state			
IVIAX. LUAU GUITEIII	10 amperes inrush at 55 ℃			

Solving Your Relay Requirements Since 1922



Amperite Co. 567 52nd Street P.O. Box 329 West New York, NJ 07093 (800) 752-2329

www.Amperite.com


			• • • • • • • • • • • • • • • • • • •	
Protection				
Dielectric Breakdown	Greater than 1500 Volts RMS			
Insulation Resistance	100 Megohms Minimum			
Transient Protected				
Mechanical				
Mounting	Surface mount with one #8 or #10 Screw			
Package	Molded housing with totally encapsulated circuitry			
Termination	1 / 4 inch quick connect terminals			
Environmental				
Operating Temperature	-20℃ to +70℃			
Storage Temperature	-30℃ to +85℃			
Humidity	95% Relative			
THE NUMBER LISTED TH		PLEASE CONT	BELOW. IF YOU DO NOT SEE TACT US. WE CAN PROVIDE .E TODAY.	
Part Number	CONTACT ARRANGEMENT	TYPE	TERMINATION	
SST1-1A 288AD 01	1A = 1 Form A	Solid State	01 = Plug-in	


Solving Your Relay Requirements Since 1922



Amperite Co. 567 52nd Street P.O. Box 329 West New York, NJ 07093 (800) 752-2329


www.Amperite.com





(Bottom View) Wiring Diagram

Outline Dimensions SST1 1 Pole PCB Mount



Wiring Diagram