

Vishay Dale

Metal Film Resistors, Military, MIL-R-10509 Qualified, Precision, Type RN and MIL-PRF-22684 Qualified, Type RL



FEATURES

- Very low noise (- 40 dB)
- Very low voltage coefficient (5 ppm/V)
- · Controlled temperature coefficient
- · Flame retardant epoxy coating
- Commercial alternatives to military styles are available with higher power ratings. See CMF Industrial data sheet: (www.vishay.com/doc?31018)

STANE	STANDARD ELECTRICAL SPECIFICATIONS										
GLOBAL MODEL	MIL STYLE	MIL SPEC. SHEET	_	POWER RATING P _{125°C} W	MAX. WORKING VOLTAGE ⁽¹⁾ V	RESISTANCE RANGE Ω MIL-R-10509 ± 100 ppm/°C (D)	RANGE Ω MIL-R-10509	RANGE Ω MIL-R-10509	RESISTANCE RANGE Ω MIL-PRF-22684	TOL. ⁽³⁾ ± %	DIELECTRIC STRENGTH V _{AC}
CMF50	RN50	08	-	0.05	200	-	10 to 100K	10 to 100K	-	0.1, 0.25, 0.5, 1	450
CMF55	RN55	07	0.125	0.10	200	10 to 301K	49.9 to 100K	49.9 to 100K	-	0.1, 0.25, 0.5, 1	450
CMF60	RN60	01	0.25	0.125	300	10 to 1M	49.9 to 499K	49.9 to 499K	-	0.1, 0.25, 0.5, 1	500
CMF65	RN65	02	0.50	0.25	350	10 to 2M	49.9 to 1M	49.9 to 1M	-	0.1, 0.25, 0.5, 1	900
CMF70	RN70	03	0.75 (2)	0.50	500	10 to 2.49M	24.9 to 1M	24.9 to 1M	-	0.1, 0.25, 0.5, 1	900
CMF07	RL07	01	0.25	=	250	-	-	-	51 to 150K	2, 5	450
CMF20	RL20	02	0.50	-	350	-	-	-	4.3 to 470K	2, 5	700

Notes

 $^{^{(3)}}$ Tolerances of \pm 0.1 %, \pm 0.25 % and \pm 0.5 % are not applicable to characteristic D.


TECHNICAL SPECIFICATIONS					
PARAMETER	UNIT	CONDITION			
Voltage Coefficient	ppm/V	5 when measured between 10 % and full rated voltage			
Insulation Resistance	W	$\geq 10^{10}$ min. dry; $\geq 10^8$ min. after moisture test			
Operating Temperature Range	°C	- 65/+ 175 (see derating curves for military range)			
Terminal Strength	lb	5 pound pull test for RL07/RL20; 2 pound pull test for all others			
Solderability		Continuous satisfactory coverage when tested in accordance with MIL-R-10509 and MIL-PRF-22684			

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.

⁽²⁾ Formerly rated at 1 W and is the direct replacement for RN70 of MIL-R-10509 rev. D.



Shay.com Vishay Dale



Note

For additional information on packaging, refer to the Through Hole Resistor Packaging document (<u>www.vishay.com/doc?31544</u>).

MATERIAL SPECIFICATIONS				
Element	Nickel-chrome alloy			
Coating	Flame retardant epoxy, formulated for superior moisture protection			
Core	Fire-cleaned high purity ceramic			
Termination	Standard lead material is solder-coated copper. Solderable and weldable.			

APPLICABLE MIL-SPECS

MIL-R-10509 and MIL-PRF-22684: The CMF models meet or exceed the electrical, environmental and dimensional requirements of MIL-R-10509 and MIL-PRF-22684.

Noise: Vishay Dale metal film resistors have exceptionally low noise level. Average for standard resistance range is 0.10 μ V per V over a decade of frequency, with low and intermediate resistance values typically below 0.05 μ V per V.


CAGE	CODE:	91637

ENVIRONMENTAL SPECIFICATIONS					
General	Environmental performance is shown in the Environmental Performance table. Test methods are those specified in MIL-R-10509 and MIL-PRF-22684.				
Shelf Life	Resistance shifts due to storage at room temperature are negligible.				


www.vishay.com

Vishay Dale

Vishay Dale CMF resistors have an operating temperature range of - 65 °C to + 175 °C. They must be derated according to the following curves:



DIMENSIONS in inches (millimeters)



VISHAY DALE MODEL	А	В	C (MAX.)	D
CMF50	0.150 ± 0.020	0.065 ± 0.015	0.244	0.016 ± 0.002
	(3.81 ± 0.51)	(1.65 ± 0.38)	(6.20)	(0.41 ± 0.05)
CMF55	0.240 ± 0.020	0.090 ± 0.008	0.278	0.025 ± 0.002
	(6.10 ± 0.51)	(2.29 ± 0.20)	(7.06) ⁽¹⁾	(0.64 ± 0.05)
CMF60	0.344 ± 0.031	0.145 ± 0.015	0.425	0.025 ± 0.002
	(8.74 ± 0.79)	(3.68 ± 0.38)	(10.80)	(0.64 ± 0.05)
CMF65	0.562 ± 0.031	0.180 ± 0.015	0.687	0.025 ± 0.002
	(14.27 ± 0.79)	(4.57 ± 0.38)	(17.45)	(0.64 ± 0.05)
CMF70	0.562 ± 0.031	0.180 ± 0.015	0.687	0.032 ± 0.002
	(14.27 ± 0.79)	(4.57 ± 0.38)	(17.45)	(0.81 ± 0.05)
CMF07	0.240 ± 0.020	0.090 ± 0.008	0.278	0.025 ± 0.002
	(6.10 ± 0.51)	(2.29 ± 0.20)	(7.06)	(0.64 ± 0.05)
CMF20	0.375± 0.040	0.145 ± 0.015	0.425	0.032 ± 0.002
	(9.53 ± 1.02)	(3.68 ± 0.38)	(10.80)	(0.81 ± 0.05)

Notes

⁽²⁾ Lead length for product in bulk pack. For product supplied in Tape and Reel, the actual lead length would be based on the body size, tape spacing and lead trim.

MILITARY POWER RATING						
	MILITARY QUALIFIED					
WATTAGE	MIL-	R-10509	MIL-PRF-22684			
WALLAGE	AT + 70 °C (D)	AT + 125 °C (C and E)	AT + 70 °C			
0.05	-	RN50	-			
0.10	-	RN55	-			
0.125	RN55	RN60	-			
0.25	RN60	RN65	RL07			
0.50	RN65	RN70	RL20			
0.75 (3)	RN70	-	-			


Notes

 $^{^{(1)}}$ 0.290" (7.37) for \pm 0.25 % and \pm 0.1 % resistance tolerances.

[•] Commercial equivalents of military styles are available with higher power ratings. Consult factory.

⁽³⁾ Formerly rated at 1 W and is the direct replacement for RN70 of MIL-R-10509 rev. D.

Vishay Dale



MARKING (per MIL-PRF-10509)

Characteristics: D = 100 ppm, C = 50 ppm, E = 25 ppm Tolerance: F = 1 %, D = 0.5 %, C = 0.25 %, B = 0.1 % Value = Three significant figures and multiplier

J = JAN (Joint Army - Navy) brand

RN50: (3 lines) RN55, RN60, RN65, RN70 (4 lines)

J50D JAN, type, characteristic DALE Company logo

John Jan, type, characteristic

1211 Value

O137J 4 digit date code and JAN brand
RN55D Type and characteristic

F137 Tolerance and 3 digit date code 1211F Value and Tolerance

Note

• RL series are color banded per MIL-PRF-22684.

PERFROMANCE					
DECLUDEMENT		MIL DDF 00004			
REQUIREMENT	CHARACTERISTIC D	CHARACTERISTIC C	CHARACTERISTIC E	MIL-PRF-22684	
MIL Temperature Coefficient	+ 200 ppm/°C - 500 ppm/°C	± 50 ppm/°C	± 25 ppm/°C	± 200 ppm/°C	
Applicable Vishay Dale Temperature Coefficient	± 100 ppm/°C	± 50 ppm/°C	± 25 ppm/°C	± 200 ppm/°C	
TEST	MIL _{max} .	MIL _{max} .	MIL _{max} .	MIL _{max} .	
Thermal Shock	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 1.00 % ΔR	
Short Time Overload	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 0.50 % ΔR	
Low Temperature Operation	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 0.50 % ΔR	
Moisture Resistance	± 1.50 % ΔR	± 0.50 % ΔR	± 0.50 % ΔR	± 1.50 % ΔR	
Shock	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 0.50 % ΔR	
Vibration	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 0.50 % ΔR	
Load Life	± 1.00 % ΔR	± 0.50 % ΔR	± 0.50 % ΔR	± 2.00 % ΔR	
Dielectric Withstanding Voltage	± 0.50 % ΔR	± 0.25 % ΔR	± 0.25 % ΔR	± 0.50 % ΔR	
Effect of Solder	± 0.50 % ΔR	± 0.10 % ΔR	± 0.10 % ΔR	± 0.50 % ΔR	



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000