


Thick Film, Dual-in-Line Resistor Networks



FEATURES

- 14, 16 or 20 terminal package
- Isolated, bussed or TTL-terminator circuits
- Molded case construction
- Thick film resistive elements
- Reflow solderable
- Compatible with automatic surface mounting equipment
- Reduces total assembly costs
- For wave flow soldering contact factory
- Lead (Pb)-free version is RoHS compliant



RoHS*
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	ELEMENT $P_{70^\circ C}$ W	PACKAGE POWER RATING $P_{70^\circ C}$ W			CIRCUIT	LIMITING ELEMENT VOLTAGE MAX. V \equiv	TEMPERATURE COEFFICIENT ¹⁾ ppm/ $^\circ C$	TOL. %	RESISTANCE RANGE Ω	E-SERIES
		14	16	20						
SOMC	0.08 0.16 0.08	1.05 1.125 1.05	1.20 1.28 1.20	1.52 1.60 1.52	01 03 05	50	100	1, 2, 5 1, 2, 5 1, 2, 5	10R - 1M	24

- ¹⁾ Temperature Range: - 55 $^\circ C$ to + 125 $^\circ C$
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material
 - Jumper: Zero-Ohm-Resistor on request (100 m Ω)
 - Packaging: according to EIA; see appropriate catalog or web page

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	01 CIRCUIT	03 CIRCUIT	05 CIRCUIT
Rated Dissipation at 70 $^\circ C$ per Element	W	0.08	0.16	0.08
Limiting Element Voltage ²⁾	V \equiv	50		
Voltage Coefficient	ppm/V	< 50		
Insulation Voltage (1min)	V _{dc/ac} peak	200		
Category Temperature Range	$^\circ C$	- 55/+ 150		
Insulation Resistance	Ω	> 10 ¹⁰		
TC Tracking (- 55 $^\circ C$ to + 125 $^\circ C$)	ppm/ $^\circ C$	50		

²⁾Rated voltage: $\sqrt{P \times R}$

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: SOMC16011K00GD (preferred part numbering format)

S O M C 1 6 0 1 1 K 0 0 G D C

GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING	SPECIAL
SOMC	14 16 20	01 = Bussed 03 = Isolated 00 = Special	R = Decimal K = Thousand M = Million 10R0 = 10 Ω 680K = 680 k Ω 1M00 = 1.0 M Ω	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ S = Special	EJ = Lead Free, Tube EA = Lead Free, Tape & Reel DC = Tin/Lead, Tube RZ = Tin/Lead, Tape & Reel	Blank = Standard (Dash Number) (up to 3 digits) From 1-999 as applicable

Historical Part Number example: SOMC1601102G (will continue to be accepted)

SOMC 16 01 102 G D02

New Global Part Numbering: SOMC2005500BGRZ (preferred part numbering format)

S O M C 2 0 0 5 5 0 0 B G R Z


GLOBAL MODEL	PIN COUNT	SCHEMATIC	RESISTANCE VALUE	TOLERANCE CODE	PACKAGING	SPECIAL
SOMC	14 16 20	05 = Dual Terminator	3 digit Impedence code, followed by Alpha modifier (see Impedence table)	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	EJ = Lead Free, Tube EA = Lead Free, Tape & Reel DC = Tin/Lead, Tube RZ = Tin/Lead, Tape & Reel	Blank = Standard (Dash Number) (up to 3 digits) From 1-999 as applicable

Historical Part Number example: SOMC2005820131G (will continue to be accepted)

SOMC 20 05 810 131 G R61

* Pb containing terminations are not RoHS compliant, exemptions may apply

DIMENSIONS




SOLDER PAD DIMENSIONS in inches [millimeters]						
	a	b	c	l	p	w
WAVE	0.64	1.91	5.34	9.53	1.27	9.15
REFLOW	0.64	1.91	5.34	9.53	1.27	9.15

The dimension shown are for a 16 pin part. For parts with different pin numbers use the same pitch and add or subtract pads as required.

NOTE: Maximum solder reflow temperature + 255 °C

DIMENSIONS [in millimeters]											
PIN NO#	L	W	B	E	F	G	H	K	R	S	T
14	9.91	7.62	7.62	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
16	11.18	7.62	8.89	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
20	13.72	7.62	11.43	6.20	5.59	2.16	2.03	0.914	0.457	1.27	1.14
Tol	±0.254	±0.381	±0.254	±0.381	±0.127	±0.127	±0.127				±0.254

CIRCUIT SCHEMATICS



IMPEDANCE CODES					
CODE	R ₁ (Ω)	R ₂ (Ω)	CODE	R ₁ (Ω)	R ₂ (Ω)
500B	82	130	141A	270	270
750B	120	200	181A	330	390
800C	130	210	191A	330	470
990A	160	260	221B	330	680
101C	180	240	281B	560	560
111C	180	270	381B	560	1.2K
121B	180	390	501C	620	2.7K
121C	220	270	102A	1.5K	3.3K
131A	220	330	202B	3K	6.2K

PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST RESULTS
Power Conditioning	MIL STD-202	± 0.5%
Load Life at 70°C	MIL STD-202	± 0.5%
Short Time Overload	MIL STD-202	± 0.25%
Thermal Shock	MIL STD-202	± 0.5%
Moisure Resistance	MIL STD-202	± 0.5%
Resistance to Soldering Heat	MIL STD-202	± 0.25%
Low Temperature Operation	MIL STD-202	± 0.25%
Vibration	MIL STD-202	± 0.25%
Shock	MIL STD-202	± 0.25%
Terminal Strength	MIL STD-202	± 0.25%



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.