

www.vishay.com

Vishay Spectrol

COMPLIANT

⁷/₈" (22.2 mm) Multi Turn Wirewound 533: 3 Turns/534: 10 Turns/535: 5 Turns



FEATURES

- Bushing and servo mount designs available
- Special resistance tolerances to 1 %
- · Rear shaft extensions and support bearing
- Metric shaft available
- Dual gang configuration and concentric shafts
- High torque, center tap, slipping clutch on request
- Special markings and front shaft extensions
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

Note

 The color of this product may either be black (US market) or blue (other regions)

| QUICK REFEREN | CE DATA |
|------------------|---|
| Sensor type | ROTATIONAL, multi turn wirewound |
| Output type | Output by turrets |
| Market appliance | Industrial |
| Dimensions | ⁷ / ₈ " (22.2 mm) |

| PARAMETER | MODEL 533 | MODEL 534 | MODEL 535 | | | |
|--------------------------------------|--|--|---------------------|--|--|--|
| Resistance range - standard values | 50Ω to $20 k\Omega$ | 100 Ω to 100 kΩ | 50 Ω to 50 kΩ | | | |
| Capability range | 5 Ω to 60 k Ω | 10 Ω to 200 kΩ | 5 Ω to 100 kΩ | | | |
| Standard tolerance | ± 5 % | ± 5 % | ± 5 % | | | |
| Linearity (independent) | ± 0.25 % | ± 0.25 % | ± 0.25 % | | | |
| Noise | 100 Ω ENR | 100 Ω ENR | 100 Ω ENR | | | |
| Rotation (electrical and mechanical) | 1080° + 10° - 0° | 3600° + 10° - 0° | 1800° + 10° - 0° | | | |
| Power rating (at 70 °C) | 1.0 W | 2.0 w | 1.5 W | | | |
| Insulation resistance | | 1000 M Ω minimum 500 V _{DC} | | | | |
| Dielectric strength | | 1000 V _{RMS} minimum 60 Hz | | | | |
| Absolute minimum resistance | Not to exceed I | inearity x total resistance or 1 Ω , wh | ichever is greater | | | |
| Temperature coefficient | 1 | 20 ppm/°C (standard values, wire on | ly) | | | |
| End voltage | 0. | 25 % of total applied voltage, maxim | num | | | |
| Phasing | CCW end points - section 2 phased to section 1 within ± 2° | | | | | |
| Taps | | Center tap only | | | | |

| MARKING | |
|---------------------|---|
| Unit identification | Manufacturer's name and model number, resistance value and tolerance, linearity specification date code and terminal identification |


| RESIST | RESISTANCE VALUES | | | | | | |
|--|--|--|--|--|--|--|--|
| 533 (Ω) 50, 100, 200, 500, 1K, 2K, 5K, 10K, 20I | | | | | | | |
| 534 (Ω) | 100, 200, 500, 1K, 2K, 5K, 10K, 20K, 50K, 100K | | | | | | |
| 535 (Ω) | 50, 100, 200, 500, 1K, 2K, 5K, 10K, 20K, 50K | | | | | | |

| | The Models 533 (3 turns), 534 (10 turns) and 535 (5 turns) can be ordered by stating | | | | | | | | | | | |
|--|--|-----------------------------------|----------------------|-----------------------------|-----------------------------|--------------------------|----------------|---------------------|----------------|--|--|--|
| | 534 | В | 2 | 10K | 20K | 5 % | С | BO10 | e4 | | | |
| | MODEL | MOUNTING | NUMBER OF SECTION | OHMIC VALUE SECTION Nº 1 | OHMIC VALUE SECTION Nº 2 | TOLERANCE ON OHMIC VALUE | LINEARITY | PACKAGING | LEAD FINISH | | | |
| | | B: Bushing S: Servo | | | | | ± 0.25 % (STD) | Box of 10 pieces | | | | |

| SAP PART | SAP PART NUMBERING GUIDELINES | | | | | | | | | | | | | |
|----------|-----------------------------------|----------------------|-----------------------------|-----------------------------|--------------------------------------|---|---------------------|--|--|--|--|--|--|--|
| 534 | В | 2 | 103 | 203 | J | С | B10 | | | | | | | |
| MODEL | STYLE | NUMBER OF SECTION | OHMIC VALUE SECTION Nº 1 | OHMIC VALUE SECTION Nº 2 | TOLERANCE ON OHMIC VALUE | LINEARITY | PACKAGING | | | | | | | |
| | B: Bushing S: Servo | | 103 = 10K | 203 = 20K | J : ± 5 % F : ± 1 % | C: ± 0.25 % CUSTOM: L: ± 0.20 % D: ± 0.1 % | Box of 10 pieces | | | | | | | |

Revision: 27-Jun-12 1 Document Number: 57065






Mounting hardware, washer and panel nut, nickel plated

| MECHANICAL SPECIFICATIONS | | | | | | |
|---|--|---|--|--|--|--|
| PARAMETER | | | | | | |
| Bearing type | Bushing: Sleeve bearing | Servo: Ball bearing | | | | |
| Torque (maximums): starting Section 1 Section 2 | 534 0.5 oz in (36 g - cm) 0.9 oz in (65 g - cm) | 533/535 0.7 oz in (50 g - cm) 1.1 oz in (79 g - cm) | | | | |
| Torque (maximums): running Section 1 Section 2 | 534 0.4 oz in (28.80 g - cm) 0.7 oz in (50.40 g - cm) | 533/535 0.6 oz in (43.20 g - cm) 0.9 oz in (64.8 g - cm) | | | | |
| Weight (maximums) Section1 Section 2 | 0.75 oz. 1.25 oz. | (21.26 g) (35.44 g) | | | | |
| Stop strength | 75 oz in (stat | 75 oz in (static) (5.4 kg - cm) | | | | |
| Ganging | 2 sections | maximum | | | | |

POWER RATING CHART



| ENVIRONMENTAL SPECI | FICATIONS |
|--|--|
| Vibration | 15 g thru 2000 Hz |
| Shock | 50 g |
| Rotational life (shaft revolution) 533 534 534 (servo) 535 | 300 000 1 000 000 > 1 000 000 500 000 |
| Load life | 900 h |
| Temperature range | - 55 °C to + 125 °C |



www.vishay.com

Vishay Spectrol

| RESIS | RESISTANCE ELEMENT DATA | | | | | | | | | | | | | |
|----------------------|-------------------------|----------------|-------|---------------|-------|---|--------|--------|---------------------------------------|-------|-------|-------|-------|-------|
| RESISTANCE VALUE (Ω) | | RESOLUTION (%) | | OHMS PER TURN | | MAXIMUM CURRENT AT 70 °C AMBIENT (mA) | | | MAXIMUM VOLTAGE ACROSS COIL (V) | | | | | |
| 533 | 534 | 535 | 533 | 534 | 535 | 533 | 534 | 535 | 533 | 534 | 535 | 533 | 534 | 535 |
| 50 | - | 50 | 0.149 | - | 0.120 | 0.0746 | - | 0.0603 | 141.0 | - | 173.0 | 7.07 | - | 8.66 |
| 100 | 100 | 100 | 0.111 | 0.060 | 0.075 | 0.1114 | 0.0603 | 0.0746 | 100.0 | 141.0 | 122.0 | 10.0 | 14.1 | 12.2 |
| 200 | 200 | 200 | 0.097 | 0.037 | 0.061 | 0.1954 | 0.0746 | 0.1220 | 70.7 | 100.0 | 86.6 | 14.1 | 20.0 | 17.3 |
| 500 | 500 | 500 | 0.069 | 0.031 | 0.049 | 0.3424 | 0.1520 | 0.2459 | 44.7 | 63.2 | 54.7 | 22.4 | 31.6 | 27.4 |
| 1K | 1K | 1K | 0.063 | 0.025 | 0.041 | 0.6331 | 0.2459 | 0.4113 | 31.6 | 44.7 | 38.7 | 31.6 | 44.7 | 38.7 |
| 2K | 2K | 2K | 0.041 | 0.021 | 0.031 | 0.8206 | 0.4113 | 0.6331 | 22.4 | 31.6 | 27.4 | 44.7 | 63.2 | 54.8 |
| 5K | 5K | 5K | 0.044 | 0.016 | 0.034 | 2.2330 | 0.8206 | 1.7230 | 14.1 | 20.0 | 17.3 | 70.7 | 100.0 | 86.6 |
| 10K | 10K | 10K | 0.034 | 0.017 | 0.030 | 3.4510 | 1.7230 | 3.0160 | 10.0 | 14.1 | 12.2 | 100.0 | 141.0 | 122.0 |
| 20K | 20K | 20K | 0.031 | 0.015 | 0.020 | 6.1790 | 3.0160 | 3.9910 | 7.07 | 10.0 | 8.66 | 141.0 | 200.0 | 173.0 |
| - | 50K | 50K | - | 0.009 | 0.015 | - | 4.6690 | 7.4560 | - | 6.32 | 5.47 | - | 316.0 | 274.0 |
| - | 100K | - | - | 0.007 | - | - | 7.4560 | - | - | 4.47 | - | - | 447.0 | - |
| - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |
| - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000