




Schneider Electric Relays

1300 South Wolf Road
Des Plaines, IL 60018

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # 783XCXC-12D, 783 ICE CUBE RELAYS / 3PDT, 15 AMP RATING



[SPECIFICATIONS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#)

Specifications	
Check Inventory	Check Distributor Inventory
Status	Standard
Contact Configuration	3PDT
Thermal (Carrying) Current	15 A
Terminal Style	Plug-in
Control	DC
Coil Resistance (Ohms)	80 Ohm
Load Type	Standard
Contact Materials	Silver Alloy
Cover Options	Plain Cover
Switching Current at Voltage (AC, Resistive)	CSA: 15 A at 150 VAC 50/60 Hz (30A max. total) UL: 15 A at 277 VAC 50/60 Hz

Switching Current at Voltage (DC, Resistive)	IEC: 15 A at 28 VDC UL: 15A at 28 VDC
---	--

Minimum Switching Requirement	10 mA at 17 VDC
--------------------------------------	-----------------

Features	Mechanical flag indicator
-----------------	---------------------------

Coil Characteristics

Operating Range - % of Nominal (AC)	85 to 110 %
--	-------------

Operating Range - % of Nominal (DC)	80 to 110 %
--	-------------

Average Consumption (AC / VA)	1.70 VA
--------------------------------------	---------

Average Consumption (DC / W)	1.50 W
-------------------------------------	--------

Drop-out Voltage Threshold (AC)	15 %
--	------

Drop-out Voltage Threshold (DC)	10 %
--	------

Performance Characteristics

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
---	--------

Mechanical Life, Unpowered	10000000
-----------------------------------	----------

Operating Time (Response Time)	20 ms
---------------------------------------	-------

Dielectric Strength - Between Coil and Contact (AC)	2000 V(rms)
--	-------------

Dielectric Strength - Between Poles (AC)	2000 V(rms)
---	-------------

Environment

Product Certifications	CSA (44087) UL (E164862) CE RoHs
-------------------------------	---

Vibration Resistance - Operational	±1 mm (10-35 Hz) and 3 gn (35-150 Hz)
---	---------------------------------------

Shock Resistance	15 g-n
-------------------------	--------

Degree of Protection	IP 40
-----------------------------	-------

Weight	2.12 oz 60 g
---------------	-----------------