Vishay Dale



# Metal Film Resistors, Industrial, ± 1 % Tolerance




### **FEATURES**

- Dual power rating:  $P_{70} = 0.25$  W with 0.5 % stability  $P_{70} = 0.50$  W with 1.0 % stability
- Temperature coefficient: ± 100 ppm/K
- Superior electrical performance
- Flame retardant epoxy conformal coating (red brown color)
- Standard 5 band color code marking for ease of identification after mounting
- Tape and reel packaging for automatic insertion (52.4 mm inside tape spacing per EIA-296-E)
- · Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Compliant to RoHS directive 2002/95/EC

STANDA	ANDARD ELECTRICAL SPECIFICATIONS					
PRODUCT	RATED DISSIPATION P <sub>70</sub> W	LIMITING ELEMENT VOLTAGE MAX. V≅	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	E-SERIES
CCF55	0.25/0.5	250	± 100	± 1	10 $\Omega$ to 3.01 $M\Omega$	E96

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	CCF55
Rated Dissipation, P70	W	0.25/0.5
Maximum Working Voltage, Umax.	V≅	≤ 250
Insulation Voltage (1 Min)	V <sub>eff</sub>	500
Dielectric Strength	V <sub>AC</sub>	450
Insulation Resistance	Ω	≥ 10 <sup>11</sup>
Operating Temperature Range	°C	- 65 to + 165
Terminal Strength (Pull Test)	lb	2
Weight	g	0.35 max.








Vishay Dale

**CCF55** 

#### **DIMENSIONS** in inches (millimeters)




PRODUCT	А	В	C (Max.)	D	E
CCF55	$0.245 \pm 0.020$	$0.090 \pm 0.008$	0.265	$0.023 \pm 0.002$	1.100 ± 0.040
	(6.22 ± 0.51)	(2.29 ± 0.20)	(6.73)	(0.60 ± 0.05)	(27.94 ± 1.02)

### **RESISTANCE VALUES**

Vishay Dale model CCF55 is available in the standard 96 resistance values per decade. Values are obtained from the following decade table by multiplying by powers of 10. As an example: 30.1 can represent 30.1  $\Omega$ , 301  $\Omega$ , 3.01 k $\Omega$ , 30.1 k $\Omega$  or 301 k $\Omega$ .

0011436					
10.0	14.7	21.5	31.6	46.4	68.1
10.2	15.0	22.1	32.4	47.5	69.8
10.5	15.4	22.6	33.2	48.7	71.5
10.7	15.8	23.2	34.0	49.9	73.2
11.0	16.2	23.7	34.8	51.1	75.0
11.3	16.5	24.3	35.7	52.3	76.8
11.5	16.9	24.9	36.5	53.6	78.7
11.8	17.4	25.5	37.4	54.9	80.6
12.1	17.8	26.1	38.3	56.2	82.5
12.4	18.2	26.7	39.2	57.6	84.5
12.7	18.7	27.4	40.2	59.0	86.6
13.0	19.1	28.0	41.2	60.4	88.7
13.3	19.6	28.7	42.2	61.9	90.9
13.7	20.0	29.4	43.2	63.4	93.1
14.0	20.5	30.1	44.2	64.9	95.3
14.3	21.0	30.9	45.3	66.5	97.6



## MARKING

The nominal resistance and tolerance are marked on the resistor using five colored bands in accordance with IEC 60062, marking codes for resistors and capacitors.

PERFORMANCE				
RATED DISSIPATION, P70				
CCF55	1/4 W	1/2 W		
TEST <sup>(1)</sup>	MAXIMUM <b>A</b> <i>R</i>	MAXIMUM AR		
Thermal Shock	± 0.5 %	-		
Short Time Overload	± 0.5 %	-		
Low Temperature Operation	± 0.5 %	-		
Moisture Resistance	± 1.5 %	-		
Resistance to Soldering Heat	± 0.5 %	-		
Shock/Bump	± 0.5 %	-		
Vibration	± 0.5 %	-		
Life	± 0.5 %	± 1.0 %		
Terminal Strength	± 0.2 %	-		
Dielectric Withstanding Voltage	± 0.5 %	-		

#### Note

<sup>(1)</sup> Test specifications as per IEC 60115-1



Vishay

## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.