ITW CHEMTRONICS MSDS # 0708

SECTION 1: CHEMICAL PRODUCT AND COMPANY INFORMATION

Company Address:

8125 Cobb Center Drive Kennesaw, GA 30152

> Product Information: 800-TECH-401 Emergency: (Chemtrec) 800-424-9300 Customer Service: 800-645-5244 Revision Date: February 10, 2007

Product Identification

KONFORM® AR (Formerly Konform® AR 2000)

Product Code: CTAR-12, CTAR-12C

SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS							
Product Ingredient Information	CAS No.	Wt. % Range					
n-Butyl acetate	123-86-4	10.0-20.0					
n-propyl acetate	109-60-4	10.0-20.0					
Propylene glycol monomethyl ether acetate	108-65-6	10.0-20.0					
Ethanol	64-17-5	10.0-20.0					
Propane/isobutane blend	68476-86-8	20.0-30.0					
Methyl ethyl ketone	78-93-3	2.0-5.0					
Acrylic copolymer resin	26760-85-0	5.0-15.0					

SECTION 3: HAZARD IDENTIFICATION

Emergency Overview: Clear, colorless liquid with strong, fruity, ethereal odor. This product is extremely flammable. Liquid will irritate eyes and skin under repeated or prolonged exposure. Breathing high concentrations of product may produce drowsiness and a headache.

Potential Health Effects:

Eyes: Liquid, aerosols and vapors of this product are irritating and can cause pain, tearing, reddening and swelling accompanied by a stinging sensation.

Skin: Contact causes skin irritation.

Ingestion: Harmful if swallowed. Irritating to the mouth, throat and stomach. May cause vomiting.

Inhalation: Harmful if inhaled. High concentrations in immediate area can displace oxygen and cause dizziness, unconsciousness and even death with longer exposure. Keep people away from such vapors without self-contained breathing apparatus.

Pre-Existing Medical Conditions Aggravated by Exposure: Heart, lung, skin, eye.

SECTION 4: FIRST AID MEASURES

Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Have eyes examined and tested by medical personnel if irritation develops or persists.

Skin: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists. Wash clothing separately before reuse. Ingestion: If swallowed, do not induce vomiting. Keep head below knees to minimize chance of aspirating material into the lungs. Never give anything by mouth to an unconscious person. Get medical attention immediately.

Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

Flash Point: 30 F (-1C) (liquid TCC), -156 F (-104C) (propellant) LEL/UEL: Not determined (% by volume in air)

Extinguishing Media: Use alcohol foam, carbon dioxide or water spray when fighting fires involving this material.

Fire Fighting Instructions: As in any fire, wear self-contained breathing apparatus (pressure demand, MSHA/NIOSH approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Large Spills: Shut off leak if possible and safe to do so. Wear self-contained breathing apparatus and appropriate personal protective equipment. Absorb spill with inert material (i.e. dry sand or earth), then place in a chemical waste container for proper disposal. Do not flush to sewer. Avoid runoff into storm sewers and ditches that lead to waterways.

Small Spills: Absorb spill with inert material (i.e. dry sand or earth), then place in a chemical waste container for proper disposal.

SECTION 7: HANDLING AND STORAGE

Avoid prolonged or repeated contact with skin, eyes or clothing. Wash hands before eating. Use with adequate ventilation. Avoid breathing product vapor. Do not reuse this container. Store in a cool dry place, away from heat, sparks or flames. Keep container tightly closed when not in use. Do not store in direct sunlight.

KEEP OUT OF REACH OF CHILDREN.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines:

CHEMICAL NAME	ACGIH TLV	OSHA PEL	ACGIH STEL
Propylene glycol monomethyl ether acetate	NA	NA	NA
n-Propyl acetate	200 ppm	200 ppm	250 ppm
n-Butyl acetate	150 ppm	150 ppm	200 ppm
Ethanol	1000 ppm	1000 ppm	NA
Methyl ethyl ketone	200 ppm	200 ppm	300 ppm
Propane	NA	1000 ppm	NA

Work/Hygienic Practices: Good general ventilation should be sufficient to control airborne levels. Local exhaust ventilation may be necessary to control any air contaminants to within their TLVs during the use of this product. If vapor concentration exceeds TLV, use NIOSH approved organic vapor cartridge respirator. Wear safety glasses with side shields (or goggles) and rubber or other chemically resistant gloves when handling this material.

NFPA and HMIS Codes:	NFPA	HMIS
Health	1	1
Flammability	3	3
Reactivity	1	1
Personal Protection	-	В

ITW CHEMTRONICS MSDS # 0708

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Clear, colorless liquid Odor: Strong, fruity, ethereal solvent

pH: NA

Eye:

Vapor Pressure: 12 mmHg @ 68 F

Boiling point: liquid: >210F (>99C); propellant: -43.7 F (-42C)

Vapor Density: >1 (Air=1)

Solubility in Water: negligible

Specific Gravity: 0.91 @ 68F (liquid only) Evaporation Rate: >1 (Butyl acetate=1)

 $\underline{\text{Viscosity:}} > 1 \text{ (Water = 1)}$ Percent Volatile: 90%

SECTION 10: STABILITY AND REACTIVITY

Stability: This product is stable. Conditions to Avoid: Do not spray near open flames, red hot surfaces or other sources of ignition.

Incompatibility; Do not mix powdered alkali and alkaline earth metals or strong oxidizing agents.

Products of Decomposition: Thermal decomposition may release carbon monoxide, carbon dioxide and incompletely burned hydrocarbons.

Hazardous Polymerization: Will not occur. Conditions to avoid: NA

SECTION 11: TOXICOLOGICAL INFORMATION

Inhalation: Ingestion:

n-Butyl acetate human TCLo 200 ppm Propylene glycol monomethyl ether acetate LD50 8532 mg/kg

n-Propyl acetate human TCLo 1000 mg/m3 n-Butyl acetate LD50/rat 10768 mg/kg Methyl ethyl ketone human TCLo 100 ppm/5M n-Propyl acetate LD50/rat 9370 mg/kg Ethanol LC50 rats 20,000 ppm/10 hrs Methyl ethyl ketone LD50/rat 2737 mg/kg Ethanol LD50/rat 7060 mg/kg

Skin:

n-Butyl acetate rabbit 20 mg open; SEV Propylene glycol monomethyl ether acetate LD50/rabbit > 5000 mg/kg

n-propyl acetate rabbit 500 mg/24H MLD n-Butyl acetate rabbit 500 mg/24H MOD Methyl ethyl ketone human 350 ppm n-Propvl acetate 500 mg open MLD Ethanol rabbit 500 mg; SEV Methyl ethyl ketone rabbit 500 mg/24H MOD

Ethanol rabbit 400 mg open MLD

Cancer Information: No ingredients listed as human carcinogens by NTP or IARC

Mutagenic effects: none Reproductive effects: none Teratogenic effects: none

SECTION 12: ECOLOGICAL INFORMATION

Environmental Impact Information

Avoid runoff into storm sewers and ditches which lead to waterways. Water runoff can cause environmental damage.

REPORTING

US regulations require reporting spills of this material that could reach any surface waters. The toll free number for the

US Coast Guard National Response Center is: 1-800-424-8802

SECTION 13: DISPOSAL CONSIDERATIONS

Dispose of in accordance with all federal, state and local regulations. Water runoff can cause environmental damage.

SECTION 14: TRANSPORTATION INFORMATION

	Proper			Sub.	Pkg.	Hazard	Pkg.	Max.
	Shipping Name	UN Number	Class	Risk	Group	Label	Instr.	Quantity
Air:	Aerosols flammable	UN 1950	2.1	NA	NA	Flammable	203	75/150 kg
						Gas		
Ground:	Consumer Commodity	NA	ORM-D	NA	NA	ORM-D	Pkg.	173.306
	ORM-D						Auth	

SECTION 15: REGULATORY INFORMATION

SECTION 313 SUPPLIER NOTIFICATION

This product contains no toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To- Know Act of 1986 (40CFR372).

This information should be included on all MSDSs copied and distributed for this material.

TOXIC SUBSTANCES CONTROL ACT (TSCA). All ingredients of this product are listed on the TSCA Inventory.

WHMIS: Class A; Class B5; Class D2B

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

SECTION 16: OTHER INFORMATION

Product is a Level 3 aerosol. Do not puncture or incinerate containers. Normal ventilation for standard manufacturing practices is usually adequate. Local exhaust should be used when large amounts are released.

To the best of our knowledge, the information contained herein is accurate. However, all materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist.