

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 8403, 14 AWG, Stranded Bare Copper, Tray Cable



14 AWG, Stranded Bare Copper Cable

UL SUBJECT 1277
OSHA ACCEPTABLE
IEEE-383

UL FLAME TEST IEEE 1202, 1581, 1685

CSA FLAME TEST FT4

Stranded bare Copper conductors, color coded PVC insulation with overall Nylon jacket, sizes 18 and 16 AWG are rated TFFN, sizes 14, 12 and 10 AWG are rated VW-1 THHN/THWN, Polyester binder tape, black PVC jacket.

Application: For use in Class 1, Division 2 hazardous locations; for installation in trays, wireways, ducts, conduit and aerially when properly supported by a messenger; approved for direct burial, wet or dry locations and outdoors in cable trays where a sunlight and oil resistant rating is required

SPECIFICATIONS

| | |
|---------------------------|--------------------------------|
| Conductor Size | 14 AWG |
| Stranding | 7/0242 Bare Copper |
| No. of Conductors | 4 (Twisted) |
| Insulation | PVC/Nylon |
| Nom. Insulation Thickness | 0.020 in |
| Jacket | PVC, Black |
| Nom. Jacket Thickness | 0.045 in |
| Nom. O.D. | 0.365 in |
| UL Style | NPLF, PLTC, TC-ER |
| Color Code | Black Blue Orange Red |
| Voltage | 600 V |
| Operating Temperature | -25 to 90 °C |

RoHS Compliant



RoHS Compliant